



OMP40M system

OMP40M system


OMP40M is a special modular version of OMP40-2. It enables probe inspection of part features inaccessible to OMP40-2, by fitting selected adaptors and extensions as shown below.



OMP40M dimensions



OMP40M screw torque values



Parts list — please quote the part number when ordering equipment.

Type	Part no.	Description
OMP40M module	A-5626-2001	OMP40M module with batteries, tool kit and Quick-start guide. Optical on, set to: optical off/trigger filter off/Probe 1 start, modulated transmission/standard power.
OMP40M module	A-5626-0001	OMP40M module with batteries, tool kit and Quick-start guide. Optical on, set to: optical off/trigger filter off/legacy transmission, start filter off/standard power.
LPE1	A-2063-7001	LPE1 extension bar - 50 mm long.
LPE2	A-2063-7002	LPE2 extension bar - 100 mm long.
LPE3	A-2063-7003	LPE3 extension bar - 150 mm long.
MA4	A-2063-7600	90° adaptor assembly.
LP2	A-2063-6098	LP2 probe.

**For worldwide contact details, please visit our
main web site at www.renishaw.com/contact**

