


Styli for Zeiss applications

When precision matters, insist on genuine Renishaw styli. Don't settle for less!

M5 threaded stylus range

Ruby ball styli (tungsten carbide)

A-5555-0018 602030-9010-000 DK 3.0 mm L 25 mm	A-5555-0019 600342-8020-000 DK 3.0 mm L 33.5 mm	A-5555-0020 602030-9011-000 DK 3.0 mm L 50 mm	A-5555-0021 600342-8021-000 DK 3.0 mm L 58 mm	A-5555-0022 600342-8025-000 DK 4.0 mm L 33.5 mm	A-5555-0052 602030-8060-000 DK 0.8 mm L 32 mm	A-5555-0053 602030-8061-000 DK 1.0 mm L 32 mm	A-5555-0054 602030-8062-000 DK 1.35 mm L 32 mm	A-5555-0055 602030-8063-000 DK 1.35 mm L 44 mm	A-5555-0056 602030-8064-000 DK 1.5 mm L 32 mm	A-5555-0057 602030-8065-000 DK 1.5 mm L 44 mm	A-5555-0058 602030-8066-000 DK 2.0 mm L 32 mm	A-5555-0059 602030-8067-000 DK 2.0 mm L 44 mm	A-5555-0060 602030-8068-000 DK 2.0 mm L 58 mm	A-5555-0061 602030-8069-000 DK 2.5 mm L 32 mm	A-5555-0062 602030-8070-000 DK 2.5 mm L 44 mm	A-5555-0063 602030-8071-000 DK 2.5 mm L 58 mm
---	---	---	---	---	---	---	--	--	---	---	---	---	---	---	---	---



Styli for star styli (tungsten carbide)

A-5555-0078 600342-8200-000 DK 1.35 mm L 32.9 mm	A-5555-0079 600342-8201-000 DK 1.5 mm L 33.0 mm	A-5555-0080 600342-8202-000 DK 2.0 mm L 33.5 mm	A-5555-0084 600342-8250-000 DK 0.3 mm L 21.8 mm	A-5555-0085 600342-8251-000 DK 0.5 mm L 22 mm	A-5555-0086 600342-8252-000 DK 0.6 mm L 22.1 mm	A-5555-0087 600342-8253-000 DK 0.8 mm L 22.3 mm	A-5555-0088 600342-8254-000 DK 1.0 mm L 22.5 mm
--	---	---	---	---	---	---	---

Rotational adjustment piece (tungsten carbide)

A-5555-0099 602030-9095-000 D 18 mm L 30 mm

Holder for styli (1-1.5 mm)

A-5555-0104 600341-8160-000 DK 1 mm L 45 mm

Holder for up to 5 styli (tungsten carbide)

A-5555-0105 600341-8367-000 D 11 mm Styl stem D 1.0 mm L 10 mm	A-5555-0106 600341-8368-000 D 11 mm Styl stem D 1.5 mm L 10 mm
---	---

Part number system
Renishaw:
A-XXXX-XXXX
Zeiss:
6XXXX-XXXX-XXX

Ball stems – stepped (tungsten carbide)

A-5555-0107 600341-8454-000 DK 1.0 mm L 16 mm	A-5555-0108 600341-8450-000 DK 0.3 mm L 5.3 mm	A-5555-0109 600341-8451-000 DK 0.5 mm L 15.5 mm	A-5555-0110 600341-8452-000 DK 0.6 mm L 15.6 mm	A-5555-0111 600341-8453-000 DK 0.8 mm L 15.8 mm
---	--	---	---	---

Ball stems (tungsten carbide)

A-5555-0112 600341-8500-000 DK 1.35 mm L 26.4 mm	A-5555-0113 600341-8501-000 DK 1.5 mm L 26.5 mm	A-5555-0114 600341-8502-000 DK 2.0 mm L 27 mm	A-5555-0115 600341-8503-000 DK 2.5 mm L 27.5 mm
--	---	---	---

Cubes (titanium)

A-5555-0189 600341-8361-000 15 mm x 15 mm	A-5555-0190 600341-8002-000 20 mm x 20 mm
--	--

Joints (titanium)

A-5555-0218 600342-9002-000 L 30 mm Depth 11 mm	A-5555-0219 600342-9003-000 L 36 mm Depth 18 mm
---	---

Adaptors (tungsten carbide)

A-5555-0226 602030-0215-000 M5 - M2 L 10 mm	A-5555-0227 602030-0315-000 M5 - M3 L 10 mm
---	---

Extensions (aluminium)

A-5555-0127 600341-8422-000 D 20 mm L 100 mm	A-5555-0128 600341-8423-000 D 20 mm L 80 mm	A-5555-0130 600341-8425-000 D 11 mm L 100 mm	A-5555-0132 600341-8264-000 D 11 mm L 100 mm	A-5555-0134 600341-8262-000 D 11 mm L 60 mm	A-5555-0135 600341-8261-000 D 11 mm L 40 mm
--	---	--	--	---	---

Extensions (stainless steel)

A-5555-0136 600341-0260-000 D 11 mm L 100 mm	A-5555-0140 600341-0252-000 D 11 mm L 20 mm	A-5555-0142 600341-0250-000 D 11 mm L 10 mm
--	---	---

Extensions (titanium)

A-5555-0145 602030-9046-000 D 11 mm L 20 mm	A-5555-0148 602030-9049-000 D 11 mm L 40 mm	A-5555-0152 602030-9053-000 D 11 mm L 60 mm
---	---	---

Extensions (thermo stable carbon fibre)

A-5555-0647 626107-1040-100 D 11 mm L 40 mm	A-5555-0648 626107-1050-100 D 11 mm L 50 mm	A-5555-0652 626107-1100-100 D 11 mm L 100 mm	A-5555-0659 626107-2100-100 D 20 mm L 100 mm	A-5555-0663 626107-2200-100 D 20 mm L 200 mm
---	---	--	--	--

Adaptor plates (aluminium)

A-5555-0255 600667-9601-000 MT/VAST with ID chip	A-5555-1235 620161-8254-000 XXT TL1 adaptor plate with ID chip	A-5555-1236 620161-8259-000 XXT TL1 reference plate with ID chip	A-5555-1237 620161-8264-000 XXT TL2 adaptor plate with ID chip	A-5555-1238 620161-8269-000 XXT TL2 reference plate with ID chip	A-5555-1241 626103-8431-055 VAST XXX TL1 with star adaptor	A-5555-1242 626103-8433-055 VAST XXX TL3 with star adaptor
---	---	---	---	---	---	---

M3 tungsten carbide XXT styli

Ruby ball styli

A-5004-3176 626113-0030-013 DK 0.3 mm L 13 mm	A-5004-2186 626113-0050-020 DK 0.5 mm L 20 mm	A-5004-3427 626113-0100-030 DK 1.0 mm L 30 mm	A-5004-1779 626113-0151-040 DK 1.5 mm L 40 mm	A-5555-3855 626113-0201-040 DK 2.0 mm L 40 mm	A-5004-3428 626113-0250-040 DK 2.5 mm L 40 mm
---	---	---	---	---	---

Reference styli XXT (red dot)

Ruby ball styli (carbon fibre)

A-5555-2033 626103-0501-030 DK 5.0 mm L 30 mm	A-5555-3858 626103-0501-050 DK 5.0 mm L 50 mm
---	---

