



America

CERTIFICATE

No. U8 17 12 61100 042

Holder of Certificate: **Renishaw PLC**
 New Mills
 Wotton under Edge
 Gloucestershire GL12 8JR
 UNITED KINGDOM

Production Facility(ies): 99726

Certification Mark:



Product: **C US Industrial Control Systems and Components Vacuum casting machines**

Model(s): **5/01 Vario
5/04 Vario**

Parameters:

Model 5/01:	
Rated Voltage:	230V
Rated Frequency:	50-60Hz
Rated Current:	10A
Protection Class:	Class I
Model 5/04:	
Rated Voltage:	
North American:	460V, 3ph
International:	415V, 3ph
Rated Frequency:	50-60Hz
Rated Current:	13A
Protection Class:	Class I

Tested according to: UL 508A:2013 / R:2014-01
CAN/CSA C22.2 No. 14-13

The product was voluntarily tested according to the relevant safety requirements noted above. It can be marked with the certification mark above. The mark must not be altered in any way. This product certification system operated by TÜV SÜD America Inc. most closely resembles system 3 as defined in ISO/IEC 17067. Certification is based on the TÜV SÜD "Testing and Certification Regulations". TÜV SÜD America Inc. is an OSHA recognized NRTL and a Standards Council of Canada accredited certification body.

Test report no.: 071-75940545T-000

Date, 2017-12-06

Page 1 of 1

