


ACR3 with powered port - power supply

www.renishaw.com/ACR3



	Input	Output
Voltage	90 V to 264 Vac, 50 Hz to 60 Hz	12 Vdc \pm 0.6 Vdc
Current	1.0 A maximum	3.75 A maximum
Protection	Fitted with an internal fuse	The unit is protected against over-voltage and over-current

Environment

Ambient temperature range	Storage	-20 °C to +85 °C
	Operating	0 °C to +40 °C

The user is advised to use this equipment only with the approved power supply (Renishaw part number P-EA02-0031). Any substitute power supply must meet an equivalent specification and must be certified to standard IEC 60950-1.

For worldwide contact details, please visit our main web site at www.renishaw.com/contact

RENISHAW HAS MADE CONSIDERABLE EFFORTS TO ENSURE THE CONTENT OF THIS DOCUMENT IS CORRECT AT THE DATE OF PUBLICATION BUT MAKES NO WARRANTIES OR REPRESENTATIONS REGARDING THE CONTENT. RENISHAW EXCLUDES LIABILITY, HOWSOEVER ARISING, FOR ANY INACCURACIES IN THIS DOCUMENT.



H - 1000 - 4084 - 02