

Styli and accessories

When precision matters insist on genuine Renishaw styli. Don't settle for less!

M2 threaded stylus range

Ruby ball styli (stainless steel) A-5000-7806 A 1.0 (0.04) B 10.0 (0.40) A-5000-7802 A 1.5 (0.06) B 10.0 (0.40) A-5000-7807 A 2.0 (0.08) B 10.0 (0.40) A-5000-3604 A 3.0 (0.12) B 10.0 (0.40)	Ruby ball styli (tungsten carbide) A-5000-7800 A 0.3 (0.012) B 10.0 (0.40) A-5000-7801 A 0.7 (0.03) B 10.0 (0.40) A-5000-7808 A 1.0 (0.04) B 20.0 (0.79) A-5003-0033 A 1.0 (0.04) B 20.0 (0.79) A-5003-0034 A 1.5 (0.06) B 20.0 (0.79) A-5003-1896 A 2.5 (0.10) B 20.0 (0.79)	Ruby ball styli (carbon fibre) A-5000-4154 A 4.0 (0.16) B 10.0 (0.40) A-5000-4155 A 5.0 (0.20) B 10.0 (0.40) A-5000-4156 A 6.0 (0.24) B 10.0 (0.40) A-5003-0035 A 1.5 (0.06) B 30.0 (1.19) A-5003-0036 A 2.0 (0.08) B 30.0 (1.19) A-5003-0038 A 2.5 (0.10) B 30.0 (1.19) A-5003-0040 A 3.0 (0.12) B 30.0 (1.19) A-5003-0043 A 4.0 (0.16) B 30.0 (1.19) A-5003-0048 A 5.0 (0.20) B 40.0 (1.58)	Stylus extensions (stainless steel) A-5004-7610 A 5.0 (0.20) B 5.0 (0.20) A-5004-7585 A 10.0 (0.40) B 10.0 (0.40) A-5004-7591 A 30.0 (1.19) B 30.0 (1.19) A-5004-7611 A 40.0 (1.58) B 40.0 (1.58)
Ruby ball styli (ceramic) A-5003-1370 A 4.0 (0.16) B 30.0 (1.19) A-5003-4779 A 5.0 (0.20) B 30.0 (1.19) A-5003-4780 A 6.0 (0.24) B 30.0 (1.19) A-5003-0066 A 5.0 (0.20) B 50.0 (1.97)	Stylus extensions (carbon fibre) A-5003-2280 A 40.0 (1.58) B 40.0 (1.58) A-5003-2283 A 90.0 (3.55) B 90.0 (3.55)	Parallel hemispherical ended styli (tungsten carbide) A-5003-0074 A 2.0 (0.08) B 40.0 (1.58)	Special purpose styli (silver steel) A-5004-7588 A 15.0 (0.60) B 15.0 (0.60) (ceramic) A-5000-3614 A 18.0 (0.71) B 11.0 (0.44)
Disc styli (ruby) A-5000-3611 A 6.0 (0.24) B 1.2 (0.06) (silver steel) A-5000-7809 A 18.0 (0.71) B 1.5 (0.06) (silver steel) A-5000-7810 A 25.0 (0.99) B 1.5 (0.06)	Star styli centres (tungsten carbide) A-5003-4789 A 1.0 (0.04) B 8.5 (0.34) (stainless steel) A-5000-3609 A 2.0 (0.08) B 16.5 (0.65)	Stylus extensions (ceramic) A-5003-0070 A 30.0 (1.19) B 30.0 (1.19) A-5003-0072 A 50.0 (1.97) B 50.0 (1.97)	Stylus extensions (carbon fibre) A-5003-5000 A 180.0 (7.09) B 180.0 (7.09)
Cylinder styli (silver steel) A-5004-7589 A 1.5 (0.06) B 11.0 (0.44) A-5004-7590 A 3.0 (0.12) B 13.0 (0.52) (Inch) A-5000-8876 A 1.0 (0.04) B 15.0 (0.60) A-5000-8877 A 1.5 (0.06) B 15.0 (0.60) A-5000-7812 A 2.0 (0.08) B 20.0 (0.79) A-5003-0073 A 4.0 (0.16) B 20.0 (0.79)	Star styli (fixed) (stainless steel) A-5000-7811 A 1.0 (0.04) B 10.0 (0.40) A-5000-7811 A 1.0 (0.04) B 20.0 (0.79) A-5003-4788 A 1.0 (0.04) B 20.0 (0.79) A-5000-7629 A 2.0 (0.08) B 30.0 (1.19) A-5000-3626 A 2.0 (0.08) B 30.0 (1.19)	Stylus extensions (stainless steel) A-5004-7609 A 10.0 (0.40) B 10.0 (0.40) A-5004-7583 A 20.0 (0.79) B 20.0 (0.79) A-5004-7584 A 35.0 (1.38) B 35.0 (1.38) (ceramic) A-5003-0075 A 50.0 (1.97) B 50.0 (1.97) (carbon fibre) A-5003-4864 A 75.0 (2.96) B 75.0 (2.96)	Disc styli (silver steel) A-5003-5288 A 12.0 (0.48) B 3.0 (0.12) A-5003-5290 A 35.0 (1.38) B 5.0 (0.20)

M3 threaded stylus range

Ruby ball styli (stainless steel) A-5000-3551 A 1.0 (0.04) B 21.0 (0.83) A-5000-3552 A 2.0 (0.08) B 21.0 (0.83) A-5000-3553 A 3.0 (0.12) B 21.0 (0.83) A-5000-7606 A 4.0 (0.16) B 21.0 (0.83) A-5000-3554 A 4.0 (0.16) B 31.0 (1.23)	Stylus extensions (stainless steel) A-5004-7609 A 10.0 (0.40) B 10.0 (0.40) A-5004-7583 A 20.0 (0.79) B 20.0 (0.79) A-5004-7584 A 35.0 (1.38) B 35.0 (1.38) (ceramic) A-5003-0075 A 50.0 (1.97) B 50.0 (1.97) (carbon fibre) A-5003-4864 A 75.0 (2.96) B 75.0 (2.96)	Silicon nitride ball styli (stainless steel) A-5003-5723 A 2.0 (0.08) B 21.0 (0.83) (ceramic) A-5003-5725 A 4.0 (0.16) B 50.0 (1.97)	Zirconia ball styli (stainless steel) A-5003-5737 A 4.0 (0.16) B 21.0 (0.83) (carbon fibre) A-5003-5740 A 6.0 (0.24) B 75.0 (2.96)	Ruby ball styli (carbon fibre) A-5003-4860 A 4.0 (0.16) B 75.0 (2.96) A-5003-4862 A 8.0 (0.32) B 75.0 (2.96) A-5003-4861 A 6.0 (0.24) B 100.0 (3.94) A-5003-4863 A 8.0 (0.32) B 100.0 (3.94)
Disc and hollow ball styli (silver steel) A-5000-7612 A 35.0 (1.38) B 5.0 (0.20) (ceramic) A-5000-7814 A 30.0 (1.19) B 17.0 (0.67)	Key 	Stylus knuckles, cubes and bolts (stainless steel) A-5003-5278 A 36.5 (1.44) B 33.0 (1.30) A-5003-5676 A 33.0 (1.30) B 20.0 (0.79) (titanium) A-5003-5682 A 20.0 (0.79) B 20.0 (0.79)	Styli centres (ceramic) A-5003-5233 A 2.5 (0.10) B 50.0 (1.97) A-5003-5275 A 16.0 (0.63) B 19.5 (0.77) A-5003-5277 A 30.0 (1.19) B 24.5 (0.97)	

M4 threaded stylus range

Ruby ball styli (stainless steel) A-5000-7545 A 1.0 (0.04) B 19.5 (0.77) A-5000-7547 A 2.0 (0.08) B 19.0 (0.75) A-5000-7549 A 3.0 (0.12) B 18.5 (0.73) A-5000-6352 A 5.0 (0.20) B 30.0 (1.19)	Stylus extensions (stainless steel) A-5004-7599 B 10.0 (0.40) A-5004-7601 B 20.0 (0.79) A-5004-7602 B 30.0 (1.19) (ceramic) A-5000-7754 B 30.0 (1.19) A-5000-7755 B 50.0 (1.97) A-5000-7727 B 100.0 (3.94)	Zirconia ball styli (stainless steel) A-5003-5742 A 2.0 (0.08) B 19.0 (0.75) (carbon fibre) A-5003-5744 A 6.0 (0.24) B 50.0 (1.97)	Silicon nitride ball styli (stainless steel) A-5003-5729 A 4.0 (0.16) B 18.0 (0.71) (carbon fibre) A-5003-5731 A 6.0 (0.24) B 100.0 (3.94)	Ruby ball styli (stainless steel) A-5000-7521 A 5.0 (0.20) B 50.0 (1.97) A-5000-7522 A 5.0 (0.20) B 100.0 (3.94) (ceramic) A-5000-3709 A 6.0 (0.24) B 50.0 (1.97) A-5000-3712 A 6.0 (0.24) B 100.0 (3.94)
Digitising styli (hemispherical anodised aluminum ball styli) A-5000-7720 A 12.0 (0.48) B 10.5 (0.42) A-5000-7722 A 20.0 (0.79) B 11.5 (0.46) A-5000-7724 A 32.0 (1.26) B 9.5 (0.38)	Crash protection devices (stainless steel) A-5004-7598 B 8.0 (0.32) (silver steel) A-5004-7621 B 12.0 (0.48)			

M5 threaded stylus range

Silicon nitride ball styli (tungsten carbide) A-5000-7720 A 2.0 (0.08) B 20.0 (0.79) (carbon fibre) A-5000-7722 A 6.0 (0.24) B 50.0 (1.97)	Ruby ball styli (tungsten carbide) A-5003-5216 A 3.0 (0.12) B 30.0 (1.19) (carbon fibre) A-5003-5218 A 4.0 (0.16) B 40.0 (1.58)	Ruby ball styli (tungsten carbide) A-5003-5224 A 3.0 (0.12) B 40.0 (1.58) A-5003-5236 A 5.0 (0.20) B 50.0 (1.97) (carbon fibre) A-5003-5251 A 8.0 (0.32) B 75.0 (2.96) A-5003-5262 A 8.0 (0.32) B 100.0 (3.94) A-5003-5265 A 6.0 (0.24) B 150.0 (5.91) A-5003-5269 A 6.0 (0.24) B 200.0 (7.88)	Stylus extensions (carbon fibre) A-5003-5000 A 180.0 (7.09) B 180.0 (7.09)
Ruby ball styli (tungsten carbide) A-5003-5215 A 1.0 (0.04) B 20.0 (0.79) A-5003-5217 A 1.5 (0.06) B 30.0 (1.19) A-5003-5221 A 1.5 (0.06) B 40.0 (1.58) A-5003-5244 A 1.5 (0.06) B 75.0 (2.96) A-5003-5255 A 1.5 (0.06) B 100.0 (3.94)	Disc styli (silver steel) A-5003-5288 A 12.0 (0.48) B 3.0 (0.12) A-5003-5290 A 35.0 (1.38) B 5.0 (0.20)	Zirconia ball styli (tungsten carbide) A-5003-5747 A 4.0 (0.16) B 20.0 (0.79) (carbon fibre) A-5003-5749 A 6.0 (0.24) B 100.0 (3.94)	Styli centres (ceramic) A-5003-5233 A 2.5 (0.10) B 50.0 (1.97) A-5003-5275 A 16.0 (0.63) B 19.5 (0.77) A-5003-5277 A 30.0 (1.19) B 24.5 (0.97)
Ruby micro ball styli (tungsten carbide) A-5003-5201 A 0.3 (0.012) B 20.0 (0.79) A-5003-5227 A 0.7 (0.03) B 50.0 (1.97)	Hemispherical styli (ceramic) A-5003-5273 A 16.0 (0.63) B 19.5 (0.77) A-5003-5277 A 30.0 (1.19) B 24.5 (0.97)	Styli knuckles, cubes and bolts (stainless steel) A-5003-5278 A 36.5 (1.44) B 33.0 (1.30) A-5003-5676 A 33.0 (1.30) B 20.0 (0.79) (titanium) A-5003-5682 A 20.0 (0.79) B 20.0 (0.79)	Styli tools A-5000-7610 M2 thread size B 7.5 (0.30) A-5000-7611 M3 thread size B 13.0 (0.52)
Adaptors (stainless steel) A-5004-7595 M4/M2 B 5.0 (0.20) A-5004-6350 M4/M2 B 10.0 (0.40) A-5003-0858 M5/M2 B 10.0 (0.40)			