




Precision styli for BLUM touch probes

Your partner in precision

Discover the comprehensive range of precision styli that our experts have developed for BLUM touch probes.

As well as high-precision product features, you'll also benefit from our styli design guidance and full global technical support.



www.renishaw.com/shop/styli



#renishaw

Select your styli

We offer a comprehensive range of ball diameters and lengths to suit your application needs. Custom variants are available on request.



Styli for TC50/51/60/61

New BLUM part number	Old BLUM part number	Renishaw part number	Description
143412	P03.8000-010.050.02	A-6560-2648	M4 STY D2R L50 EWL8 d4,5CER
143414	P03.8000-010.050.04	A-6560-2649	M4 STY D4R L50 EWL11 d4,5CER
143415	P03.8000-010.050.05	A-6560-2650	M4 STY D5R L50 EWL12 d4,5CER
143416	P03.8000-010.050.06	A-5555-2868	M4 STY D6R L50 EWL27,5 d4,5CER
143424	P03.8000-010.100.02	A-6560-2651	M4 STY D2R L100 EWL8,3 d4,5CER
143425	P03.8000-010.100.03	A-6560-2652	M4 STY D3R L100 EWL10 d4,5CER
143426	P03.8000-010.100.04	A-6560-2653	M4 STY D4R L100 EWL11 d4,5CER
143427	P03.8000-010.100.05	A-6560-2654	M4 STY D5R L100 EWL12 d4,5CER
143428	P03.8000-010.100.06	A-5555-2873	M4 STY D6R L100 EWL77,5 d4,5CER

Styli for TC52/53/54/62/63/64/76

New BLUM part number	Old BLUM part number	Renishaw part number	Description
143743	P03.8000-020.050.01	A-6560-2655	M4 STY D1R L50 EWL5,1 d4,5CER
143744	P03.8000-020.050.02	A-6560-2656	M4 STY D2R L50 EWL18,3 d4,5CER
143746	P03.8000-020.050.04	A-6560-2657	M4 STY D4R L50 EWL13,7 d4,5CER
143747	P03.8000-020.050.05	A-6560-2658	M4 STY D5R L50 EWL27,5 d4,5CER
143759	P03.8000-020.100.05	A-6560-2659	M4 STY D5R L100 EWL72,5 d4,5CER

www.renishaw.com/shop/styli



#renishaw

+44 (0) 1453 524524



uk@renishaw.com

© 2021 - 2024 Renishaw plc. All rights reserved. RENISHAW® and the probe symbol are registered trade marks of Renishaw plc. Renishaw product names, designations and the mark 'apply innovation' are trade marks of Renishaw plc or its subsidiaries. Other brand, product or company names are trade marks of their respective owners. Renishaw plc. Registered in England and Wales. Company no: 1106260. Registered office: New Mills, Wotton-under-Edge, Glos, GL12 8JR, UK.

WHILE CONSIDERABLE EFFORT WAS MADE TO VERIFY THE ACCURACY OF THIS DOCUMENT AT PUBLICATION, ALL WARRANTIES, CONDITIONS, REPRESENTATIONS AND LIABILITY, HOWSOEVER ARISING, ARE EXCLUDED TO THE EXTENT PERMITTED BY LAW.

Part no.: H-1000-8507-01-C