



SCOPE OF ACCREDITATION TO ISO/IEC 17025:2017

RENISHAW MEXICO S DE RL DE CV
Iridium 5004, Parque Industrial Milenium
Apodaca, Nuevo León, MÉXICO 66626
Diego Barron Phone: +52 81 2282 2900

CALIBRATION

Valid to: June 30, 2028

Certificate Number: 4010.01

In recognition of the successful completion of the A2LA evaluation process (including an assessment of the organization's compliance with R205 – A2LA's Calibration Program Requirements), accreditation is granted to this laboratory to perform the following calibrations^{1, 5}:

I. Dimensional

Parameter/Equipment	Range	CMC ^{2, 4} (±)	Comments
Coordinate Measuring Machines (CMM) ³ – Length Measurement Error E_L and R_0	Up to 1500 mm	$(0.23 + L/990) \mu\text{m}$	ISO 10360-2 use of gage blocks
	Cylindrical Measurement Volume (250 mm x 250 mm radius)	$(0.23 + L/990) \mu\text{m}$	In-house method based on ISO 10360- 2
CMM Single Stylus Probing ³	(25 to 45) mm	0.10 μm	ISO 10360-5:2010 – single stylus probing test (form)
			ISO 10360-5:2020 – single stylus probing test:
		0.08 μm 0.30 μm	PForm.Sph.1x25:SS:Tact PSize.Sph.1x25:SS:Tact

¹ This laboratory offers commercial calibration service and field calibration service.

- ² Calibration and Measurement Capability Uncertainty (CMC) is the smallest uncertainty of measurement that a laboratory can achieve within its scope of accreditation when performing more or less routine calibrations of nearly ideal measurement standards or nearly ideal measuring equipment. CMCs represent expanded uncertainties expressed at approximately the 95 % level of confidence, usually using a coverage factor of $k = 2$. The actual measurement uncertainty of a specific calibration performed by the laboratory may be greater than the CMC due to the behavior of the customer's device and to influences from the circumstances of the specific calibration.
- ³ Field calibration service is available for this calibration. Please note the actual measurement uncertainties achievable on a customer's site can normally be expected to be larger than the CMC found on the A2LA Scope. Allowance must be made for aspects such as the environment at the place of calibration and for other possible adverse effects such as those caused by transportation of the calibration equipment. The usual allowance for the actual uncertainty introduced by the item being calibrated, (e.g. resolution) must also be considered and this, on its own, could result in the actual measurement uncertainty achievable on a customer's site being larger than the CMC.
- ⁴ L is the numerical value of the nominal length of the device measured in millimeters.
- ⁵ This scope meets A2LA's *P112 Flexible Scope Policy*.



Accredited Laboratory

A2LA has accredited

RENISHAW MEXICO S DE RL DE CV

Apodaca, Nuevo León, MÉXICO

for technical competence in the field of

Calibration

This laboratory is accredited in accordance with the recognized International Standard ISO/IEC 17025:2017 General requirements for the competence of testing and calibration laboratories. This laboratory also meets the requirements of R205 – Specific Requirements: Calibration Laboratory Accreditation Program. This accreditation demonstrates technical competence for a defined scope and the operation of a laboratory quality management system (refer to joint ISO-ILAC-IAF Communiqué dated April 2017).



Presented this 12th day of June 2026.

A blue ink signature of Mr. Trace McInturff, Vice President of Accreditation Services.

Mr. Trace McInturff, Vice President, Accreditation Services
For the Accreditation Council
Certificate Number 4010.01
Valid to June 30, 2028

For the calibrations to which this accreditation applies, please refer to the laboratory's Calibration Scope of Accreditation.