


RTLA30 absolute linear scale



RTLA30 absolute linear encoder tape scale from Renishaw combines $\pm 5 \mu\text{m}/\text{m}$ accuracy with the ruggedness of stainless steel. Two versions are available: self-adhesive RTLA30-S and RTLA30 for use with the *FASTRACK*™ carrier system.

Designed for applications that demand high-accuracy and an independent expansion coefficient with tape scale convenience, RTLA30-S and RTLA30 are read by Renishaw's RESOLUTE™ absolute readhead.

RTLA30-S is laid onto the substrate using its self-adhesive backing tape. A patented application tool makes this a quick, simple and inexpensive process. A clamp is fitted at a single point to lock the scale to the substrate.

RTLA30 (without self-adhesive) is used with *FASTRACK*. In this case, the scale is held securely in place by two miniature, yet rugged, guide rails. Again, the scale is clamped in a single point to allow independent expansion with extremely low hysteresis, even over wide temperature ranges. If damaged, the scale can be pulled out of the guide rails and quickly replaced, even where access is limited, thus reducing machine downtime. This feature also makes the new linear encoder system ideal for large machines that need to be sectioned for transportation.

RTLA30-S and RTLA30 with *FASTRACK* are suitable for many applications, including FPD manufacturing and inspection machines, PV manufacturing, linear motors with aluminium substrates, axes that are exposed to potential damage, large CMMs and other machines that require the scale to be installed/removed for transit, or simply for any application where thermal expansion of the scale must be independent of the machine structure.

- High accuracy ($\pm 5 \mu\text{m}/\text{m}$) absolute scale. Further improvement possible with error correction.
- RTLA30 scale expands at its own low thermal coefficient ($10.1 \pm 0.2 \mu\text{m}/\text{m}/^\circ\text{C}$ @ 20°C)
- Use with the *FASTRACK* carrier for very low hysteresis
- *FASTRACK* guide rails are pre-aligned in reels for cut-to-suit flexibility
- Quick installation. *FASTRACK* adds fast scale replacement capability
- Scale can be locked to the substrate at a single datum point anywhere along the axis
- Lengths up to 21 m
- High solvent immunity
- Compatible with RESOLUTE absolute readheads

RTLA30-S, RTLA30 and *FASTRACK* specifications

| | | |
|--|-------------------------------------|--|
| Description | RTLA30-S | Hardened and tempered martensitic stainless steel tape scale with self-adhesive backing tape for use with RESOLUTE readheads |
| | RTLA30 | Hardened and tempered martensitic stainless steel tape scale for use with the <i>FASTRACK</i> carrier and RESOLUTE readheads. |
| | <i>FASTRACK</i> | Hardened stainless steel guide rails with integral sacrificial spacers, with self-adhesive backing tape for easy installation. |
| Pitch | RTLA30-S/RTLA30 | 30 µm |
| Form (height x width) | RTLA30-S | 0.4 mm x 8 mm (including adhesive) |
| | <i>FASTRACK</i> | 0.4 mm x 18 mm (including adhesive) |
| Accuracy (at 20 °C) | RTLA30-S/RTLA30 | ±5 µm/m |
| Coefficient of thermal expansion (at 20 °C) | RTLA30-S/RTLA30/ <i>FASTRACK</i> | 10.1 ± 0.2 µm/m/°C |
| Temperature (system) | Storage | -20 °C to +80 °C |
| | Operating | 0 °C to +80 °C |
| Humidity (system) | | 95% relative humidity (non-condensing) to IEC 60068-2-78 |
| Shock (system) | Non-operating | 1000 m/s ² , 6 ms, ½ sine, 3 axes |
| Vibration (system) | Operating | 100 m/s ² maximum @ 55 to 2000 Hz, 3 axes |
| Mass | RTLA30-S | 12.9 g/m |
| | RTLA30 | 12.2 g/m |
| | <i>FASTRACK</i> | 24 g/m |
| Available lengths | RTLA30-S/RTLA30 | 20 mm to 21 m (available in increments of 10 mm) |
| | <i>FASTRACK</i> | 100 mm to 25 m (available in increments of 25 mm) |
| Measuring length | RTLA30-S | See ' RTLA30-S installation drawing ' on page 4 |
| | RTLA30/ <i>FASTRACK</i> | See ' RTLA30/<i>FASTRACK</i> installation drawing ' on page 5 |

For further information on installation and mounting, refer to the *RESOLUTE RTLA30-S absolute linear encoder system* installation guide (Renishaw part no. M-9553-9433) or *RESOLUTE RTLA30 and *FASTRACK* absolute linear encoder system* installation guide (Renishaw part no. M-9553-9134), which are available from the website at www.renishaw.com/resolutedownloads.

Maximum scale lengths


The maximum scale length depends upon the serial interface, readhead resolution and the number of position bits.

The table below shows the maximum scale length for each system:

| Serial interfaces | Position bits | Resolution | | | |
|--------------------------|---------------|------------|--------|---------|--------|
| | | 1 nm | 5 nm | 50 nm | 100 nm |
| BiSS-C (uni-directional) | 26 bit | 67 mm | 336 mm | 3.355 m | - |
| | 32 bit | 4.295 m | 21 m | 21 m | - |
| | 36 bit | 21 m | 21 m | 21 m | - |
| FANUC | 37 bit | 21 m | - | 21 m | - |
| Mitsubishi | 40 bit | 2.1 m | - | 21 m | - |
| Panasonic | 48 bit | 21 m | - | 21 m | 21 m |
| Siemens DRIVE-CLiQ | 28 bit | - | - | 13.42 m | - |
| | 34 bit | 17.18 m | - | - | - |
| Yaskawa | 36 bit | 1.8 m | - | 21 m | - |

RTLA30-S installation drawing



Dimensions and tolerances in mm



For further information on installation, refer to the *RESOLUTE RTLA30-S absolute linear encoder system installation guide* (Renishaw part no. M-9553-9433), which is available from the website at www.renishaw.com/resolutedownloads.

RTLA30/FASTRACK installation drawing

Dimensions and tolerances in mm



- 1 The gap allows for thermal expansion.
- 2 Assumes a 1 mm gap between the scale and the end covers and a zero gap between the FASTRACK carrier and the end covers. The minimum recommended FASTRACK carrier length = 100 mm.
- 3 Only required for sectional installations.

For further information on installation, refer to the *RESOLUTE RTLA30 and FASTRACK absolute linear encoder system installation guide* (Renishaw part no. M-9553-9134), which is available from the website at www.renishaw.com/resolutedownloads.

Scale and *FASTRACK* carrier part numbers

RTLA30-S

Stainless steel tape scale with self-adhesive backing tape.

| Part number | Available lengths | Available in increments of | Ordering instructions |
|-------------|-------------------|----------------------------|---|
| A-9763-xxxx | 20 mm to 21 m | 10 mm | xxxx is the length in cm. Ordering A-9763-0450 for example will result in a length of 4500 mm. |

RTLA30

Stainless steel tape scale for use with the *FASTRACK* carrier.

| Part number | Available lengths | Available in increments of | Ordering instructions |
|-------------|-------------------|----------------------------|---|
| A-9764-xxxx | 20 mm to 21 m | 10 mm | xxxx is the length in cm. Ordering A-9764-0450 for example will result in a length of 4500 mm. |

FASTRACK carrier





Stainless steel carrier for use with the RTLA30 tape scale.

| Part number | Available lengths | Available in increments of | Ordering instructions |
|-------------|-------------------|----------------------------|---|
| A-9704-xxxx | 100 mm to 25 m | 25 mm ¹ | xxxx is the length in cm. Ordering A-9704-0450 for example will result in a length of 4500 mm. |





¹ Part numbers for *FASTRACK* carrier lengths ending in 25 mm are: A-9704-xxx3
 Part numbers for *FASTRACK* carrier lengths ending in 75 mm are: A-9704-xxx8

Scale accessory part numbers

General accessories






| Part description | Part numbers | Product image |
|--|--------------|--|
| Loctite® 435™ adhesive - 20 g bottle For securing the axis datum position | P-AD03-0012 |  |
| Dispensing tip for Loctite® 435™ adhesive | P-TL50-0209 |  |
| Guillotine For cutting RTLA30-S scale, RTLA30 scale, and <i>FASTRACK</i> carrier | A-9589-0071 |  |
| Shears For cutting RTLA30-S scale, RTLA30 scale, and <i>FASTRACK</i> carrier | A-9589-0133 |  |

RTLA30-S accessories

| Part description | Part numbers | Product image |
|---|--------------|---|
| Self-adhesive datum clamp | A-9585-0028 |  |
| 0.8 mm blue setting shim ¹ Used for setting the correct distance (rideheight) between the readhead and the RTLA30-S scale. | M-9517-0122 |  |
| RTLA30-S scale applicator For easy installation of the RTLA30-S scale | A-9589-0095 |  |
| End cover kit | A-9585-0035 |  |

¹ The shim is supplied with the readhead.


RTLA30 and *FASTRACK* accessories

| Part description | Part numbers | Product image |
|--|--------------|---|
| <p>0.6 mm red setting shim ¹ Used for setting the correct distance (rideheight) between the readhead and the <i>FASTRACK</i> carrier.</p> | M-9517-0124 |  |
| <p><i>FASTRACK</i> centre section removal tool Removes centre section of <i>FASTRACK</i> when carrier has been mounted</p> | A-9589-0066 |  |
| <p><i>FASTRACK</i> separator assembly Removes centre section of <i>FASTRACK</i> when carrier has been mounted – includes removable side panels for use when <i>FASTRACK</i> is mounted against a ledge or dowels</p> | A-9589-0122 |  |
| <p>RTLA30 scale pulling tool Aids installation of RTLA30 scale through the <i>FASTRACK</i> carrier</p> | A-9589-0420 |  |
| <p><i>FASTRACK</i> end cover kit</p> | A-9589-0058 |  |



¹ The shim is supplied with the readhead.

Compatible products


RTLA30-S



RTLA30/FASTRACK



RESOLUTE standard readheads



RESOLUTE UHV
(Ultra-high vacuum) readheads



RESOLUTE FS
(Functional Safety) readheads

www.renishaw.com/contact



#renishaw

+44 (0) 1453 524524

 uk@renishaw.com

© 2009–2024 Renishaw plc. All rights reserved. This document may not be copied or reproduced in whole or in part, or transferred to any other media or language by any means, without the prior written permission of Renishaw.

RENISHAW® and the probe symbol are registered trade marks of Renishaw plc. Renishaw product names, designations and the mark 'apply innovation' are trade marks of Renishaw plc or its subsidiaries. BiSS® is a registered trademark of iC-Haus GmbH. DRIVE-CLIQ is a registered trademark of Siemens. Other brand, product or company names are trade marks of their respective owners.

WHILE CONSIDERABLE EFFORT WAS MADE TO VERIFY THE ACCURACY OF THIS DOCUMENT AT PUBLICATION, ALL WARRANTIES, CONDITIONS, REPRESENTATIONS AND LIABILITY, HOWSOEVER ARISING, ARE EXCLUDED TO THE EXTENT PERMITTED BY LAW. RENISHAW RESERVES THE RIGHT TO MAKE CHANGES TO THIS DOCUMENT AND TO THE EQUIPMENT, AND/OR SOFTWARE AND THE SPECIFICATION DESCRIBED HEREIN WITHOUT OBLIGATION TO PROVIDE NOTICE OF SUCH CHANGES.

Renishaw plc. Registered in England and Wales. Company no: 1106260. Registered office: New Mills, Wotton-under-Edge, Glos, GL12 8JR, UK.

Part no.: L-9517-9418-08-A

Issued: 02.2024