



## RMC35 commutation and incremental encoder solution



**The RMC35 is designed for use in motor feedback applications requiring both A, B, Z incremental and U, V, W signals.**

**Robust non-contact OnAxis™ sensor technology provides ultimate long term reliability and with simple installation costs of ownership are minimal.**



Installation is simplified with a range of magnetic actuators and mounting options for the encoder. A simple one time zero position programming then removes the need for careful adjustment of the encoder.

Resolutions are available from 64 to 2,048 pulses per revolution (256 to 8,192 counts per revolution with ×4 evaluation). U, V, W commutation signals are simultaneously output with 1 to 8 pole pairs (2 to 16 poles).

- Incremental resolution from 256 cpr to 8,192 cpr
- Simple installation and setup
- U, V, W commutation signals with up to 16 poles (±24 mA output drive)
- Industry standard incremental outputs (RS422)
- Operating speed to 30,000 rpm
- Compact - 35 mm diameter body
- Non-contact, frictionless design
- Low inertia
- IP40

## Installation drawing

Dimensions and tolerances in mm



Clockwise rotation of magnetic actuator.

### Connector type

Molex 501568-1107

**Mating connector** (Not provided)

Molex 501330-1100 (crimp terminal 501334-xxxx)

## Installation procedure

### 1. Install the magnetic actuator

Use glue to fix the magnetic actuator to the shaft (recommended LOCTITE 648 or LOCTITE 2701). Actuator should protrude by 7 mm.

### 2. Install the flange with the encoder module on the mounting surface


Screw the flange to the mounting surface using 2 screws (not provided).

### 3. Turn the power on

Plug in the mating connector and turn on the power


### 4. Zero the UVW signals

Move the motor to the required zero UVW position. Short together the two zeroing pads.



### 5. Cover the encoder with the metal cover

Place the metal cover over the encoder and gently press it in position. Be sure to align the opening with the connector.




## Product specification

Power supply	5 V $\pm$ 10 %
Power consumption	40 mA (not loaded)
Accuracy	$\pm 0.5^\circ$
Hysteresis	0.17° typ.
Incremental outputs	A, B, Z, A-, B-, Z- (RS422)
Incremental resolution	256, 320, 400, 500, 512, 800, 1,000, 1,024, 1,600, 2,000, 2,048, 4,096, 8,192 cpr
Commutation outputs	U, V, W ( $\pm 24$ mA output drive)
Number of poles for commutation outputs	2, 4, 6, 8, 10, 12, 14, 16
Operating temperature	-40 °C to +105 °C (Limited by connector. All other components used are specified for operation from -40 °C to +125 °C.)
Weight	45 g

Incremental resolution (cpr)	Maximum speed (rpm)
8,192	4,000
4,096	8,000
2,048, 2,000	16,000
1,600	20,000
All other resolutions	30,000

## Connections



### Please note!

For IC output pins 9, 10 and 11 are not connected.


## UVW outputs

Pole	A	Period	Pole pairs*
2	60°	360°	one
4	30°	180°	two
6	20°	120°	three
8	15°	90°	four
10	12°	72°	five
12	10°	60°	six
14	8.57°	51.42°	seven
16	7.50°	45°	eight

\* Number of pole pairs equals number of periods per revolution.


## Timing diagram - Incremental

Complementary signals not shown




B leads A for clockwise rotation of magnet.

## Timing diagram - Commutation for clockwise rotation



## Recommended signal termination

For complementary signals only



## Zero function

The UVW commutation outputs can be zeroed at any angle with a resolution of 0.0879 degrees. The first rising edge on the U signal will be reset at this point of zeroing. The reference impulse of the incremental signals is not changed by this procedure.

Part numbering

**RMC35**

**UA**

**12B**

**AA**

**10**

**Special requirements**  
10 - None (standard)

**Connector type**  
AA - Molex 501568-1107

**Resolution (counts per revolution)**



Decimal		Binary	
D32 - 320	1D0 - 1,000	08B - 256	12B - 4,096
D40 - 400	1D6 - 1,600	09B - 512	13B - 8,192
D50 - 500	2D0 - 2,000	10B - 1,024	
D80 - 800		11B - 2,048	

**Output type**  
IC - Incremental, RS422, 5 V  
Ux - Commutation single ended + incremental with line driver, 5 V

Code	Description	Nr. of poles
UA	one (1) period per revolution	2 poles
UB	two (2) periods per revolution	4 poles
UC	three (3) periods per revolution	6 poles
UD	four (4) periods per revolution	8 poles
UE	five (5) periods per revolution	10 poles
UF	six (6) periods per revolution	12 poles
UG	seven (7) periods per revolution	14 poles
UH	eight (8) periods per revolution	16 poles

Magnetic actuator and magnet part numbering

Actuator for integration onto shaft




Fixing: Glue (recommended – LOCTITE 648 or LOCTITE 2701)

Part number:

For resolutions from 10 bit absolute (800 cpr incremental) and above  
RMA03A3A07 – Ø3 mm shaft

Actuator for integration into shaft




Hole = Ø6G7

Fixing: Glue (recommended – LOCTITE 648 or LOCTITE 2701)

Part numbers:

For resolutions from 10 bit absolute (800 cpr incremental) and above  
RMH06A3A00

Magnet for direct recessing in non-ferrous shafts



Fixing: Glue (recommended – LOCTITE 648 or LOCTITE 2701)

Part numbers:

For resolutions from 10 bit absolute (800 cpr incremental) and above  
RMM44A3A00 (individually packed) – for sample quantities only  
RMM44A3C00 (packed in tubes)

## Accessories part numbering




Cable assembly for connection  
of MOLEX 501330-1100, 12 core

## Cable specifications

<b>Cable specifications</b>	LI12YC12Y
<b>Configuration</b>	12 × 0.14 mm <sup>2</sup>
<b>Sheath color</b>	Grey (RAL7032)
<b>Rated voltage</b>	250 V
<b>Temperature range</b>	Stationary −40 °C to +130 °C Moving −30 °C to +125 °C
<b>Environmental conformation</b>	Conform to RoHS Conform to 73/23/EWG-Guideline CE Halogen free
<b>Chemical resistance</b>	Largely resistant to acids, bases and usual oils. Free from lacquer damaging substances and silicone.

## Dimensions



Part number	Cable length (L)
ACC001	30 cm
ACC002	50 cm
ACC003	100 cm

Pin	Wire color
1	Blue
2	Red
3	Brown
4	White
5	Green
6	Yellow
7	Grey
8	Pink
9	Black
10	Violet
11	Grey/Pink

## Head office

### RLS merilna tehnika d.o.o.

Poslovna cona Žeje pri Komendi  
Pod vrbami 2  
SI-1218 Komenda  
Slovenia

**T** +386 1 5272100

**F** +386 1 5272129

**E** [mail@rls.si](mailto:mail@rls.si)

**www.rls.si**

## Document issues

Issue	Date	Page	Corrections made
1	21. 4. 2011	-	New document
2	22. 1. 2013	1,3	U, V, W specification added
3	11. 2. 2014	3	Resolution and maximum speed table added
4	24. 4. 2015	2	Changed dimensions and tolerances in installation drawing
		3	Pin out comment added for incremental output
		4	Ordering code updated with the incremental option and a new option of LOCTITE glue added
5	3. 12. 2015	1	New image
		3,4	Temperature from +85 °C to +105 °C
6	26. 3. 2018	5	Accessories part numbering added
7	20. 12. 2018	1	IP protection grade added
8	4. 2. 2019	2	Magnet tolerance in installation drawing amended
9	19. 6. 2019	5	Cable configuration amended, wire color table added
10	27. 9. 2021	2	Dimensions drawing amended

This product is not designed or intended for use outside the environmental limitations and operating parameters expressly stated on the product's datasheet. Products are not designed or intended for use in medical, military, aerospace, automotive or oil & gas applications or any safety-critical applications where a failure of the product could cause severe environmental or property damage, personal injury or death. Any use in such applications must be specifically agreed to by seller in writing, and is subject to such additional terms as the seller may impose in its sole discretion. Use of products in such applications is at buyer's own risk, and buyer will indemnify and hold harmless seller and its affiliates against any liability, loss, damage or expense arising from such use. Information contained in this datasheet was derived from product testing under controlled laboratory conditions and data reported thereon is subject to the stated tolerances and variations, or if none are stated, then to tolerances and variations consistent with usual trade practices and testing methods. The product's performance outside of laboratory conditions, including when one or more operating parameters is at its maximum range, may not conform to the product's datasheet. Further, information in the product's datasheet does not reflect the performance of the product in any application, end-use or operating environment buyer or its customer may put the product to. Seller and its affiliates make no recommendation, warranty or representation as to the suitability of the product for buyer's application, use, end-product, process or combination with any other product or as to any results buyer or its customer might obtain in their use of the product. Buyer should use its own knowledge, judgment, expertise and testing in selecting the product for buyer's application, end-use and/or operating environment, and should not rely on any oral or written statement, representation, or samples made by seller or its affiliates for any purpose. EXCEPT FOR THE WARRANTIES EXPRESSLY SET FORTH IN THE SELLER'S TERMS AND CONDITIONS OF SALE, SELLER MAKES NO WARRANTY EXPRESS OR IMPLIED WITH RESPECT TO THE PRODUCT, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR ANY PARTICULAR PURPOSE, WHICH ARE DISCLAIMED AND EXCLUDED. All sales are subject to seller's exclusive terms and conditions of sale which, where the seller is (a) RLS merilna tehnika d.o.o., are available at <https://www.rls.si/customer-service>, (b) Renishaw, Inc., are available at <http://www.renishaw.com/Shop/legal/en/-42186>, or (c) another person, are available on request, and in each case, are incorporated herein by reference, and are the exclusive terms of sale. No other terms and conditions apply. Buyer is not authorized to make any statements or representations that expand upon or extend the environmental limitations and operating parameters of the products, or which imply permitted usage outside of that expressly stated on the datasheet or agreed to in writing by seller.

RLS merilna tehnika d.o.o. has made considerable effort to ensure the content of this document is correct at the date of publication but makes no warranties or representations regarding the content. RLS merilna tehnika d.o.o. excludes liability, howsoever arising, for any inaccuracies in this document. © 2021 RLS d.o.o.