

NC4+ Blue non-contact tool setting range




Specification

Principal application	High-precision, high-speed non-contact tool setting and tool breakage detection on all sizes of vertical and horizontal machining centres, multi-tasking machines and gantry machining centres.	
Transmission type	Hard-wired transmission	
Compatible interfaces	NCi-6, NCSI, NCi-E	
Repeatability	F100 and F100-10	$\pm 0.10 \mu\text{m}$ (4 μin) 2σ
	F115 and F145	$\pm 0.50 \mu\text{m}$ (20 μin) 2σ
	F230 and F300	$\pm 0.75 \mu\text{m}$ (30 μin) 2σ
Tool setting and tool breakage detection (minimum tool or feature size)	F100-10 systems	$\varnothing 5 \mu\text{m}$ (197 μin)
	F100 systems	$\varnothing 15 \mu\text{m}$ (591 μin)
	F115 systems	$\varnothing 30 \mu\text{m}$ (1181 μin)
	F145 systems	$\varnothing 50 \mu\text{m}$ (1968 μin)
	F230 systems	$\varnothing 100 \mu\text{m}$ (3937 μin)
	F300 systems	$\varnothing 200 \mu\text{m}$ (7874 μin)
Output signal (from NCi-6 interface unit)	Two voltage-free, solid-state relays (SSR). Each can be either normally open or normally closed (selectable via a switch). Current (maximum) 50 mA, voltage (maximum) $\pm 50 \text{ V}$. The interface contains an auxiliary relay which can be used for switching the output between the NC4+ Blue and a spindle probe. This relay can also be used to control an air blast solenoid (optional).	
Supply voltage (to interface)	11 Vdc to 30 Vdc	
Supply current (to interface)	120 mA @ 12 Vdc, 70 mA @ 24 Vdc	
Supply protection	Resettable fuses in interface. Reset by removing power and cause of fault.	
Electrical connection arrangement	Systems with connector: Connector socket. Hard-wired systems: Cable on the end of the unit. Other configurations are available on request.	
Cable (to interface)	Specification	$\varnothing 6.0 \text{ mm}$ (0.24 in), two twisted pairs, two individual cores plus screen, each core $18 \times 0.1 \text{ mm}$ insulated.
	Length	12.5 m (41.01 ft)
	Electrical connection	Systems with connector: cable with bayonet-type plug, connector socket on the end of the unit. Hard-wired systems: cable on the end of the unit. Other configurations are available on request.
Barrier air pneumatic supply	Air supply must conform to BS ISO 8573-1: 2010 Class 1.4.2. 6.0 bar (87.02 psi) maximum. Systems with connector: $\varnothing 4.0 \text{ mm}$ (0.16 in) air pipe. Hard-wired systems: $2 \times \varnothing 3.0 \text{ mm}$ (0.12 in) air pipe.	
Air blast pneumatic supply	Air supply must conform to BS ISO 8573-1: 2010 Class 2.9.4. 6.0 bar (87.02 psi) maximum. $\varnothing 6.0 \text{ mm}$ (0.24 in) air pipe.	
Laser type	Class 2 laser product: 1 mW maximum output emitted wavelength 405 nm. WARNING: Laser radiation. Do not stare into beam.	
Laser beam alignment	The unit is supplied with an adjustable mounting plate on the underside.	
Weight (including 12.5 m (41.01 ft) of cable)	1.1 kg (2.43 lb) to 2.0 kg (4.4 lb) depending on configuration.	

Specification (continued)

Environment	For F100 and F100-10 systems: Use M4 (× 3) or M10 (3/8 in) bolts for mounting via the adjuster plate. For F115, F145, F230, and F300 systems: Use M4 (× 3), M10 (3/8 in), or M12 (½ in) bolts for mounting via the adjuster plate. Bolts are not supplied. Other fixing arrangements are available on request.	
	IP rating	IPX5, IPX6, IPX8. BS EN 60529:1992+A2:2013
	Storage temperature	–25 °C to +70 °C (–13 °F to +158 °F)
	Operating temperature	+5 °C to +55 °C (+41 °F to +131 °F)


NC4+ Blue hard-wired system dimensions



Model	Dimensions									
	A	B	C	D	E	F	G	H	ØJ	ØK
F145	85.0 (3.35)	145.0 (5.71)	72.5 (2.85)	31.0 (1.22)	61.0 (2.40)	77.0 (3.03)	20.4 (0.80)	24.5 (0.96)	205.0 (8.07)	147.0 (5.79)
F230	170.0 (6.69)	230.0 (9.06)	115.0 (4.53)	31.0 (1.22)	61.0 (2.40)	77.0 (3.03)	21.3 (0.84)	25.3 (1.00)	652.0 (25.67)	535.0 (21.06)

Dimensions given in mm (in)


NC4+ Blue system with connector dimensions




Model	Dimensions									
	A	B	C	D	E	F	G	H	ØJ	ØK
F100C	40.0 (1.57)	140.0 (5.51)	87.0 (3.43)	31.0 (1.22)	61.0 (2.40)	77.0 (3.03)	18.0 (0.71)	10.9 (0.43)	66.0 (2.60)	44.0 (1.73)
F115C	55.0 (2.17)	155.0 (6.10)	97.3 (3.83)	31.0 (1.22)	61.0 (2.40)	77.0 (3.03)	18.0 (0.71)	13.8 (0.54)	105.0 (4.13)	70.0 (2.76)
F115C-R	55.0 (2.17)	155.0 (6.10)	97.3 (3.83)	50.0 (1.97)	80.0 (3.15)	96.0 (3.78)	35.1 (1.38)	12.3 (0.48)	105.0 (4.13)	70.0 (2.76)
F145C	85.0 (3.35)	185.0 (7.28)	112.3 (4.42)	31.0 (1.22)	61.0 (2.40)	77.0 (3.03)	21.3 (0.84)	25.3 (1.00)	205.0 (8.07)	147.0 (5.79)
F145C-R	85.0 (3.35)	185.0 (7.28)	112.3 (4.42)	50.0 (1.97)	80.0 (3.15)	96.0 (3.78)	37.1 (1.46)	24.7 (0.97)	205.0 (8.07)	147.0 (5.79)
F230C	170.0 (6.69)	270.0 (10.63)	155.0 (6.10)	31.0 (1.22)	61.0 (2.40)	77.0 (3.03)	21.3 (0.84)	25.3 (1.00)	652.0 (25.67)	535.0 (21.06)
F230C-R	170.0 (6.69)	270.0 (10.63)	155.0 (6.10)	50.0 (1.97)	80.0 (3.15)	96.0 (3.78)	40.3 (1.59)	44.3 (1.74)	652.0 (25.67)	535.0 (21.06)
F300C	240.0 (9.45)	340.0 (13.39)	190.0 (7.48)	31.0 (1.22)	61.0 (2.40)	77.0 (3.03)	21.3 (0.84)	25.3 (1.00)	1200.0 (47.24)	1043.0 (41.06)
F300C-R	240.0 (9.45)	340.0 (13.39)	190.0 (7.48)	50.0 (1.97)	80.0 (3.15)	96.0 (3.78)	40.3 (1.59)	44.3 (1.74)	1200.0 (47.24)	1043.0 (41.06)

Dimensions given in mm (in)

NC4+ Blue F100-10C system with connector dimensions



NC4+ Blue bottom exit system dimensions




Model	Dimensions									
	A	B	C	D	E	F	G	H	$\varnothing J$	$\varnothing K$
F145	85.0 (3.35)	145.0 (5.71)	72.5 (2.85)	31.0 (1.22)	61.0 (2.40)	77.0 (3.03)	20.4 (0.80)	24.5 (0.96)	205.0 (8.07)	147.0 (5.79)
F230	170.0 (6.69)	230.0 (9.06)	115.0 (4.53)	31.0 (1.22)	61.0 (2.40)	77.0 (3.03)	21.3 (0.84)	25.3 (1.00)	652.0 (25.67)	535.0 (21.06)


Dimensions given in mm (in)

NC4+ Blue connector dimensions

Straight connector





90° connector





Dimensions given in mm (in)

NC4+ Blue adjuster plates mounting and dimensions

Mounting plate for F100 systems only




Mounting plate for F115, F145, F230 and F300 systems



Dimensions given in mm (in)

Electro-pneumatic integration



Spare parts and accessories

A full range of spare parts and accessories is available; see the *NC4 non-contact tool setting accessories* data sheet (Renishaw part no. H-2000-2223).

www.renishaw.com/contact

 #renishaw

 +44 (0) 1453 524524

 uk@renishaw.com

© 2022-2025 Renishaw plc. All rights reserved. This document may not be copied or reproduced in whole or in part, or transferred to any other media or language by any means, without the prior written permission of Renishaw.
RENISHAW® and the probe symbol are registered trade marks of Renishaw plc. Renishaw product names, designations and the mark 'apply innovation' are trade marks of Renishaw plc or its subsidiaries. Other brand, product or company names are trade marks of their respective owners.
WHILE CONSIDERABLE EFFORT WAS MADE TO VERIFY THE ACCURACY OF THIS DOCUMENT AT PUBLICATION, ALL WARRANTIES, CONDITIONS, REPRESENTATIONS AND LIABILITY, HOWSOEVER ARISING, ARE EXCLUDED TO THE EXTENT PERMITTED BY LAW. RENISHAW RESERVES THE RIGHT TO MAKE CHANGES TO THIS DOCUMENT AND TO THE EQUIPMENT, AND/OR SOFTWARE AND THE SPECIFICATION DESCRIBED HEREIN WITHOUT OBLIGATION TO PROVIDE NOTICE OF SUCH CHANGES.
Renishaw plc. Registered in England and Wales. Company no: 1106260. Registered office: New Mills, Wotton-under-Edge, Glos, GL12 8JR, UK.

Part no.: H-6435-8200-03-A

Issued: 11.2025