

# M8 CMM magnetic and clamping kit with component set A

Renishaw fixture kits including a fixture base plate and set of components




Kit choices		
Kit part no.	Set	Base plate size
R-KC-MC1A-8*	A	13 mm × 300 mm × 300 mm
R-KC-MC2A-8*	A	13 mm × 450 mm × 450 mm
R-KC-MC3A-8*	A	19 mm × 600 mm × 600 mm
R-KC-MC4A-8**	A	19 mm × 750 mm × 750 mm
R-KC-MC5A-8**	A	19 mm × 750 mm × 1020 mm
R-KC-MC6A-8**	A	19 mm × 900 mm × 1200 mm



\* The kit is supplied with a pair of CMM plate clamps.

\*\* For large plates custom bolt holes are recommended to mount the plate to the CMM table. Please provide the make and the machine model when placing an order.



Component set A (R-FSC-MCA-M8) 47 8 components		
Quantity	Part no.	Description
3	R-M-13-8	Ø13 mm × 25 mm magnet
3	R-M-19-8	Ø19 mm × 25 mm magnet
3	R-M-25-8	Ø25 mm × 25 mm magnet
3	R-S-1320-8	Ø13 mm × 20 mm standoff
3	R-S-1325-8	Ø13 mm × 25 mm standoff
3	R-S-1350-8	Ø13 mm × 50 mm standoff
3	R-S-1920-8	Ø19 mm × 20 mm standoff
3	R-S-1925-8	Ø19 mm × 25 mm standoff
3	R-S-1950-8	Ø19 mm × 50 mm standoff
3	R-S-2520-8	Ø25 mm × 20 mm standoff
3	R-S-2525-8	Ø25 mm × 25 mm standoff
3	R-S-2550-8	Ø25 mm × 50 mm standoff
3	R-CT-64-70-8	63.5 mm tension clamp with 68 mm post
4	R-RCD-8	13 mm × 16 mm Delrin® resting cone
1	R-AJ-19-8	Ø19 mm × 37 mm adjustable jackstand
1	R-AS-70-8	70 mm × 10 mm long adjustable slide
1	R-TC-500200	500 mm × 200 mm × 25 mm component tray
1	R-BC10	200 mm × 150 mm × 45 mm compartment box (not shown)