


Parallel shanks for lathe probes



Shanks for OLP40 / OMP40M / RLP40 / RMP40M

- Please quote the part number when ordering equipment.
- Shanks are supplied in a natural finish.
- For taper shanks please refer to data sheet H-2000-2011.
- If you cannot find the shank you require, please contact your local Renishaw company for further information.

Part number	Description	Length A	Length B	Diameter C
A-5625-1000	SHANK KIT 12 mm DIA	21 mm (0.827 in)	35 mm (1.378 in)	Ø 12 mm
A-5625-1001	SHANK KIT 16 mm DIA	13 mm (0.512 in)	40 mm (1.575 in)	Ø 16 mm
A-5625-1002	SHANK KIT 20 mm DIA	13 mm (0.512 in)	50 mm (1.969 in)	Ø 20 mm
A-5625-1003	SHANK KIT 25 mm DIA	13 mm (0.512 in)	60 mm (2.362 in)	Ø 25 mm
A-5625-1004	SHANK KIT 1/2" DIA	21 mm (0.827 in)	35 mm (1.378 in)	Ø 1/2 in
A-5625-1005	SHANK KIT 5/8" DIA	13 mm (0.512 in)	40 mm (1.575 in)	Ø 5/8 in
A-5625-1006	SHANK KIT 3/4" DIA	13 mm (0.512 in)	50 mm (1.969 in)	Ø 3/4 in
A-5625-1007	SHANK KIT 1" DIA	13 mm (0.512 in)	60 mm (2.362 in)	Ø 1 in

A-5625-1003 and A-5625-1007 are the standard shanks available in stock. All other shanks are available with associated lead time.

Renishaw plc
New Mills, Wotton-under-Edge,
Gloucestershire, GL12 8JR
United Kingdom

T +44 (0)1453 524524
F +44 (0)1453 524901
E uk@renishaw.com
www.renishaw.com

RENISHAW 
apply innovation™

**For worldwide contact details, please visit our
main web site at www.renishaw.com/contact**

RENISHAW HAS MADE CONSIDERABLE EFFORTS TO ENSURE THE CONTENT OF THIS DOCUMENT IS CORRECT
AT THE DATE OF PUBLICATION BUT MAKES NO WARRANTIES OR REPRESENTATIONS REGARDING THE CONTENT.
RENISHAW EXCLUDES LIABILITY, HOWSOEVER ARISING, FOR ANY INACCURACIES IN THIS DOCUMENT.



H - 2000 - 2377 - 01