# SAFETY DATA SHEET



## 1. Identification of the substance/preparation and of the company/undertaking

Product name	Castrol Classic GP 50
SDS #	453946
Product Use	Automotive engine crankcase lubricant For specific application advice see appropriate Technical Data Sheet or consult your Castrol representative.
Supplier	Castrol (UK) Ltd Wakefield House Pipers Way Swindon Wiltshire SN3 1RE
EMERGENCY TELEPHONE NUMBER	+44 (0)1793 512712

## 2. Composition/information on ingredients

Highly refined mineral oil (IP 346 DMSO extract < 3%) Proprietary performance additives. This product does not contain any hazardous ingredients at or above regulated thresholds.

### 3. Hazards identification

This preparation is not classified as dangerous according to Directive 1999/45/EC as amended and adapted.

Physical/chemical Hazards	Not classified as dangerous.
Human health hazards	Not classified as dangerous.
Environmental hazards	Unlikely to be harmful to aquatic organisms.
Effects and symptoms	
Eyes	No significant health hazards identified.
Skin	No significant health hazards identified.
	USED ENGINE OILS Used engine oil may contain hazardous components which have the potential to cause skin cancer. See Toxicological Information, section 11 of this Safety Data Sheet.
Inhalation	No significant health hazards identified.
Ingestion	No significant health hazards identified.

### 4. First-aid measures

Eye Contact	In case of contact, immediately flush eyes with a copious amount of water for at least 15 minutes. Get medical attention if irritation occurs.
Skin contact	In case of contact, immediately flush skin with plenty of water. Remove contaminated clothing and shoes. Wash clothing before reuse. Clean shoes thoroughly before reuse. Get medical attention if irritation develops.
Inhalation	If inhaled, remove to fresh air. Get medical attention if symptoms appear.
Ingestion	Do NOT induce vomiting unless directed to do so by medical personnel. Never give anything by mouth to an unconscious person. If large quantities of this material are swallowed, call a physician immediately.
Notes to physician	Treatment should in general be symptomatic and directed to relieving any effects.

### 5. Fire-fighting measures

Breduct Name Ocatral Olassia OD 50			1500.10 00.10	Dama: 4/4
Special fire-fighting procedures	None identified.			
Unusual fire/explosion Hazards	None.			
Hazardous decomposition products	These products are carbon oxides (CO, CO2).			
Not Suitable	Do not use water jet.			
Suitable	In case of fire, use water fog, foam, dry chemical of	r CO2 extinguis	her or spray.	
Extinguishing Media				

 Product Name Castrol Classic GP 50
 Product Code
 453946-GB10
 Page: 1/4

 Version 1
 Date of issue 28 August 2002
 Format United Kingdom (UK)
 Language ENGLISH

 (ENGLISH )

## 6. Accidental release measures

Personal Precautions	Immediately contact emergency personnel. Keep unnecessary personnel away. Use suitable protective equipment (Section 8). Follow all fire fighting procedures (Section 5).
Environmental precautions and cleanup methods	If emergency personnel are unavailable, contain spilled material. For small spills add absorbent (soil may be used in the absence of other suitable materials) scoop up material and place in a sealed, liquid-proof container for disposal. For large spills dike spilled material or otherwise contain material to ensure runoff does not reach a waterway. Place spilled material in an appropriate container for disposal. Minimize contact of spilled material with soils to prevent runoff to surface waterways. See Section 13 for Waste Disposal Information.
Personal Protection in Case of a Large Spill	Splash goggles. Full suit. Boots. Gloves.

# 7. Handling and storage

Handling	Wash thoroughly after handling.
Storage	Keep container tightly closed. Keep container in a cool, well-ventilated area.

# 8. Exposure controls/personal protection

<b>Occupational Exposure Limits</b>	None assigned.
Control Measures	Provide exhaust ventilation or other engineering controls to keep the airborne concentrations of vapours below their respective occupational exposure limits. Ensure that eyewash stations and safety showers are close to the workstation location.
Hygiene measures	Wash hands after handling compounds and before eating, smoking, using lavatory, and at the end of day.
Personal protective equipment	
Respiratory system	Use with adequate ventilation.
Skin and body	Avoid contact with skin. Wear clothing and footwear that cannot be penetrated by chemicals or o
Hands	Wear gloves that cannot be penetrated by chemicals or oil.
Eyes	Safety glasses with side shields.

# 9. Physical and chemical properties

Autoignition temperature	>250 °C
Flash point	>200 °C (CLOSED CUP)
Pour Point	-9 °C
Colour	Amber.
Odour	Mild
Odour threshold	Not available.
Physical state	Liquid.
Boiling point / range	>250 °C
Density	<1 g/cm³ at 20 °C
Solubility	insoluble in water.
Viscosity	kinematic at 40°C: 220 cSt kinematic: 19 cSt at 100°C

# 10. Stability and reactivity

Incompatibility with Various	Reactive with oxidizing agents.
Substances	
Hazardous Polymerization	Will not occur.

# 11. Toxicological information

Acute toxicity	Unlikely to cause more than	transient stinging or redness if accider	ntal eye contact occ	curs.
	Unlikely to cause harm to the lead to dermatitis.	skin on brief or occasional contact but	t prolonged or repea	ated exposure may
		g from the operation of internal combu may contain hazardous components v		
Product Name Cast	trol Classic GP 50	Product Code	453946-GB10	Page: 2/4
Version 1	Date of issue 28 August 2002	Format United Kingdom (UK)	Langua	age ENGLISH
				(ENGLISH)

cancer. Frequent or prolonged contact with all types and makes of used engine oil must therefore be<br/>avoided and a high standard of personal hygiene maintained.Unlikely to cause harm if accidentally swallowed in small doses, though larger quantities may cause nausea<br/>and diarrhoea.At normal ambient temperatures this product will be unlikely to present an inhalation hazard because of its<br/>low volatility. May be harmful by inhalation if exposure to vapour, mists or fumes resulting from thermal<br/>decomposition products occurs.Chronic toxicity<br/>Carcinogenic effectsNo component of this product at levels greater than 0.1% is identified as a carcinogen by ACGIH, the<br/>International Agency for Research on Cancer (IARC) or the European Commission (EC).

### 12. Ecological information

Persistence/degradability	Inherently biodegradable
Mobility	Spillages may penetrate the soil causing ground water contamination.
<b>Bioaccumulative potential</b>	This product is not expected to bioaccumulate through food chains in the environment.
Environmental hazards	Unlikely to be harmful to aquatic organisms.
Other Ecological Information	Spills may form a film on water surfaces causing physical damage to organisms. Oxygen transfer could also be impaired.

#### 13. Disposal considerations

Disposal Consideration / Waste information Where possible, arrange for product to be recycled.Dispose of via an authorised person/licensed waste disposal contractor in accordance with local regulations.Incineration may be carried out under controlled conditions provided that local regulations for emissions are met.

### 14. Transport information

Not classified as hazardous for transport (ADR, RID, UN, IMO, IATA/ICAO).

### 15. Regulatory information

Label Requirements	
Risk Phrases	This product is not classified according to the EU regulations.
Restrictions to product use	Classification and labeling have been performed according to EU directives 1999/45/EC and 67/548/EEC as amended and adapted. - Industrial applications.
Other Regulations	
Inventories	AUSTRALIAN INVENTORY (AICS): In compliance
	CANADA INVENTORY (DSL): In compliance.
	CHINA INVENTORY (IECS): Not determined.
	EC INVENTORY (EINECS): In compliance.
	JAPAN INVENTORY (ENCS): Not listed.
	KOREA INVENTORY (ECL): In compliance.
	PHILIPPINE INVENTORY (PICCS): In compliance.
	US INVENTORY (TSCA): In compliance.

### 16. Other information

#### **HISTORY**

Date of issue Date of previous issue Prepared by <u>Notice to Reader</u> 28/08/2002. No Previous Validation. Product Stewardship Group

Version 1

Product Code 453946-GB10

Language ENGLISH

The data and advice given apply when the product is sold for the stated application or applications. The product is not sold as suitable for any other application. Use of the product for applications other than as stated in this sheet may give rise to risks not mentioned in this sheet. You should not use the product other than for the stated application or applications without seeking advice from us.

If you have purchased the product for supply to a third party for use at work, it is your duty to take all necessary steps to secure that any person handling or using the product is provided with the information in this sheet.

If you are an employer, it is your duty to tell your employees and others who may be affected of any hazards described in this sheet and of any precautions which should be taken

#### Further copies of this Safety Data Sheet may be obtained from Castrol International.

Product Name Castrol Classic GP 50		Product Code	453946-GB10	Page: 4/4
Version 1	Date of issue 28 August 2002	Format United Kingdom (UK)	Language	
			( )	