

Stainless steel 17-4PH (1.4542)

Parameter set options

Layer thickness	Optimised for	Laser mode	Page
60 µm	Single laser per part	Continuous wave	4

To download the latest material files, visit www.renishaw.com/softwarelicensing.

Material description

Stainless steel 17-4PH (DIN/W.Nr 1.4542) is a martensitic, precipitation-hardening stainless steel that comprises of iron alloyed with chromium, nickel, copper and other minor elements.

The excellent specific strength and good corrosion-resistant properties of 17-4PH have resulted in its use across a wide range of industries and applications, such as engine components, petrochemical equipment, and food processing.

Material properties

- High toughness
- High corrosion resistance
- Excellent specific strength
- Good machinability

Applications

- Surgical tools
- Aerospace
- Chemical processing
- Nuclear
- General engineering

Disclaimer

The mechanical property data featured in this document were obtained from tests performed in Renishaw's laboratories and they indicate the mechanical properties that can be achieved. The data is not intended as a guaranteed minimum specification.

Glossary of terms

Term	Definition
Scan strategy	Determines the path the laser will take to melt the cross-sectional area of the parts featured in each layer of the build process.
Meander	A scan strategy that takes the form of a straight-line vector path that bounces back and forth from each side of the part border. Meander strategy is quick and ideal for parts with a small XY cross section.
Stripe	A scan strategy where the area within the part border is split into strips and a meander technique is used within each strip. Stripe is ideal for parts with a large XY cross section.

Typical wrought material properties

Material property	Wrought material value
Density	7.8 g/cm ³
Thermal conductivity	18 W/mK to 23 W/mK
Melting temperature	1 404 °C to 1 440 °C
Coefficient of thermal expansion ¹	11×10 ⁻⁶ K ⁻¹

¹ In the range of 21 °C to 427 °C.

Recommended composition of powder

Element	Mass (%)
Iron	Balance
Chromium	15.00 to 17.50
Nickel	3.00 to 5.00
Copper	3.00 to 5.00
Silicon	≤ 1.00
Manganese	≤ 1.00
Nitrogen	≤ 0.25
Oxygen	≤ 0.20
Carbon	≤ 0.07
Phosphorus	≤ 0.04
Sulphur	≤ 0.03

Recommended powder size distribution: 15 µm to 45 µm.

The values shown in this table are for ASTM standard composition powder. Renishaw powders are supplied to a tighter specification to minimise batch-to-batch variations. Results quoted in this data sheet are from samples produced using Renishaw's tighter-specification powder. To purchase powder from Renishaw, visit the online store at www.renishaw.com/shop.

Please contact Renishaw for further information about specifications or if you require support in qualifying non-Renishaw powders.

Parameter set summary

Layer thickness	Optimised for	Laser mode	Gas flow rate	Build rate	
60 µm	Single laser per part	Continuous wave	190 m ³ /h	One laser: 19.3 cm ³ /h	Four lasers: 77.1 cm ³ /h

Material files: SS17-4PH_500QS_B60_M_01_B (meander scan strategy)
SS17-4PH_500QS_B60_S_01_B (stripe scan strategy)

Properties of additively manufactured components

NOTE: This parameter set is optimised for bulk density. The material properties in this table are indicative only. Further modification of the material file may be required to suit your application.

		Solution treated and precipitation hardened ¹
Bulk density ²		≥ 99.8%
Ultimate tensile strength ³	Horizontal (XY)	1 119 MPa ±4 MPa
	Vertical (Z)	1 299 MPa ±9 MPa
Yield strength ³	Horizontal (XY)	893 MPa ±18 MPa
	Vertical (Z)	1 046 MPa ±14 MPa
Elongation after fracture ³	Horizontal (XY)	17% ±1%
	Vertical (Z)	17% ±1%
Modulus of elasticity ³	Horizontal (XY)	164 GPa ±12 GPa
	Vertical (Z)	180 GPa ±8 GPa
Hardness (Vickers) ⁴	Horizontal (XY)	440 HV0.5 ±11 HV0.5
Surface roughness ⁵	Vertical (Z) (Median Ra)	10 µm ±2 µm

Mechanical test samples were created using four lasers, one laser per sample and with no downstream processing. Meander scan strategy was used for vertical samples. Stripe scan strategy was used for horizontal samples.

- ¹ Solution treatment and precipitation hardening method used for testing: Under vacuum, heat at 13 °C/min to 1 040 °C ±10 °C, then hold temperature for 30 min. Gas quench with argon at 1 bar to room temperature. Under vacuum, heat at 13 °C/min to 480 °C ±10 °C, then hold temperature for 1 hour. Gas quench with argon at 1 bar to room temperature.
- ² Measured optically on 10 mm × 10 mm × 10 mm samples at 75× magnification.
- ³ Tested at ambient temperature to ASTM E8. Machined prior to testing. Values based on 32 samples for vertical and 16 for horizontal.
- ⁴ Tested to ASTM E384-11 after polishing.
- ⁵ Tested on as-built vertical surfaces using laser interferometry. Tested to JIS B 0601 2001 (ISO 4287:1997).

This page is intentionally left blank.

www.renishaw.com/additivemanufacturing



#renishaw



+44 (0) 1453 524524



uk@renishaw.com

© 2000–2024 Renishaw plc. All rights reserved. This document may not be copied or reproduced in whole or in part, or transferred to any other media or language by any means, without the prior written permission of Renishaw.

RENISHAW® and the probe symbol are registered trade marks of Renishaw plc. Renishaw product names, designations and the mark 'apply innovation' are trade marks of Renishaw plc or its subsidiaries. Other brand, product or company names are trade marks of their respective owners.

WHILE CONSIDERABLE EFFORT WAS MADE TO VERIFY THE ACCURACY OF THIS DOCUMENT AT PUBLICATION, ALL WARRANTIES, CONDITIONS, REPRESENTATIONS AND LIABILITY, HOWSOEVER ARISING, ARE EXCLUDED TO THE EXTENT PERMITTED BY LAW. RENISHAW RESERVES THE RIGHT TO MAKE CHANGES TO THIS DOCUMENT AND TO THE EQUIPMENT, AND/OR SOFTWARE AND THE SPECIFICATION DESCRIBED HEREIN WITHOUT OBLIGATION TO PROVIDE NOTICE OF SUCH CHANGES.

Renishaw plc. Registered in England and Wales. Company no: 1106260. Registered office: New Mills, Wotton-under-Edge, Glos, GL12 8JR, UK.

Part no.: H-5800-6832-02-A

Issued: 08.2024