

# Controller requirements: SupaScan

## Fanuc Series 0–3*x**i*

The information within this document provides the minimum recommended controller requirements to enable use of the SupaScan system on a machining centre with a Fanuc Series 0–3*x**i* controller.

---

**NOTE:** Part numbers and descriptions within this document relating to items provided by organisations other than Renishaw are provided for information only. Whilst every effort has been made to ensure these are accurate, contact the machine tool builder, controller OEM or distributor for confirmation before purchasing.

---



## Fanuc Series 0–21*i* MODEL A

Controller option	Option number
High-speed serial bus (HSSB) extended driver library option	A02B-0207-J900 <sup>1</sup>
1 × Ethernet port	
3 × pairs of latched M-codes (high-speed digital outputs)	
1 × skip (high-speed or standard)	A02B-03xx-J848 <sup>2</sup>
'Macro B' user macro option	
Custom macro option (common variables)	
<b>OPTIONAL</b>	
Interruption type custom macro (UINT) (for overtravel protection)	A02B-03xx-J874 <sup>2</sup>


## Fanuc Series 30–32*i* MODEL A, Series 0–3x*i* MODEL B

Controller option	Option number
1 × Ethernet port	
3 × pairs of high speed M-codes / digital outputs	
1 × skip (high-speed or standard)	A02B-03xx-J848 <sup>2</sup>
'Macro B' user macro option	
Custom macro option (common variables)	
<b>OPTIONAL</b>	
Interruption type custom macro (UINT) (for overtravel protection)	A02B-03xx-J874 <sup>2</sup>

<sup>1</sup> A HSSB card is not required with this software option.

<sup>2</sup> Contact Fanuc for further information and the appropriate option number.

## Output signal requirements



Any increase in these values will impact negatively on cycle times and may prevent the system working reliably.

The 3 × pairs of latched M-codes (high-speed digital outputs) should be reset when Reset is pressed on the CNC machine tool.

The output/input signal level change must be from 0 V to between 5 V and 30 V.

Use of solid-state relays is recommended as issues can arise from noise on mechanical relay contacts (contact debounce time of 20 ms maximum).

[www.renishaw.com/supascan](http://www.renishaw.com/supascan)

#renishaw

+44 (0) 1453 524524

uk@renishaw.com

© 2016–2022 Renishaw plc. All rights reserved. This document may not be copied or reproduced in whole or in part, or transferred to any other media or language by any means, without the prior written permission of Renishaw.

RENISHAW® and the probe symbol are registered trade marks of Renishaw plc. Renishaw product names, designations and the mark 'apply innovation' are trade marks of Renishaw plc or its subsidiaries. Other brand, product or company names are trade marks of their respective owners.

WHILE CONSIDERABLE EFFORT WAS MADE TO VERIFY THE ACCURACY OF THIS DOCUMENT AT PUBLICATION, ALL WARRANTIES, CONDITIONS, REPRESENTATIONS AND LIABILITY, HOWSOEVER ARISING, ARE EXCLUDED TO THE EXTENT PERMITTED BY LAW. RENISHAW RESERVES THE RIGHT TO MAKE CHANGES TO THIS DOCUMENT AND TO THE EQUIPMENT, AND/OR SOFTWARE AND THE SPECIFICATION DESCRIBED HEREIN WITHOUT OBLIGATION TO PROVIDE NOTICE OF SUCH CHANGES.

Renishaw plc. Registered in England and Wales. Company no: 1106260. Registered office: New Mills, Wotton-under-Edge, Glos, GL12 8JR, UK.

Part no.: H-5465-8531-03-B

Issued: 08.2022