




America

CERTIFICATE

No. U8 061100 0066 Rev. 00

Holder of Certificate: Renishaw PLC
New Mills
Wotton under Edge, Gloucestershire GL12 8JR
UNITED KINGDOM

Certification Mark:



Product: Metal working and finishing machines
Laser melting machine for additive
manufacturing in metals

Brand Name: Renishaw

Model(s): RenAM 500x, RenAM 500x-Flex, RenAM 500x-MV,
RenAM 500x-MV-Flex

Parameters:

- where "x" may be S, D, T, or Q, denoting Single, Double, Triple, or Quadruple laser versions	
Rated Voltage:	380-480V, 3ph
Rated Frequency:	50-60Hz
Rated Current:	50A
Protection Class:	Class I
Rated Operating Ambient:	18-22°C

Tested according to: UL 508A:2018/R2020-08
CAN/CSA C22.2 No. 14-2018

This product was voluntarily tested to the relevant safety requirements referenced on this certificate. It can be marked with the certification mark above. The mark must not be altered in any way. This product certification system operated by TÜV SÜD America Inc. most closely resembles system 3 as defined in ISO/IEC 17067. Certification is based on the TÜV SÜD "Testing and Certification Regulations". TÜV SÜD America Inc. is an OSHA recognized NRTL and a Standards Council of Canada accredited Certification body.

Test report no.: 071-75951967T-000

Date, 2021-11-26

(David Guyett-Smith)