

TUV SUD TUV SUD TUV SUD TUV SUD TUV SUD TUV SUD TUV SUD TUV SUD TUV SUD TUV SUD TUV SUD TUV SUD TUV SUD TUV SUD TUV SUD  
ZERTIFIKAT ◆ CERTIFICATE ◆ CERTIFICADO ◆ CERTIFICAT ◆ 認證證書 ◆ CERTIFICATE ◆ CERTIFICATE




America

# CERTIFICATE

No. U8 061100 0048 Rev. 00

**Holder of Certificate:** **Renishaw PLC**  
New Mills  
Wotton under Edge, Gloucestershire GL12 8JR  
UNITED KINGDOM

**Production Facility(ies):** 084666  
**Certification Mark:**



**Product:** **Metal working and finishing machines**  
**Brand Name:** **Renishaw**  
**Model(s):** **RenAM 500M, RenAM 500MV**  
**Parameters:**

Rated Voltage: 220-240V  
Rated Frequency: 50-60Hz  
Rated Current: 25A  
Protection Class: Class I  
Degree of Protection: IP22  
Maximum Ambient Temp: 22°C  
Laser: Class: 4 Wavelength: 1070nm  
Output Power: 500W  
Remarks: Laser is enclosed resulting in a class 1 product.  
CAN/CSA C22.2 No. 14:2013  
UL 508A:2013

**Tested according to:**

The product was voluntarily tested according to the relevant safety requirements noted above. It can be marked with the certification mark above. The mark must not be altered in any way. This product certification system operated by TÜV SÜD America Inc. most closely resembles system 3 as defined in ISO/IEC 17067. Certification is based on the TÜV SÜD "Testing and Certification Regulations". TÜV SÜD America Inc. is an OSHA recognized NRTL and a Standards Council of Canada accredited certification body.

**Test report no.:** 071-75943419T-000

**Date,** 2018-08-06

( David Guyett-Smith )