

39 mm vacuum chamber window



The Renishaw RLE fibre optic laser encoder uses interferometry to provide high resolution, linear position feedback.

The differential interferometer head (RLD10-X3-DI) is designed to mount onto the vacuum chamber wall. A vacuum chamber window then allows the laser beams to pass between the detector head and the measurement mirror. Vacuum chamber windows can also be used with other interferometer head variants where the RLD is required to measure within a vacuum chamber, such as RVI20 vacuum compatible interferometer.

Renishaw's 39 mm vacuum chamber window has been manufactured to a custom specification to maximise the performance of the RLE system.

Mounting recommendations

Renishaw recommends the following when mounting the chamber window within the chamber wall.


- The window must not be mounted under tension which could cause the window to distort and the beam to deviate from the nominal.
- An O-ring must be used on at least one side of the chamber window to create and maintain a seal in the vacuum chamber wall.

39 mm vacuum chamber window specification

Incident beam	Angle of incidence	Normal $\pm 5^\circ$
Operating environment	Temperature	0 °C to 40 °C
	Relative humidity	0% to 95% non-condensing
	Vacuum	Suitable up to: $\times 10^{-7}$ Torr
Storage environment	Temperature	-20 °C to 200 °C

General dimensions

Dimensions in mm



www.renishaw.com/contact



#renishaw

+44 (0) 1453 524524

uk@renishaw.com

© 2019–2026 Renishaw plc. All rights reserved. This document may not be copied or reproduced in whole or in part, or transferred to any other media or language by any means, without the prior written permission of Renishaw.

RENISHAW® and the probe symbol are registered trade marks of Renishaw plc. Renishaw product names, designations and the mark 'apply innovation' are trade marks of Renishaw plc or its subsidiaries. Other brand, product or company names are trade marks of their respective owners.

WHILE CONSIDERABLE EFFORT WAS MADE TO VERIFY THE ACCURACY OF THIS DOCUMENT AT PUBLICATION, ALL WARRANTIES, CONDITIONS, REPRESENTATIONS AND LIABILITY, HOWSOEVER ARISING, ARE EXCLUDED TO THE EXTENT PERMITTED BY LAW. RENISHAW RESERVES THE RIGHT TO MAKE CHANGES TO THIS DOCUMENT AND TO THE EQUIPMENT, AND/OR SOFTWARE AND THE SPECIFICATION DESCRIBED HEREIN WITHOUT OBLIGATION TO PROVIDE NOTICE OF SUCH CHANGES.

Renishaw plc. Registered in England and Wales. Company no: 1106260. Registered office: New Mills, Wotton-under-Edge, Glos, GL12 8JR, UK.

Part no.: L-9904-2479-03-A

Issued: 07.2026