New Mills, Wotton-under-Edge, Gloucestershire GL12 8JR United Kingdom T +44 (0)1453 524524 F +44 (0)1453 524901 E uk@renishaw.com

www.renishaw.com



PH10M-iQ PLUS

Less time calibrating, more time measuring

PH10M-iQ PLUS offers all the benefits of a traditional PH10M PLUS but with the addition of inferred qualification. This further demonstrates Renishaw's commitment to continuous product development.

PH10M-iQ PLUS increases throughput by removing the need to qualify each head position that is used. This allows more time to be spent measuring.

Following an initial head localisation, a simple qualification procedure of as few as three positions allows the user to operate PH10M-iQ PLUS in every orientation possible without requalifying.



Innovations

Two heads in one

PH10M-iQ PLUS provides all the functionality of Renishaw's industry standard PH10M PLUS but with the addition of inferred qualification for touch-trigger probing routines.

Where an application or specific angle demands ultimate touch-trigger accuracy then PH10M-iQ PLUS can be qualified in the same way as a standard PH10M PLUS.

Fine tune your performance

PH10M-iQ PLUS must perform a simple qualification procedure before inferred mode can be used, after which any head position can be used for measurement without having to requalify.

Depending on your metrology requirements you can optimise the accuracy of your system by increasing the number of qualification positions during probe qualification.

Machine type	Mounting orientation	Qualification positions	<i>P</i> ьт - Typical positional span*
		3	95 µm
		8	125 μm
		12	80 μm
		18	65 μm
		3	15 μm

Horizontal arm machine specification

Using a PAA3 300 mm extension bar, standard force TP20 module, 10 mm x 4 mm diameter stylus on a machine with the following specification;

MPEe = \pm (9 + L / 100) μ m (L in mm) ISO 10360-2 (2009)

Bridge machine specification

Using a PAA1 adaptor, standard force TP20 module, 10 mm x 4 mm diameter stylus on a machine with the following specification;

MPEe = \pm (1 + L / 750) μ m (L in mm) ISO 10360-2 (2009)


*Positional span of sphere location (P_{LTI}) evaluated as per ISO 10360-5 (2010) but covering all 720 head positions




Compatibility

Renishaw's complete range of PH10M PLUS compatible probes are also compatible with PH10M-iQ PLUS. However, the added functionality of inferred qualification can only be used with touch-trigger probes.

TP20, TP2-5W, TP200, TP6, TP6A and TP7M touch-trigger probes can be used in traditional PH10 mode or can utilise inferred qualification; whereas SP25M and SP600M scanning probes can only be used in traditional PH10 mode and cannot utilise inferred qualification.





Specification

Head	PH10M-iQ PLUS		
Length	117 mm (4.60 in)		
Width	62 mm (2.44 in)		
Weight	645 g (22.07 oz)		
Mounting	Shank		
Probe mount	Renishaw Autojoint (multiwire) M8 threaded probes can be used with a PAA probe adaptor		
Controller	PHC10-3 PLUS		
Repeatability	$0.4~\mu m$ (2 σ 0.00002 in) specified at a distance of 62 mm (2.44 in) from the A-axis centre of rotation		
Angular movement	A-axis 0° to 105° in 7.5° steps B-axis -180° to 180° in 7.5° steps		
Total number of positions	720 positions		
Maximum drive output torque	0.45 Nm		
Maximum extension bar	300 mm (11.8 in) using PAA3 probe adaptor 450 mm (17.7 in) using PAACF special order only extension	300 mm (11.8 in) using PEL4 extension	
Temperature range Operating Storage	10 °C to 40 °C (50 °F to 104 °F) -10 °C to 70 °C (14 °F to 158 °F)		
Head control unit	HCU1 or MCUlite-2, MCU5 or MCU W		
Warranty	2 years		

For worldwide contact details, please visit our main website at www.renishaw.com/contact

RENISHAW HAS MADE CONSIDERABLE EFFORTS TO ENSURE THE CONTENT OF THIS DOCUMENT IS CORRECT AT THE DATE OF PUBLICATION BUT MAKES NO WARRANTIES OR REPRESENTATIONS REGARDING THE CONTENT. RENISHAW EXCLUDES LIABILITY, HOWSOEVER ARISING, FOR ANY INACCURACIES IN THIS DOCUMENT.

RENISHAW® and the probe emblem used in the RENISHAW logo are registered trademarks of Renishaw plc in the UK and other countries. **apply innovation** is a trademark of Renishaw plc.

© 2009 - 2013 Renishaw plc All rights reserved Issued 1013 Part no. H-1000-1272-02-A