# **SAFETY DATA SHEET** PTFE/SILICONE LUBRICANT 569-256-0001

RS REACH MSDS Date 01/01/08

# 1 IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND COMPANY/UNDERTAKING

PRODUCT NAME PTFE/SILICONE LUBRICANT 569-256-0001

PRODUCT NO.

Supplier: RS Components Ltd.

Birchington Road, Corby, Northants, NN17 9RS,

Tel: +44 (0) 1536 402888 (8am to 8pm)

Fax: +44 (0) 1536 401588

technical.help@rs-components.com Fmail:

#### **2 HAZARDS IDENTIFICATION**

Extremely flammable. Vapours may cause drowsiness and dizziness. Irritating to skin. Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

CLASSIFICATION Xi;R38. F+;R12. N;R51/53. R67.

# **3 COMPOSITION/INFORMATION ON INGREDIENTS**

Name	EC No.	CAS-No.	Content	Classification
BUTANE	203-448-7	106-97-8	10-30%	F+;R12
ISOBUTANE	200-857-2	75-28-5	5-10%	F+;R12
NAPHTHA (PETROLEUM) , HYDROTREATED LIGHT	265-151-9	64742-49-0	30-60%	Xn;R65. Xi;R38. F;R11. N;R51/53. R67.
PROPANE	200-827-9	74-98-6	10-30%	F+;R12

The Full Text for all R-Phrases are Displayed in Section 16

# **4 FIRST-AID MEASURES**

# **GENERAL INFORMATION**

Move the exposed person to fresh air at once. Get medical attention if any discomfort continues.

#### INHALATION

Move the exposed person to fresh air at once. When breathing is difficult, properly trained personnel may assist affected person by administering oxygen. Keep the affected person warm and at rest. Get prompt medical attention.

DO NOT INDUCE VOMITING! Rinse mouth thoroughly with water and give large amounts of milk or water to people not unconscious. Get medical attention if any discomfort continues.

SKIN CONTACT

Wash the skin immediately with soap and water. Get medical attention if any discomfort continues.

# **FYF CONTACT**

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes. Get medical attention if any discomfort continues.

# **5 FIRE-FIGHTING MEASURES**

#### **EXTINGUISHING MEDIA**

Use: Powder. Dry chemicals, sand, dolomite etc. Water spray, fog or mist.

SPECIAL FIRE FIGHTING PROCEDURES

Containers close to fire should be removed or cooled with water. Use water to keep fire exposed containers cool and disperse vapours.

**UNUSUAL FIRE & EXPLOSION HAZARDS** 

Aerosol cans may explode in a fire.

# **6 ACCIDENTAL RELEASE MEASURES**

# SPILL CLEAN UP METHODS

Wear necessary protective equipment. Extinguish all ignition sources. Avoid sparks, flames, heat and smoking. Ventilate. Let evaporate. Keep out of confined spaces because of explosion risk. If leakage cannot be stopped, evacuate area.

# **7 HANDLING AND STORAGE**

**REVISION DATE: 13/12/2007** 

# PTFE/SILICONE LUBRICANT 569-256-0001

# **USAGE PRECAUTIONS**

Keep away from heat, sparks and open flame. Avoid spilling, skin and eye contact. Ventilate well, avoid breathing vapours. Use approved respirator if air contamination is above accepted level.

STORAGE PRECAUTIONS

Aerosol cans: Must not be exposed to direct sunlight or temperatures above 50°C.

#### 8 EXPOSURE CONTROLS/PERSONAL PROTECTION

Name	Std	LT - ppm	LT - mg/m3	ST - ppm	ST - mg/m3
BUTANE	WEL	600 ppm	1450 mg/m3	750 ppm	1810 mg/m3
ISOBUTANE	WEL	800 ppm		800 ppm	
NAPHTHA (PETROLEUM) , HYDROTREATED LIGHT			1200 mg/m3		
PROPANE		Asphyxiating	Asphyxiating	Asphyxiating	Asphyxiating

**INGREDIENT COMMENTS** 

WEL = Workplace Exposure Limits

PROTECTIVE EQUIPMENT





#### **ENGINEERING MEASURES**

Provide adequate general and local exhaust ventilation.

#### RESPIRATORY EQUIPMENT

No specific recommendation made, but respiratory protection must be used if the general level exceeds the Recommended Workplace Exposure Limit. Use chemical cartridge protection with appropriate cartridge.

HAND PROTECTION

Use protective gloves.

#### **EYE PROTECTION**

Use approved safety goggles or face shield.

#### OTHER PROTECTION

Wear appropriate clothing to prevent any possibility of liquid contact and repeated or prolonged vapour contact.

#### HYGIENE MEASURES

DO NOT SMOKE IN WORK AREA! Wash at the end of each work shift and before eating, smoking and using the toilet. Promptly remove any clothing that becomes contaminated. When using do not eat, drink or smoke.

# 9 PHYSICAL AND CHEMICAL PROPERTIES

APPEARANCE Aerosol

COLOUR Light (or pale)

ODOUR Characteristic

SOLUBILITY Insoluble in water

FLAMMABILITY LIMIT - LOWER(%) 0.8 FLAMMABILITY LIMIT - UPPER(%) 9.

# 10 STABILITY AND REACTIVITY

#### **STABILITY**

Stable under normal temperature conditions.

#### CONDITIONS TO AVOID

Avoid heat, flames and other sources of ignition. Avoid contact with: Strong oxidising agents. Strong alkalis. Strong mineral acids.

# HAZARDOUS DECOMPOSITION PRODUCTS

Fire creates: Vapours/gases/fumes of: Carbon monoxide (CO). Carbon dioxide (CO2).

# 11 TOXICOLOGICAL INFORMATION

#### INHALATION

May cause irritation to the respiratory system. Vapours may cause headache, fatigue, dizziness and nausea. Prolonged inhalation of high concentrations may damage respiratory system. Irritating to respiratory system.

**REVISION DATE: 13/12/2007** 

# PTFE/SILICONE LUBRICANT 569-256-0001

#### INGESTION

May cause discomfort if swallowed. May cause stomach pain or vomiting. Gastrointestinal symptoms, including upset stomach.

#### SKIN CONTACT

Prolonged or repeated exposure may cause severe irritation. Acts as a defatting agent on skin. May cause cracking of skin, and eczema. May cause allergic contact eczema. May cause sensitisation by skin contact. Irritating to skin.

#### **EYE CONTACT**

Irritating to eyes. May cause chemical eye burns.

#### **ROUTE OF ENTRY**

Inhalation. Skin and/or eye contact.

# 12 ECOLOGICAL INFORMATION

#### **ECOTOXICITY**

Dangerous for the environment if discharged into watercourses.

# 13 DISPOSAL CONSIDERATIONS

#### **DISPOSAL METHODS**

Empty containers must not be burned because of explosion hazard. Dispose of waste and residues in accordance with local authority requirements.

#### 14 TRANSPORT INFORMATION



UK ROAD CLASS 2

PROPER SHIPPING NAME AEROSOLS

UN NO. ROAD 1950 UK ROAD PACK GR. N/A

ADR CLASS NO. 2 ADR CLASS Class 2: Gases

ADR PACK GROUP N/A ADR LABEL NO. 2.1
CEFIC TEC(R) NO. 20G5F RID CLASS NO. 2
RID PACK GROUP N/A UN NO. SEA 1950

IMDG CLASS IMDG PACK GR. Not Applicable 2.1 **EMS** F-D, S-U MFAG See Guide MARINE POLLUTANT UN NO. AIR 1950 Nο AIR CLASS AIR PACK GR. N/A 2.1

# **15 REGULATORY INFORMATION**

# **LABELLING**







Irritant

Extremely Flammable

Dangerous for the environment

# RISK PHRASES

R12 Extremely flammable.

R38 Irritating to skin.

R51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic

environment.

R67 Vapours may cause drowsiness and dizziness.

#### SAFETY PHRASES

S2 Keep out of the reach of children

S16 Keep away from sources of ignition - No smoking.

# PTFE/SILICONE LUBRICANT 569-256-0001

S21	When using do not smoke.
S23	Do not breathe vapour/spray.
S24	Avoid contact with skin.
S51	Use only in well-ventilated areas.
S60	This material and its container must be disposed of as hazardous waste.

#### **UK REGULATORY REFERENCES**

The Chemicals (Hazard Information and Packaging for Supply) Regulations 2002.

The Control of Substances Hazardous to Health Regulations 2002.

#### STATUTORY INSTRUMENTS

The Control of Substances Hazardous to Health Regulations 2002.

The Chemicals (Hazard Information and Packaging for Supply) Regulations 2002.

#### APPROVED CODE OF PRACTICE

Classification and Labelling of Substances and Preparations Dangerous for Supply.

# **GUIDANCE NOTES**

Workplace Exposure Limits EH40.

Introduction to Local Exhaust Ventilation HS(G)37.

CHIP for everyone HSG(108).

# **16 OTHER INFORMATION**

REVISION DATE 13/12/2007

REV. NO./REPL. SDS GENERATED 8

# RISK PHRASES IN FULL

R11 Highly flammable.
R12 Extremely flammable.
R38 Irritating to skin.

R51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

R65 Harmful: may cause lung damage if swallowed.
R67 Vapours may cause drowsiness and dizziness.

# DISCLAIMER

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.