





# Machine tool probe calibration solutions

# Achieving maximum accuracy from your probe

Accurate metrology is critical for making high-quality parts. The use of probing can improve your part processes, but any errors in the set-up of a probe can ripple through to the machined part.

Renishaw and MSP have introduced two products to guarantee your probe accuracy.

# ACS-1

ACS-1 helps you to achieve maximum measurement accuracy on your machine tools by removing manual probe calibration steps. The lockable mechanism on ACS-1 overcomes the need for manual use of precision gauge blocks or slips, ensuring consistency and reliability.

# AutoClock

AutoClock requires no human intervention and runs closed-door, 'lights out' operation. The patented technology in AutoClock makes probe set-up easy, safe, accurate, reliable and fast.









# Renishaw ACS-1: Manual probe set-up system

ACS-1 is invaluable for any Renishaw probe calibration. You should select this option if:

- you want to remove the manual steps involved in using gauge blocks or slips to eliminate errors;
- there is no connection to the machine controller available;
- you require a cost-effective solution to improve an existing manual operating procedure; or
- you need quick set-up and training for immediate operation.

#### www.renishaw.com/acs



RENISHAW 🕑

apply innovation<sup>™</sup>

# MSP AutoClock: Automated probe set-up system

AutoClock is essential to achieve the maximum probe accuracy and capability for a 'lights out' manufacturing environment, particularly for 5-axis machines, where probe set-up errors are multiplied. You should select this option if:

- your automated part processes require automated probe set-up and calibration to eliminate human intervention;
- traceability is important and reports for each calibration are needed;
- remote running and fast speed of operation are important; or
- closed-door operation is required to improve health and safety.

#### www.mspltd.com/autoclock

### www.renishaw.com/acs



#### 📞 +44 1453 524524

#### uk@renishaw.com

© 2022 Renishaw plc. All rights reserved. RENISHAW® and the probe symbol are registered trade marks of Renishaw plc. Renishaw product names, designations and the mark 'apply innovation' are trade marks of Renishaw plc or its subsidiaries. Other brand, product or company names are trade marks of their respective owners. Renishaw plc. Registered in England and Wales. Company no: 1106260. Registered office: New Mills, Wotton-under-Edge, Glos, GL12 & JR, UK.

WHILE CONSIDERABLE EFFORT WAS MADE TO VERIFY THE ACCURACY OF THIS DOCUMENT AT PUBLICATION, ALL WARRANTIES, CONDITIONS, REPRESENTATIONS AND LIABILITY, HOWSOEVER ARISING, ARE EXCLUDED TO THE EXTENT PERMITTED BY LAW.

Part no.: H-2000-9032-01-A