

# TP7M stylus kit



© 1990 - 2005 Renishaw plc. All rights reserved.

This document may not be copied or reproduced in whole or in part, or transferred to any other media or language, by any means, without the prior written permission of Renishaw.

The publication of material within this document does not imply freedom from the patent rights of Renishaw plc.

### **Disclaimer**

Considerable effort has been made to ensure that the contents of this document are free from inaccuracies and omissions. However, Renishaw makes no warranties with respect to the contents of this document and specifically disclaims any implied warranties. Renishaw reserves the right to make changes to this document and to the product described herein without obligation to notify any person of such changes.

### **Trademarks**

**RENISHAW®** and the probe emblem used in the RENISHAW logo are registered trademarks of Renishaw plc in the UK and other countries.

**apply innovation** is a trademark of Renishaw plc.


All other brand names and product names used in this document are trade names, service marks, trademarks, or registered trademarks of their respective owners.

Renishaw part no: H-1000-5012-02-A

Issued: 05 2005

## **TP7M stylus kit**

### **Stylus selection guide**



Position	Description
1	M4 STY D8R L100 EWL 100 D4.5CE
2	M4-M3 EXT L100CE
3	M4-M3 EXT L75CE
4	M4 STY D8R L50 EWL 50 D4.5CE
5	M4-M3 EXT L50CE
6	M4 EXT L50 D7.4CE
7	M4 EXT L30 D7.4CE
8	M4 ACC CENTER 5-WAY
9	M3 HEM D30CE
10	M4-M3 EXT L9SS
11	M4-M3 EXT L9SS
12	M3 ACC CENTER 5-WAY
13	M2 ACC CENTER 5-WAY
14	M3-M2 EXT L5SS
15	M3-M2 EXT L5SS
16	M3-M2 EXT L5SS
17	M3-M2 EXT L5SS
18	M3-M2 EXT L5SS
19	M4 STYLUS TOOL
20	M4 STYLUS TOOL
21	M2-M3 STYLUS TOOL
22	M2-M3 STYLUS TOOL
23	M4-M3 EXT L20SS
24	M4 STY D1R L19.5 EWL4 D0.7SS
25	M4 STY D2R L19 EWL8 D1.4SS
26	M4 STY D2R L19 EWL8 D1.4SS
27	M4 STY D2R L19 EWL8 D1.4SS
28	M4 STY D2R L19 EWL8 D1.4SS
29	M4 STY D4R L18 EWL13 D3SS

## Stylus selection

The TP7M is high accuracy probe specifically designed to maintain a high level of accuracy and reliability across a wide spectrum of applications. For best performance, the guidelines given should be followed:

### Do not:

- use more than 50 mm of M3 or M2 styli, or accessories.
- use M2 styli within 30 mm of the probe mounting face or probe axis.
- use the M4 / M2 (SA5) adaptor, use the M4 / M3 and the M3 / M2 adaptors instead.
- do not use stylus knuckle joints.

### Do:

- use the longest possible M4 stylus extensions or M4 / M3 adaptor extensions to achieve a required stylus length.
- follow the guidelines in section 5 of the TP7M user's guide (Renishaw part number H-1000-5010) for stylus selection
- use M3 and M4 styli wherever possible to maximise the stiffness of the stylus configuration, however, M2 styli can be used if necessary for workpiece access.
- tighten up styli adequately using the stylus tools provided.
- ensure stylus ball is kept clean at all times by using distilled water or a proprietary cleaning fluid.

**Renishaw plc**

New Mills, Wotton-under-Edge,  
Gloucestershire, GL12 8JR  
United Kingdom

**T** +44 (0)1453 524524


**F** +44 (0)1453 524901

**E** [uk@renishaw.com](mailto:uk@renishaw.com)

[www.renishaw.com](http://www.renishaw.com)

**RENISHAW**   
apply innovation™

**For worldwide contact details,  
please visit our main website at  
[www.renishaw.com/contact](http://www.renishaw.com/contact)**



H - 1000 - 5012 - 02