


# DPU-2 data processing unit





## Specification

<b>System principal application</b>	Hosts programming and data analysis software for use with Renishaw probing systems.
<b>Part number</b>	A-5465-4002
<b>Compatible software applications</b>	Productivity+™ CNC plug-in; Productivity+™ Scanning Toolkits (see relevant application documentation for part numbers)
<b>Physical</b>	
<b>Size</b>	200 mm × 148.4 mm × 54.7 mm (7.87 in × 5.845 in × 2.15 in) (without DIN rail mounting and brackets)
<b>Weight</b>	1800 g (63.49 oz)
<b>Mounting</b>	DIN rail mount
<b>Environmental</b>	
<b>IP rating</b>	IP3X BS EN 60529:1992+A2:2013
<b>Operating temperature</b>	+5 °C to +55 °C (+41 °F to +131 °F) BS EN 60068-2-30:2005
<b>Humidity</b>	Maximum 93% RH at +40 °C
<b>Cooling</b>	Fanless
<b>Connectivity</b>	
<b>USB</b>	2 × USB 2.0; 2 × USB 3.0
<b>Ethernet</b>	3 × GbE LAN ports
<b>Display</b>	1 × HDMI; 1 × VGA
<b>Power supply</b>	
<b>Voltage</b>	24 V DC ±10% (powered from CNC machine tool)
<b>Protection</b>	Reverse voltage, over current, over voltage
<b>Power consumption</b>	17 W (typical)
<b>Connector</b>	2-pin Phoenix connector
<b>Power on</b>	Auto-on
<b>System storage</b>	128 GB solid-state drive

## Connections



## Mounting the DPU-2



Dimensions given in mm (in)

Compliance information for this product is available by scanning the QR code or visiting [www.renishaw.com/mtpdoc](http://www.renishaw.com/mtpdoc).



## Spare parts and accessories

A full range of spare parts and accessories is available. Contact Renishaw for a full list.

[www.renishaw.com/dpu2](http://www.renishaw.com/dpu2)



#renishaw

+44 (0) 1453 524524

✉ [uk@renishaw.com](mailto:uk@renishaw.com)

© 2017–2023 Renishaw plc. All rights reserved. This document may not be copied or reproduced in whole or in part, or transferred to any other media or language by any means, without the prior written permission of Renishaw.

RENISHAW® and the probe symbol are registered trade marks of Renishaw plc. Renishaw product names, designations and the mark 'apply innovation' are trade marks of Renishaw plc or its subsidiaries. Other brand, product or company names are trade marks of their respective owners.

WHILE CONSIDERABLE EFFORT WAS MADE TO VERIFY THE ACCURACY OF THIS DOCUMENT AT PUBLICATION, ALL WARRANTIES, CONDITIONS, REPRESENTATIONS AND LIABILITY, HOWSOEVER ARISING, ARE EXCLUDED TO THE EXTENT PERMITTED BY LAW. RENISHAW RESERVES THE RIGHT TO MAKE CHANGES TO THIS DOCUMENT AND TO THE EQUIPMENT, AND/OR SOFTWARE AND THE SPECIFICATION DESCRIBED HEREIN WITHOUT OBLIGATION TO PROVIDE NOTICE OF SUCH CHANGES.

Renishaw plc. Registered in England and Wales. Company no: 1106260. Registered office: New Mills, Wotton-under-Edge, Glos, GL12 8JR, UK.

Part no.: H-5465-8230-02-B

Issued: 02.2023