New Mills, Wotton-under-Edge, Gloucestershire GL12 8JR United Kingdom T +44 (0)1453 524524 F +44 (0)1453 524901 E uk@renishaw.com

www.renishaw.com



# PH20 motorised probe head



PH20 is a dynamic measuring probe head which delivers a 3-fold increase in measurement throughput whilst maintaining high system accuracy.

Utilising technology developed for the multi-award winning REVO® measurement system, the new PH20 probe head offers unique 'head touches' for rapid touch-trigger measurement, and fast infinite 5-axis positioning to guarantee optimal feature access. Unlike conventional touch trigger measurement methods which rely on speeding up the motion of the CMM's 3 axes to measure quickly, PH20 uses head motion to minimise the dynamic errors of the CMM at higher measurement speeds. Its compact design makes it suitable for new CMM purchases, and as a retrofit to the vast majority of existing CMM touch-trigger installations.

PH20 incorporates the industry standard TP20 touch-trigger probe, affording immediate access to a range of proven probe modules and a wide selection of trigger forces, directional sensing options and extensions to meet application requirements. The detachable modules provide crash protection and can be automatically changed using the MCR20 change rack. Current users of TP20 systems will be able to upgrade to PH20 and utilise their existing modules\*.

The PH20 probe head offers dramatic time savings with a unique rapid 'inferred calibration' technique which determines head orientation and probe position in a single operation, allowing subsequent measurement at any head angle. The system's design requires no air supply, and it can be mounted to the CMM quill either directly or via a shank using a range of mounting adaptors.

### **Key features**

**Compact design** – suitable for a wide range of CMMs using shank or quill mounting.

**Renishaw CMM controller** – I++DME communication; wide selection of metrology software.

**Index head compatibility** – no requirement to modify existing programs in the majority of cases.

Integral TP20 probe - allows re-use of existing equipment.

## **Innovations**

**Rapid head touches** – where the CMM is stationary and the head moves and takes a touch point.

Rapid 5 axis moves – synchronised motion of the head and CMM between measurements.

**Inferred calibration** – determines head orientation and probe position in a single operation, allowing subsequent measurement at any head angle.


<sup>\*</sup> Excepting the extended force module

New Mills, Wotton-under-Edge, Gloucestershire GL12 8JR United Kingdom T +44 (0)1453 524524 F +44 (0)1453 524901 E uk@renishaw.com

www.renishaw.com



# **Specification**



Dimensions in mm (inch)

Dimens	
Dimension A	
mm	inch
21	0.83
21	0.83
21	0.83
25	0.98
71	2.79
96	3.78
	21 21 21 21 25 71



Weight (excluding module and cables)	810 g (28.6 oz)		
Temperature range			
Operating	15 °C to 35 °C (59 °F to 95 °F)		
Storage	-25 °C to 70 °C (-13 °F to 158 °F)		
Maximum movement speed	3 revs/s (1281 mm/s with standard module & 10 mm stylus)		
Maximum head touch speed	50 mm/s		
Rotation angles			
A axis	1150 to 1150		
B axis	-115° to 115° <b>∞</b>		
Angular resolution	0.4 µRadians		
Bearings	Mechanical		
Change rack system	MCR20 NI and MCR20		
Joystick	Multifunction MCU lite-2		
ISO 10360-5 (2001) typical performance		CMM TOUCH	HEAD TOUCH
std force module with 12 x 4 mm stylus on a CMM	Size	0.0006 mm (0.00002 in)	0.0002 mm (0.00001 in)
with ISO 10360-2 (2002) specification of 0.48+ L/1000 $^{\circ}$	Form	0.0026 mm (0.00010 in)	0.0024 mm (0.00009 in)
* specified with a TP7	Location	0.0013 mm (0.00005 in)	0.0009 mm (0.00003 in)

#### Additional information

- PH20 can be fitted directly to the CMM quill. A wide range of shank adaptors is also available.
- The PH20 system utilises the Renishaw Universal CMM controller system, which provides functionality particular to 5-axis
  motion and head-touch measurement.
- I++DME command protocol communication via Renishaw UCCserver™ software application.

### For worldwide contact details, please visit our main website at www.renishaw.com/contact

RENISHAW HAS MADE CONSIDERABLE EFFORTS TO ENSURE THE CONTENT OF THIS DOCUMENT IS CORRECT AT THE DATE OF PUBLICATION BUT MAKES NO WARRANTIES OR REPRESENTATIONS REGARDING THE CONTENT. RENISHAW EXCLUDES LIABILITY, HOWSOEVER ARISING, FOR ANY INACCURACIES IN THIS DOCUMENT.

**RENISHAW**® and the probe emblem used in the RENISHAW logo are registered trademarks of Renishaw plc in the UK and other countries. **apply innovation** is a trademark of Renishaw plc.

© 2010 Renishaw plc All rights reserved Issued 0410 Part no. H-1000-2059-01-A