
Standard wiring configuration and fuse locations

Closed MRO relay Open Closed ARO relay Open Closed Probe LED LĖD Red status N/C Green Open Probe enabled Probe Closed status N/O

NOTE: See the diagram below for location of the spare fuse.



Type: Inputs are not polarity conscious

Apply voltage of 15 Vdc to 30 Vdc across

input to activate

Specification: Input load = 12.5 mA maximum @30 V

Input voltage = 30 V maximum

Outputs: MRO,

Open


MRO, ARO
Probe status N/O Probe status N/C

All outputs are protected by fuses (f) 50 mA (TE5)

Wickman 3950050 Renishaw P-FS02-0001

Inhibit input

The inhibit input is not polarity conscious. Apply a voltage of 15 Vdc to 30 Vdc across PLI-24 and PLI-25 to activate. Inhibit input presents a load of 12.5 mA max. Probe inhibit disables the probe outputs.




NOTE: Probe status LED will still function when inhibit is active.

TSI2-C connections

NOTE: ARO, MRO and Probe Status outputs are SSR (solid state relay). Maximum current = 40 mA, maximum voltage = 30 V

The TSI2-C interface unit should be installed in the CNC control cabinet. Where possible, site the unit away from potential sources of interference such as transformers and motor controllers.





 V_{SS} = (Interface supply) 18 Vdc to 30 Vdc

 $I_{MAX} = 120 \text{ mA}$

Input power supply protection is provided by self resetting fuses. Reverse polarity protection is provided.

Cable screen must be terminated at the machine star point via the most direct route from the free end of the cable. Mount interface and route cables away from known sources of EMI.

This document may not be copied or reproduced in whole or in part, or transferred to any other media or language, by any means, without the prior written permission of Renishaw.

The publication of material within this document does not imply freedom from the patent rights of Renishaw plc.

Disclaimer

RENISHAW HAS MADE CONSIDERABLE EFFORTS TO ENSURE THE CONTENT OF THIS DOCUMENT IS CORRECT AT THE DATE OF PUBLICATION BUT MAKES NO WARRANTIES OR REPRESENTATIONS REGARDING THE CONTENT. RENISHAW EXCLUDES LIABILITY, HOWSOEVER ARISING, FOR ANY INACCURACIES IN THIS DOCUMENT.

Trademarks

Renishaw® and the probe emblem used in the RENISHAW logo are registered trademarks of Renishaw plc in the UK and other countries.

apply innovation is a trademark of Renishaw plc.

All brand names and product names used in this document are trade names, service marks, trademarks, or registered trademarks of their respective owners.

Renishaw part no: H-2000-5245-04-A

Issued: 09 2009

Changes to specification

Renishaw plc may modify or change its products or specifications without notice and without obligation

Equipment requiring attention under warranty must be returned to your supplier No claims will be considered where Renishaw equipment has been misused, or repairs or adjustments have been attempted by unauthorised persons.

Patent notice

The following patents relate to features of the products shown in this user's leaflet and of other similar products (Other patents applied for):

JPw 2002-531,839

US 5,669151

FCC Declaration

FCC Section 15.19

This device complies with Part 15 of the FCC rules.

- Operation is subject to the following two conditions: This device may not call harmful interference.
- 2. This device must accept any interference received, including interference

including interference that may cause undesired operation.

This equipment has been tested and found to comply with the limits for a Class A digital device, pursuant to Part 15 of the FCC rules. These limits are designed to provide reasonable protection against harmful interference when the equipment is operated in a commercial environment.

This equipment generates, uses, and can radiate radio frequency energy and, if not installed and used in accordance with the instruction manual, may cause harmful interference to radio communications.

Operation of this equipment in a residential area is likely to cause harmful interference, in which case you will be required to correct the interference at your own expense.

The user is cautioned that any changes or modifications not expressly approved by Renishaw plc, or authorised representative could void the user's authority to operate

The user is also cautioned that any peripheral device installed with this equipment such as a computer, must be connected with a high-quality shielded cable to insure compliance with FCC limits.

EC DECLARATION OF CONFORMITY

Renishaw plc declare that the product: -

TSI2-C Name

Description: Machine tool interface for HPPA or HPRA

has been manufactured in conformity with the following standards: -

BS EN 61326:1998/ A1:1998/A2:2001

Power supply:

Inhibit:

Screen

Outputs - voltage free SSR:

Probe status N/C, MRO,

Probe status N/O, ARO:

Cable requirements:

Environmental:

Connector requirements:

Length:

Operating: Storage:

Electrical equipment for measurement, control and laboratory use - EMC

requirements.

Immunity to annex A - industrial locations. Emissions to class A (non-domestic) limits.

and that it complies with the requirements of directives: -

89/336/EEC - Electromagnetic compatibility (EMC)

The above information is summarised from the full EC Declaration of Conformity. A copy is available from Renishaw on request.

Specification

18 Vdc to 30 Vdc

SELV BS EN61010 (IEC1010)

Maximum load current 140 mA

Note: Reverse polarity protection provided. Input supply protection is provided

by self resetting fuses.

Inhibit input is not polarity conscious

Maximum load 12.5 mA

Maximum current 40 mA

Open circuit leakage max. 10 nA

Maximum voltage 30 V

(f) 50 mA

Wickman 3950050

Specification: 7/0.2 mm (0.22 mm²) 12 core

3 m maximum

Renishaw P-FS02-0001

machine ground star point

terminated at the D shell

+5 °C to +60 °C (41 °F to 140 °F)

0 °C to +70 °C (32 °F to 158 °F)

Power supply 0 V must be

15 Vdc to 30 Vdc across input to activate.

Probe inhibit disables the probe outputs.

Short circuit load resistance max. 100 ohms (excluding voltage drops across the cable)

Outputs are protected by fuses (TE5) -

Connect free end of cable screen to


polyurethane insulated with braided screen


shell - connector end of screen must be

25 way D socket with EMI/RFI shielded

connected to machine star point.

TSI2-C installation and dimensions





TSI2-C

RENISHAW

H-2000-5245-04-A User's leaflet


New Mills, Wotton-under-Edge Gloucestershire, GL12 8JR

+44 (0)1453 524524 +44 (0)1453 524901 uk@renishaw.com

RENISHAW.

Probe trigger delay

Brown/White or Blue/Green (side exit) wire configuration for DELAY OFF. Example below shows normally closed probe status output delay.



visit our main web site at www. renishaw.com/contact



For worldwide contact details, please