

Renishaw CMM Products Division

PRODUCT BULLETIN – PBC1541

Product:	PH20	Status:	Company confidential
Title:	PH20 Reference Mark	Date:	3 rd August 2011

Originator:		Distribution:	
L Quick		Internal	✓
Reviewer:		Subsidiaries	✓
		PH20 OEMs	✓
		Distributors	✓
D Wallace		Retrofitters	✓

Summary:

Due to obsolescence issues we have recently introduced a new reference mark sensor into the PH20. As part of this introduction all heads with these new sensors **must** be used with UCCSuite version 4.4.5 or greater. Failure to use the correct version of UCCSuite may result in intermittent homing failures or the head may 'home' approximately 20° out of position.

Identifying a PH20 with the new reference mark sensor

An initial batch of the following serial numbers has been manufactured and are now available to be shipped:

41F121
41F122
41F124
41F125
41F126
41F127

We have since formally introduced this into production and all heads manufactured with a serial number of 41K341 or greater will have the reference mark sensor fitted.

If you have any questions or comments on this bulletin please visit www.renishaw.com/cmmsupport and use the "Contact" facility. This will ensure that your call is logged and processed efficiently.