# NC4+ Blue non-contact tool setting range

## Specification

Principal application	High-precision, high-speed non-contact tool setting and tool breakage detection on all sizes of vertical and horizontal machining centres, multi-tasking machines and gantry machining centres.		
Transmission type	Hard-wired transmission		
Compatible interfaces	NCi-6		
Repeatability	F115 and F145	±0.5 μm (19.69 μin) 2σ	
	F230 and F300	±0.75 μm (29.53 μin) 2σ	
Tool setting and tool breakage detection (minimum tool or feature size)	F115 systems	Ø0.03 mm (0.0012 in)	
	F145 systems	Ø0.05 mm (0.0020 in)	
	F230 systems	Ø0.1 mm (0.0039 in)	
	F300 systems	Ø0.2 mm (0.0079 in)	
Output signal (from interface unit)	Two voltage-free, solid-state relays (SSR). Each can be either normally open or normally closed (selectable via a switch). Current (maximum) 50 mA, voltage (maximum) ±50 V. The interface contains an auxiliary relay which can be used for switching the output between the NC4+ Blue and a spindle probe. This relay can also be used to control an air blast solenoid (optional).		
Supply voltage (to interface)	11 Vdc to 30 Vdc		
Supply current (to interface)	120 mA @ 12 Vdc, 70 mA @ 24 Vdc		
Supply protection	Resettable fuses in interface. Reset by removing power and cause of fault.		
Electrical connection arrangement	Systems with connector: Connector socket. Hard-wired systems: Cable on the end of the unit. Other configurations are available on request.		
Cable (to interface)	Specification	$\emptyset$ 6.0 mm (0.24 in), two twisted pairs, two individual cores plus screen, each core 18 × 0.1 mm insulated.	
	Length	12.5 m (41.01 ft)	
	Electrical connection	Systems with connector: cable with bayonet-type plug, connector socket on the end of the unit. Hard-wired systems: cable on the end of the unit. Other configurations are available on request.	
NC4+ Blue pneumatic supply	Air supply to the NC4 must conform to BS ISO 8573-1: 2010 Class 1.4.2. 6.0 bar (87.02 psi) maximum. Systems with connector: $\emptyset$ 4.0 mm (0.16 in) × 5.0 m (16.40 ft). Hard-wired systems: $\emptyset$ 3.0 mm (0.12 in) × 5.0 m (16.40 ft).		
Air blast pneumatic supply	Air supply to the air blast must conform to BS ISO 8573-1: 2010 Class 2.9.4. Ø6.0 mm (0.24 in) air pipe × 5.0 m (16.40 ft), 6.0 bar (87.02 psi) maximum.		
Laser type	Class 2 laser product: 1 mW maximum output emitted wavelength 405 nm. WARNING: Laser radiation. Do not stare into beam.		
Laser beam alignment	The unit is supplied with an adjustable mounting plate on the underside.		
Weight (including 12.5 m (41.01 ft) of cable)	1080 g (2.38 lb) to 2000 g (4.4 lb) depending on configuration.		






**RENISHAW**, apply innovation<sup>™</sup>




## **Specification (continued)**

Mounting	M4 ( $\times$ 3), M10 (3/8 in) or M12 ( $\frac{1}{2}$ in) bolts for mounting via adjuster plate (not supplied). Other fixing arrangements are available on request.	
Environment	IP rating	IPX6 and IPX8, BS EN 60529:1992+A2:2013 (IEC 60529:1989+A1:1999+A2:2013)
	Storage temperature	–25 °C to +70 °C (–13 °F to +158 °F)
	Operating temperature	+5 °C to +55 °C (+41 °F to +131 °F)


## NC4+ Blue hard-wired system dimensions



#### NC4+ Blue straight connector dimensions









#### NC4+ Blue with connector dimensions

NC4+ Blue 90° connector dimensions









#### NC4+ Blue adjuster plate mounting and dimensions

#### **Electro-pneumatic integration**



#### Spare parts and accessories

A full range of spare parts and accessories is available. Contact Renishaw for a full list.





**L** +44 (0) 1453 524524

uk@renishaw.com

© 2021 Renishaw plc. All rights reserved. RENISHAW® and the probe symbol are registered trade marks of Renishaw plc. Renishaw product names, designations and the mark 'apply innovation' are trade marks of Renishaw plc or its subsidiaries. Other brand, product or company names are trade marks of their respective owners. Renishaw plc. Registered in England and Wales. Company no: 1106260. Registered office: New Mills, Wotton-under-Edge, Glos, GL12 & JR, UK.

WHILE CONSIDERABLE EFFORT WAS MADE TO VERIFY THE ACCURACY OF THIS DOCUMENT AT PUBLICATION, ALL WARRANTIES, CONDITIONS, REPRESENTATIONS AND LIABILITY, HOWSOEVER ARISING, ARE EXCLUDED TO THE EXTENT PERMITTED BY LAW.

Part no.: H-6435-8200-01-A Issued: 11.2021