

Renishaw systems crucial to manufacturing at Martin Baker

Martin-Baker, the world's leading supplier of aircraft ejection seats, relies on Renishaw's QC10 ballbar and machine tool probe systems to manufacture complex, high-quality components.

Martin-Baker gauges the success of its ejection seats by the number of successful ejections. With over 7000 lives saved to date the company can easily justify its reputation as the leading supplier of aircraft escape systems in the world, having 80% of the world market and supplying aircraft manufacturers and end-users in most countries.

The first ejection seats were developed in 1944, and a series of developments over the years have led to the very sophisticated micro-processor controlled, rocket-propelled seats supplied today. The company may have a long history, but manufacturing at the factory in Uxbridge, Middlesex, is right up to date, with the latest equipment in use. This is very important, when you consider that about 1 in 10 of Martin-Baker seats have actually been used in emergencies. It is difficult to imagine a situation where the reliability of mechanical parts, for the few seconds when they do their job, could be more important.

The complex machined components that go into the seats have multiple features, and demand very high standards of quality control to ensure reliable operation in the toughest conditions. Aluminium is the most common material, and with the machine time and resources almost all finished parts are of a high value, so minimising scrap is of paramount importance.



Typical complex components, quality is critical to the reliable operation of the seats



Martin Baker seat in use with the US Navy




MP10 spindle probe setting the component for further machining operations

Probing on fully automated systems

Most components are manufactured on 3 Makino A55 4-axis machining centres, fed by a common 60 pallet loading system.

These machines are set up identically to allow flexibility when requirements for quantities and types fluctuate. All three rely on spindle-mounted probes to control their operation.

When a pallet is loaded into the machine containing the raw material on simple fixtures, the first feature is machined and immediately probed with the Renishaw MP10 probe. This measurement establishes the datum to which all subsequent machining is related - the programs do not rely on the accuracy of the fixtures. Peter Smith, the production engineer and programmer responsible, adds, "the probe is also used when needed during the course of the program, probing the machined surfaces then machining the next ops relative. This guarantees positions on bores and other features that must relate to each other rately. All components are probed at the end of machining, which allows the machine automatically to make 'intelligent' decisions such as whether extra ops are needed." "When needed" is a key phrase here, the probe system being sufficiently flexible to be used only when a measurement is required, with routines lasting just a matter of seconds. The programmers need add only 1 or 2 simple lines of code to their program to take these measurements, with the resident probing software enabling the probe to be loaded into the spindle from the tool changer, working out the necessary moves and automatically updating offsets.



Ejection seat guide rails - wall thickness, gauged with the spindle probe is critical along the full length

Probing on older machines with manual loading

Probes have also found applications on three Makino 106 CNC milling machines, each twenty years old but still in full production and expected to hold consistent tolerances on key components. The probes are used for job set-up in several different ways, for example, forged billets are clamped into the vice and the probe checks certain features to detect any variation in the forging. The readings can be used by the machine's control to 'decide' where machining starts and how many cuts are required, eliminating 'fresh-air' cuts and any scrap due to setting.



QC10 ballbar performing a quick performance test on a Makino 160 milling machine: the diagnostic results allow immediate adjustments to improve machining accuracy

These Makino machines are also used to produce the slots on the guide rails along which the seat will be propelled when used. While the weight must be kept to a minimum, it is essential for the strength of the rail that the wall thickness is sufficient along the full length. This brings challenges when setting up and aligning. The probe checks the exact position of multiple positions on the material clamped to the machine bed. These readings are used to adjust the machining program and ensure that the correct amount is machined in all the required places. Before probing, when this was done manually, the whole job took over 2 hours. Each rail is now completed in 30 minutes, with a far higher confidence and reduced scrap.

Each Makino is fitted with an indexer, which although used for a variety of jobs to reduce time consuming manual setting for each face, does not position as accurately as the work requires. Therefore the spindle probe is quickly used in-cycle after each indexed move and takes points on a part's surface. This determines the component position and the control then works out any compensation required to the machining program. Peter Smith is in no doubt how important this is to the process, "Without this, the machine couldn't do all the faces of the component, in fact we couldn't easily machine some of these components at all".

Future plans for machining operations

Recently, Martin-Baker has had two very large Mori Seiki mill-turn machines installed, to provide extra capacity to cope with demand and upgrade machining capability and productivity. Both are fitted with Renishaw MP700 spindle probes, which are ideal for such versatile multi-axis machines. To fit probing was not a difficult decision, as Martin-Baker now has a well established policy that all new machines must have probing systems.

Confidence in machine performance with the QC10 ballbar

Measuring components on the machines and setting jobs where dimensions are critical relies on having the confidence that the machine is positioning correctly to start with. This is also true for the machining operations themselves, but if you have suspicions that the machine is not always where it thinks it is, how do you find out about the root causes? Robbie Mitchell, Martin-Baker's machine tool maintenance engineer, obtains the information he needs with a Renishaw QC10 ballbar.

The QC10 ballbar is coupled to magnetic mounts on the machine's bed and in the machine spindle. It then follows the radius of a circle described by the machine in 2 axes, controlled by a simple program running on the machine's control. The high accuracy transducer in the ballbar records any variation in this measured radius and the ballbar software, running on a linked PC, displays and diagnoses the results. Whether the machining performed on that machine involves circular interpolation or not, this test enables the software to identify and quantify the exact causes of any positioning errors. If the error can be corrected by making adjustments, for example trimming servos, the exact figure is entered, and another test run after adjustment to confirm the improved performance.

Robbie Mitchell has used it regularly for 6 years, performing the 10 minute tests on every CNC machine in the factory every 3 months, together with extra tests if the machine has suffered a crash. Generally he is looking for machines that show that they are describing paths with a circularity error greater than 25microns. Beyond this value he knows that the machine cannot hold most specified component tolerances so scrap parts are highly likely and the machine will require maintenance. For him the ballbar allows true predictive maintenance.

"The bottom line is that the ballbar is easy to use", comments Mitchell, "It takes you straight to the fault and is much quicker. If we thought something was up with a machine, I used to spend a morning checking everything, now I know what to do after 10 minutes. Also, the information we have on machines is passed to the production guys and is used to plan certain jobs onto machines we know are capable of doing them".

www.renishaw.com/MTP

Renishaw plc

New Mills, Wotton-under-Edge,
Gloucestershire GL12 8JR
United Kingdom

T +44 (0) 1453 524524

F +44 (0) 1453 524901

E uk@renishaw.com

www.renishaw.com

RENISHAW 
apply innovation™

About Renishaw

Renishaw is an established world leader in engineering technologies, with a strong history of innovation in product development and manufacturing. Since its formation in 1973, the company has supplied leading-edge products that increase process productivity, improve product quality and deliver cost-effective automation solutions.

A worldwide network of subsidiary companies and distributors provides exceptional service and support for its customers.

Products include:

- Dental CAD/CAM scanning and milling systems.
- Encoder systems for high accuracy linear, angle and rotary position feedback.
- Laser and ballbar systems for performance measurement and calibration of machines.
- Medical devices for neurosurgical applications.
- Probe systems and software for job set-up, tool setting and inspection on CNC machine tools.
- Raman spectroscopy systems for non-destructive material analysis.
- Sensor systems and software for measurement on CMMs (co-ordinate measuring machines).
- Styli for CMM and machine tool probe applications.

Renishaw worldwide

Australia

T +61 3 9521 0922

E australia@renishaw.com

Austria

T +43 2236 379790

E austria@renishaw.com

Brazil

T +55 11 4195 2866

E brazil@renishaw.com

Canada

T +1 905 828 0104

E canada@renishaw.com

The People's Republic of China

T +86 21 6180 6416

E china@renishaw.com

Czech Republic

T +420 548 216 553

E czech@renishaw.com

France

T +33 1 64 61 84 84

E france@renishaw.com

Germany

T +49 7127 9810

E germany@renishaw.com

Hong Kong

T +852 2753 0638

E hongkong@renishaw.com

Hungary

T +36 23 502 183

E hungary@renishaw.com

India

T +91 80 6623 6000

E india@renishaw.com

Indonesia

T +62 21 2550 2467

E indonesia@renishaw.com

Israel

T +972 4 953 6595

E israel@renishaw.com

Italy

T +39 011 966 10 52

E italy@renishaw.com

Japan

T +81 3 5366 5316

E japan@renishaw.com

Malaysia

T +60 3 5631 4420

E malaysia@renishaw.com

The Netherlands

T +31 76 543 11 00

E benelux@renishaw.com

Poland

T +48 22 577 11 80

E poland@renishaw.com

Russia

T +7 495 231 16 77

E russia@renishaw.com

Singapore

T +65 6897 5466

E singapore@renishaw.com

Slovenia

T +386 1 527 2100

E mail@rls.si

South Korea

T +82 2 2108 2830

E southkorea@renishaw.com

Spain

T +34 93 663 34 20

E spain@renishaw.com

Sweden

T +46 8 584 90 880

E sweden@renishaw.com

Switzerland

T +41 55 415 50 60

E switzerland@renishaw.com

Taiwan

T +886 4 2473 3177

E taiwan@renishaw.com

Thailand

T +66 2 746 9811

E thailand@renishaw.com

Turkey

T +90 216 380 92 40

E turkiye@renishaw.com

UK (Head Office)

T +44 1453 524524

E uk@renishaw.com

USA

T +1 847 286 9953

E usa@renishaw.com

For all other countries

T +44 1453 524524

E international@renishaw.com

RENISHAW HAS MADE CONSIDERABLE EFFORTS TO ENSURE THE CONTENT OF THIS DOCUMENT IS CORRECT AT THE DATE OF PUBLICATION BUT MAKES NO WARRANTIES OR REPRESENTATIONS REGARDING THE CONTENT. RENISHAW EXCLUDES LIABILITY, HOWSOEVER ARISING, FOR ANY INACCURACIES IN THIS DOCUMENT.

©2011 Renishaw plc. All rights reserved.

Renishaw reserves the right to change specifications without notice.

RENISHAW® and the probe emblem used in the RENISHAW logo are registered trademarks of Renishaw plc in the UK and other countries. apply innovation, Productive Process Pyramid, Productive Process Patterns, Productivity+, AxiSet, Rengage, Trigger Logic, ToolWise, Sprint, MicroHole, PassiveSeal and SwarfStop are trademarks of Renishaw plc.

All other brand names and product names used in this document are trade names, service marks, trademarks or registered trademarks of their respective owners.



H - 5650 - 3004 - 01

Part no. H-5650-3004-01-A