


# The power of Additive Manufacturing



# Design today, build tomorrow

## The huge potential for Additive Manufacturing

In the world of manufacturing technology, we occasionally experience breakthroughs that have the potential to transform the industry, enabling existing products to be made faster, cheaper and better, and opening up a world of new product possibilities.


Just like the advent of CNC machining, CAD/CAM, co-ordinate measuring machines and lasers, metal-based Additive Manufacturing will transform part production, but we are only at the start of this exciting journey.

At the core of metal-based Additive Manufacturing is the use of focused laser energy to fuse fine metallic powders to form highly complex functional components that go way beyond the designs of today.


In comparison to other technological advances, lasers are something of a quiet revolution, spanning the last 50 years, but their influence on fields as diverse as bio-medical, surface analysis, electronics, ship building, molecular diagnostics, precision measurement and a multitude of others is immeasurable.

Yet, just like Additive Manufacturing, in their early years, lasers were something of a solution in search of an application - not unusual in disruptive technologies.

Renishaw's laser melting technology has the power to unlock this hidden potential, and in the hands of talented engineers, the full commercial and technical advantages offered by Additive Manufacturing can be enjoyed by manufacturers like you.



Hip implant model



Laser melting machine build chamber

## CAD driven direct manufacturing in a wide range of metals

Renishaw's laser melting is a pioneering, additive manufacturing process capable of producing fully dense metal parts direct from 3D CAD, using a high-powered fibre laser. Parts are built from a range of fine metal powders that are melted in a tightly controlled atmosphere, in layer thicknesses ranging from 20 to 100 microns.

The technology is already widely employed for the manufacture of custom medical implants, lightweight aerospace and motorsports parts, efficient heat exchangers, and injection moulding inserts with conformal cooling channels.


The capability to safely process reactive materials such as titanium and aluminium is a standard feature on all Renishaw laser melting machines with safe systems for process emissions and powder handling. Laser melting machine users also benefit from minimal waste product as over 98% of the material is re-usable after refinement in the Renishaw powder conditioning system.



Motorsport component



Tool with conformal cooling



## Your partner for change

Renishaw is a global engineering technologies company with key strengths in machining, metrology and process control. For almost 40 years our innovative products have enabled businesses across the world, from engineering, science and medical sectors, to improve efficiency in manufacturing processes and enrich peoples' lives.

We have over 3300 staff across the globe, and with around 18% of annual sales invested in R&D and engineering, significant numbers of our talented staff are devoted to the development of ground breaking technologies. So we're here for the long haul and we enjoy an excellent reputation for offering strong support to our customers through a network of over 70 wholly-owned service and support offices in 32 countries.

## Applications

Early adopters of laser melting for medical orthopaedics benefit significantly from the ability of laser melting to manufacture complex geometries and structures in high grade materials, such as titanium.

From patient-specific orthopaedic implants to volume production of medical devices featuring hybrid structures and textures, laser melting has the potential to unlock manufacturing capabilities that combine free-form shapes and intricate lattice structures. This improves osseointegration in orthopaedics, leading to much improved patient outcomes. It also allows aerospace and motorsport companies to 'add lightness' to components in a range of demanding applications.

Our experienced staff have the commitment and the applications expertise necessary to ensure a smooth, trouble-free integration of our pioneering technologies into your manufacturing systems. You can also be assured that we'll work with you beyond the initial installation to ensure that you gain maximum benefit from your Renishaw purchase through ongoing applications support and a range of service packages to keep your system in top condition, ready for the next manufacturing challenge.



Global service and support



Renishaw's world-class machine shop in Gloucestershire, UK

From tooling inserts, featuring conformal cooling, to lightweight structures for aerospace and high technology applications, laser melting gives designers more freedom, resulting in structures and shapes that would otherwise be constrained by conventional processes or the tooling requirements of volume production. Laser melting is complementary to conventional machining technologies and forms part of a manufacturing system including heat treatment, surface post-processing, and directly contributes to reduced lead times, tooling costs and material waste.

- Shorten development timescales - be first to market
- Reduce waste product and cost - build only what you need
- Enjoy increased design freedom - create complex structures and hidden features



## About Renishaw

Renishaw is an established world leader in engineering technologies, with a strong history of innovation in product development and manufacturing. Since its formation in 1973, the company has supplied leading-edge products that increase process productivity, improve product quality and deliver cost-effective automation solutions.

A worldwide network of subsidiary companies and distributors provides exceptional service and support for its customers.

### Products include:

- Additive manufacturing and vacuum casting technologies for design, prototyping, and production applications
- Dental CAD/CAM scanning systems and supply of dental structures
- Encoder systems for high-accuracy linear, angle and rotary position feedback
- Fixturing for CMMs (co-ordinate measuring machines) and gauging systems
- Gauging systems for comparative measurement of machined parts
- High-speed laser measurement and surveying systems for use in extreme environments
- Laser and ballbar systems for performance measurement and calibration of machines
- Medical devices for neurosurgical applications
- Probe systems and software for job set-up, tool setting and inspection on CNC machine tools
- Raman spectroscopy systems for non-destructive material analysis
- Sensor systems and software for measurement on CMMs
- Styli for CMM and machine tool probe applications

For worldwide contact details, visit [www.renishaw.com/contact](http://www.renishaw.com/contact)



RENISHAW HAS MADE CONSIDERABLE EFFORTS TO ENSURE THE CONTENT OF THIS DOCUMENT IS CORRECT AT THE DATE OF PUBLICATION BUT MAKES NO WARRANTIES OR REPRESENTATIONS REGARDING THE CONTENT. RENISHAW EXCLUDES LIABILITY, HOWSOEVER ARISING, FOR ANY INACCURACIES IN THIS DOCUMENT.

© 2016 Renishaw plc. All rights reserved.

Renishaw reserves the right to change specifications without notice.

**RENISHAW** and the probe symbol used in the **RENISHAW** logo are registered trade marks of Renishaw plc in the United Kingdom and other countries. **apply innovation** and names and designations of other Renishaw products and technologies are trade marks of Renishaw plc or its subsidiaries. All other brand names and product names used in this document are trade names, trade marks or registered trade marks of their respective owners.



H - 5800 - 0100 - 07

Part no.: H-5800-0100-07-A  
Issued: 06.2016