

# Tapintószárak és tartozékaik

Ha a pontosság számít, ragaszkodjon az eredeti Renishaw tapintószárakhoz. Ne érje be kevesebbel!

## M2 menetes tapintószárak

Rubingömb-végű tapintószárak										Szilícium-nitrát és cirkóniumgömb-végű tapintószárak																								
<b>(rozsdamentes acél)</b> <b>A-5000-7802</b> A 1.5 (0.06) B 10.0 (0.40) <b>A-5000-4154</b> A 4.0 (0.16) B 10.0 (0.40) <b>A-5000-4156</b> A 6.0 (0.24) B 10.0 (0.40)					<b>(keményfém)</b> <b>A-5000-7805</b> A 0.5 (0.020) B 10.0 (0.40) <b>A-5003-0577</b> A 0.7 (0.028) B 20.0 (0.79) <b>A-5003-0034</b> A 1.5 (0.06) B 20.0 (0.79) <b>A-5003-0938</b> A 3.0 (0.12) B 20.0 (0.79) <b>A-5003-0043</b> A 4.0 (0.16) B 30.0 (1.19)					<b>(kerámia)</b> <b>A-5003-1370</b> A 4.0 (0.16) B 30.0 (1.19) <b>A-5003-4779</b> A 5.0 (0.20) B 30.0 (1.19) <b>A-5003-4780</b> A 6.0 (0.24) B 30.0 (1.19) <b>A-5003-0066</b> A 5.0 (0.20) B 50.0 (1.97) <b>A-5003-4241</b> A 4.0 (0.16) B 30.0 (1.19)					<b>(szénsszál)</b> <b>A-5003-2286</b> A 5.0 (0.20) B 50.0 (1.97) <b>A-5003-4785</b> A 5.0 (0.20) B 75.0 (2.96) <b>A-5003-4786</b> A 6.0 (0.24) B 75.0 (2.96) <b>A-5003-2291</b> A 6.0 (0.24) B 100.0 (3.94)					<b>(rozsdamentes acél)</b> <b>A-5003-6120</b> A 2.0 (0.08) B 10.0 (0.40) <b>A-5003-7723</b> A 2.0 (0.08) B 10.0 (0.40) <b>A-5004-1017</b> A 2.0 (0.08) B 20.0 (0.79) <b>A-5004-2923</b> A 2.0 (0.08) B 20.0 (0.79)					<b>(keményfém)</b> <b>A-5003-0074</b> A 2.0 (0.08) B 40.0 (1.58) <b>A-5003-0074</b> A 2.0 (0.08) B 40.0 (1.58)					<b>(ezüstacél)</b> <b>A-5000-3611</b> A 6.0 (0.24) B 1.2 (0.05) <b>A-5000-7809</b> A 18.0 (0.71) B 1.5 (0.06)				

**Jelmagyarázat**

A Gömb átmérője  
B Teljes hossz  
Méretek: mm (hüvelyk)

## M3 menetes tapintószárak

REVO-hoz ajánlott tapintószárak										Hengeres tapintószárak										Tapintószár hosszabbítók									
<b>(rozsdamentes acél)</b> <b>A-5000-7806</b> A 1.0 (0.04) B 10.0 (0.40) <b>A-5000-7807</b> A 2.0 (0.08) B 10.0 (0.40) <b>A-5000-3604</b> A 3.0 (0.12) B 10.0 (0.40) <b>A-5000-4154</b> A 4.0 (0.16) B 10.0 (0.40)					<b>(keményfém)</b> <b>A-5003-0033</b> A 1.0 (0.04) B 20.0 (0.79) <b>A-5000-8663</b> A 1.0 (0.04) B 27.5 (1.08) <b>A-5004-3404</b> A 2.0 (0.08) B 30.0 (1.19) <b>A-5003-4177</b> A 3.0 (0.12) B 30.0 (1.19) <b>A-5003-7852</b> A 3.0 (0.12) B 30.0 (1.19)					<b>(szénsszál)</b> <b>A-5003-3877</b> A 3.0 (0.20) B 40.0 (1.58) <b>A-5004-7589</b> A 1.5 (0.06) B 11.0 (0.44) <b>A-5004-7590</b> A 3.0 (0.12) B 13.0 (0.52) <b>A-5000-8877</b> A 1.5 (0.06) B 15.0 (0.60) <b>A-5000-7812</b> A 2.0 (0.08) B 20.0 (0.79)					<b>(rozsdamentes acél)</b> <b>A-5004-7610</b> B 5.0 (0.20) <b>A-5004-7585</b> B 10.0 (0.40) <b>A-5004-7586</b> B 20.0 (0.79) <b>A-5004-7611</b> B 40.0 (1.58)					<b>(kerámia)</b> <b>A-5003-0070</b> B 30.0 (1.19) <b>A-5003-0072</b> B 50.0 (1.97) <b>A-5003-2280</b> B 40.0 (1.58) <b>A-5003-2283</b> B 90.0 (3.55)									

## M4 menetes tapintószárak

Rubingömb-végű tapintószárak										Szilícium-nitrát gömb végű tapintószárak										Cirkóniumgömb-végű tapintószárak										Tapintószár hosszabbítók									
<b>(rozsdamentes acél)</b> <b>A-5000-3551</b> A 1.0 (0.04) B 21.0 (0.83) <b>A-5000-3552</b> A 2.0 (0.08) B 21.0 (0.83) <b>A-5000-3553</b> A 3.0 (0.12) B 21.0 (0.83) <b>A-5000-7606</b> A 4.0 (0.16) B 21.0 (0.83)					<b>(szénsszál)</b> <b>A-5003-3554</b> A 4.0 (0.16) B 31.0 (1.23) <b>A-5003-4860</b> A 6.0 (0.24) B 27.5 (1.08) <b>A-5003-4862</b> A 8.0 (0.32) B 27.5 (1.08) <b>A-5003-4861</b> A 3.0 (0.12) B 100.0 (3.94) <b>A-5003-4863</b> A 8.0 (0.32) B 100.0 (3.94)					<b>(rozsdamentes acél)</b> <b>A-5003-5723</b> A 2.0 (0.08) B 100.0 (3.94) <b>A-5003-5725</b> A 4.0 (0.16) B 50.0 (1.97)					<b>(szénsszál)</b> <b>A-5003-5737</b> A 4.0 (0.16) B 21.0 (0.83) <b>A-5003-5740</b> A 6.0 (0.24) B 21.0 (0.83)					<b>(rozsdamentes acél)</b> <b>A-5004-7609</b> B 10.0 (0.40) <b>A-5004-7583</b> B 20.0 (0.79) <b>A-5004-7584</b> B 35.0 (1.38) <b>A-5003-0075</b> B 50.0 (1.97) <b>A-5003-4864</b> B 75.0 (2.96)																			

## M5 menetes tapintószárak

Tapintószár hosszabbítók										Rubingömb-végű tapintószárak										Szerszámbemérő tapintószárak										Törőelemek										SPRINT stílus										OMP 400/RMP 600 tapintószárak										MP700 tapintószárak										Tapintószár hosszabbítók									
<b>(szénsszál)</b> <b>A-5555-0662</b> B 180.0 (7.09)					<b>(szénsszál)</b> <b>A-5003-5251</b> A 8.0 (0.32) B 75.0 (2.96) <b>A-5003-5262</b> A 8.0 (0.32) B 100.0 (3.94) <b>A-5003-5265</b> A 6.0 (0.24) B 150.0 (5.91) <b>A-5003-5269</b> A 8.0 (0.32) B 200.0 (7.88)					<b>(keményfém)</b> <b>A-5003-5204</b> A 1.0 (0.04) B 20.0 (0.79) <b>A-5003-5218</b> A 3.0 (0.12) B 30.0 (1.19) <b>A-5003-5224</b> A 3.0 (0.12) B 40.0 (1.58) <b>A-5003-5236</b> A 5.0 (0.20) B 50.0 (1.97)					<b>(kerámia)</b> <b>A-5004-4472</b> A 6.0 (0.24) B 100.0 (3.94) <b>A-5004-6463</b> A 2.0 (0.08) B 80.0 (3.15) <b>A-5004-6470</b> A 6.0 (0.24) B 100.0 (3.94) <b>A-5004-6467</b> A 2.0 (0.08) B 80.0 (3.15) <b>A-5003-7306</b> A 6.0 (0.24) B 50.0 (1.97)					<b>(szénsszál)</b> <b>A-5003-6510</b> B 100.0 (3.94)					<b>(szénsszál)</b> <b>A-5003-1436</b> A 6.0 (0.24) B 50.0 (1.97) <b>A-5003-1358</b> A 6.0 (0.24) B 100.0 (3.94) <b>A-5004-7599</b> B 10.0 (0.40) <b>A-5004-7601</b> B 20.0 (0.79) <b>A-5004-7602</b> B 30.0 (1.19)					<b>(rozsdamentes acél)</b> <b>A-5000-7754</b> B 30.0 (1.19) <b>A-5000-7755</b> B 50.0 (1.97) <b>A-5000-7727</b> B 100.0 (3.94)																																																	

**Félgömbös tapintószár**  
(kerámia)  
A-5003-5275 A 16.0 (0.63) B 19.5 (0.77)  
A-5003-5277 A 30.0 (1.19) B 24.5 (0.97)

**Tárcsás tapintószárak**  
(ezüstacél)  
A-5003-5288 A 12.0 (0.48) B 3.0 (0.12)  
A-5003-5290 A 35.0 (1.38) B 5.0 (0.20)

**Csuklók, kockák és csavarok**  
(rozsdamentes acél)  
A-5003-5278 B 36.5 (1.44)  
A-5003-5676 B 33.0 (1.30)  
A-5555-0194 B 20.0 (0.79)

**Rubin mikrogömbös tapintószárak**  
(keményfém)  
A-5003-5201 A 0.3 (0.012) B 20.0 (0.79)  
A-5003-5227 A 0.7 (0.03) B 50.0 (1.97)  
A-5003-5233 A 2.5 (0.10) B 50.0 (1.97)

## Kiegészítők

Tapintószár csuklók		Tapintószár közepek		Szerelőszerszámok tapintószárakhoz		Adapterek	
A-5000-7534 M2 thread size B 8.0 (0.32)	A-5000-7616 M2 thread size B 12.0 (0.48)	A-5000-3627 M2 thread size B 7.5 (0.30)	A-5000-7610 M3 thread size B 13.0 (0.52)	A-5003-2300 M2 carbon fibre range	A-5004-7587 M4 thread size	A-5004-7595 M4/M2 B 5.0 (0.20)	A-2054-6350 M4/M2 B 10.0 (0.40)
A-5555-0226 M5/M2 B 10.0 (0.40)							



KÖZVETLEN ELÉRHETŐSÉGEK