


# Custom stylus request form OPTiMUM™ diamond styli

Please complete the form and send it back to us. Our design team will review the supplied information and present you with a solution for your application.

Customer _____	Customer email _____
Company _____	Customer telephone _____



**Ball diameter**  
 1.5 mm    2 mm    2.5 mm    3 mm    4 mm    5 mm    6 mm    7 mm    8 mm  
 \* Actual ball diameter will be supplied 0.03 mm oversize due to the coating.

**Thread**  
 M2    M3    M4    M5    Other    Please specify \_\_\_\_\_

**Length** \_\_\_\_\_    **EWL** \_\_\_\_\_

**Stem material**  
 Stainless steel    Tungsten carbide    Ceramic    Carbon fibre

**Quantity** \_\_\_\_\_

**Probe information**  
 Type of probe \_\_\_\_\_    Scanning    Touch trigger

**Additional information**

---



---



---



---



---