

Custom vision plate request form



Please complete this form and send it back to us. Our design team will review the supplied information and present you with a solution for your application. **Important: Any missing information will delay your quotation.**

Renishaw office _____ Company (end user) _____ Date _____	Renishaw contact name * _____ Renishaw contact email * _____
--	---

* This person will receive the quotation and approval drawings

Machine make _____	Machine model _____
---------------------------	----------------------------

Required for quote		Dimensions given are: Metric (mm) <input type="checkbox"/> Imperial (in) <input type="checkbox"/>
Plate size	Width (X) _____ Length (Y) _____	
	Recommended thread spacing	
Plate thread size	M4 <input type="checkbox"/> 10 mm <input type="checkbox"/> 20 mm <input type="checkbox"/>	
	M6 <input type="checkbox"/> 12.5 mm <input type="checkbox"/> 25 mm <input type="checkbox"/>	
	Other _____	
Is the plate required for use with a Renishaw QLC/IVF? Yes ¹ <input type="checkbox"/> No <input type="checkbox"/>		
		¹ If yes, please indicate the part number _____
Number of plates required _____		
Plate type: You must fill in either (1) or (2) below.		

(1) Multi-hole <input type="checkbox"/> Is a clear centre section required? Yes ² <input type="checkbox"/> No <input type="checkbox"/> ² If yes, please specify a size: (A) _____ (B) _____ <small>Note: If "yes" is selected and no values are given, our design engineers will recommend a suitable clear section.</small>	(2) Multi-window <input type="checkbox"/> How many clear sections are required? _____ <small>Note: If you do not provide a sketch with this form, our design engineers will recommend suitable clear section sizes.</small>
	

Additional information _____ _____ _____	INTERNAL USE ONLY Part number _____ Order number _____ S/O number _____
--	---