

# Mould and die manufacturing: reduce operator intervention and increase machine productivity



## **Overview**

Company information	BK Tooling is a precision toolmaker specialising in the manufacture of high-quality plastic injection mould tools.		
	The company, based in Bishops Stortford (UK) was established over 30 years ago. Its main markets are the medical, leisure, industrial automotive and electrical sectors.		
Products and services	Mould design, moulding analysis, rapid tooling and production mould manufacture using a range of machining technologies, low-volume injection moulding.		
Industry standards	Kaizen	Six Sigma and standardisation	
Company	To work with customers to deliver mould tools and services that exceed expectations, achieving this through a combination of experience and the use of the latest manufacturing technology.		
objectives	To serve industries that require low to medium volumes of injection mouldings and/or have concerns about their IP security.		

### **Process**

BK Tooling is focused on highquality one-off manufacturing. Typically moulds produced are for research, development and prototype work. Once the mould tool has been machined using XYZ high-speed machining centres, modification and rework may be required as part of the development process. To re-set mould tools on the machine, it is vital that datum points can be accurately and quickly located prior to continuing the machining process.

### Challenges

Improve accuracy

To ensure accurate part setting and repositioning of highly complex mould tools for any subsequent machining work, which without probing could be limited to an accuracy of  $\pm 0.03$  mm.



### Eliminate human error and reduce scrap

Maximise machine time by reducing the time required to reset mould tools. Without probing this could take many hours, depending on the complexity of the form.



### **Process considerations**

Renishaw engineers considered key elements within BK Tooling's process and production stages of manufacturing using Renishaw's *Productive Process Pyramid<sup>TM</sup>*. This framework is used to identify and control the variations that can occur at key stages of the machining process.

For more information, please visit the **When do I probe?** section of the Renishaw website: www.renishaw.com/whendoiprobe

### Informative controls applied after machining is complete Postprocess monitoring Active controls applied during metal cutting In-process control Predictive controls applied just before cutting Process setting Preventative controls applied in advance Process foundation

**Productive Process Pyramid** 

### **Solutions**

### Manufacturing process focus: process setting

Focusing on process setting, Renishaw engineers introduced measures to increase automation and eliminate manual intervention.

The introduction of automated on-machine part set-up using Renishaw probes enables BK Tooling to:

- Ensure accurate setting and repositioning of highly complex mould tools for any subsequent machining work to an accuracy of ±0.01 mm.
- Reduce the time required to re-set mould tools by many hours.

Automated on-machine tool setting has also delivered a significant improvement, enabling multiple tools with different forms and radii to accurately blend on the mould tool profile.

This has been a vital step in reducing the amount of handfinishing required.



The images above show a Renishaw Primo Radio Part Setter (left) in use on an XYZ high-speed vertical machining centre whilst setting a 3D mould. The Primo Radio 3D Tool Setter (right) is used to automatically set tool lengths and diameters.

#### 2. Automated component setting



#### 1. Manual component setting





# **Results**

These charts provide a typical illustration for this industry application where tool setting and probing has been introduced.

Reduced component setting tir	Without probing	With probing	Saving/reduction	
11 3 mins	Time (each)	60 mins	3 mins	95% 57 min
10 2*	Time (annual) (twice per week)	100 hours	5 hours	95%
-9 60 mins	Machine time cost	100	100	95 hours -
7 6 5	Total setting time cost US\$	10,000	500	9,500

\* The example above is based on setting up a mould tool for secondary machining

### Improved accuracy and repeatability





# Summary

Process controls applied to mould and die machining through the use of Renishaw probing systems have significantly reduced both component setting and tool setting times for BK Tooling. In addition to the improvements to its efficiency, the company and its customers benefit from increased confidence in precision and quality.

Through a combination of experience and use of the latest technology, BK Tooling has gained wide recognition as a highly competent partner in a challenging and demanding industry sector.

Renishaw probes applied to mould and die machining have helped BK Tooling to:

- · Eliminate uncertainty and variation associated with manual methods
- Improve accuracy, repeatability and quality
- · Introduce other in-process controls in addition to process setting

### Contact

To find out how you could benefit from our process control solutions, contact us today – find your local office at www.renishaw.com/contacts

### **Customer comment**

When we first used a Renishaw probe, some 20 years ago, we didn't recognise the value of it. Now we realise that it is a vital piece of equipment. There would be no argument; any CNC machine tools that we buy have to be equipped with probing. We can't understand why some companies, particularly toolmakers, still try to operate without it.



**BK Tooling (United Kingdom)** 

### **Best practice**

Productive Process Patterns<sup>™</sup> from Renishaw provide guidance on best practice and the implementation of a wide range of probing solutions.

For more information regarding job set-up and other applications, visit www.renishaw.com/processcontrol



#### Renishaw plc

New Mills, Wotton-under-Edge Gloucestershire, GL12 8JR United Kingdom

T +44 (0) 1453 524524 F +44 (0) 1453 524901 E uk@renishaw.com

www.renishaw.com



### About Renishaw

Renishaw is an established world leader in engineering technologies, with a strong history of innovation in product development and manufacturing. Since its formation in 1973, the company has supplied leading-edge products that increase process productivity, improve product quality and deliver cost-effective automation solutions.

A worldwide network of subsidiary companies and distributors provides exceptional service and support for its customers.

### Products include:

- · Additive manufacturing and vacuum casting technologies for design, prototyping, and production applications
- · Dental CAD/CAM scanning systems and supply of dental structures
- · Encoder systems for high-accuracy linear, angle and rotary position feedback
- · Fixturing for CMMs (co-ordinate measuring machines) and gauging systems
- · Gauging systems for comparative measurement of machined parts
- · High-speed laser measurement and surveying systems for use in extreme environments
- · Laser and ballbar systems for performance measurement and calibration of machines
- · Medical devices for neurosurgical applications
- · Probe systems and software for job set-up, tool setting and inspection on CNC machine tools
- · Raman spectroscopy systems for non-destructive material analysis
- · Sensor systems and software for measurement on CMMs
- · Styli for CMM and machine tool probe applications

### For worldwide contact details, visit www.renishaw.com/contact



RENISHAW HAS MADE CONSIDERABLE EFFORTS TO ENSURE THE CONTENT OF THIS DOCUMENT IS CORRECT AT THE DATE OF PUBLICATION BUT MAKES NO WARRANTIES OR REPRESENTATIONS REGARDING THE CONTENT. RENISHAW EXCLUDES LIABILITY, HOWSOEVER ARISING, FOR ANY INACCURACIES IN THIS DOCUMENT.

\*H-2000-3863-01\*

© 2016 Renishaw plc. All rights reserved. Renishaw reserves the right to change specifications without notice. **RENISHAW** and the probe symbol used in the RENISHAW logo are registered trade marks of Renishaw plc in the United Kingdom and other countries. **apply innovation** and names and designations of other Renishaw products and technologies are trade marks of Renishaw plc or its subsidiaries. All other brand names and product names used in this document are trade names, trade marks or registered trade marks of their respective owners.

Part no.: H-2000-3863-01-A Issued: 11.2016