

Five-axis CMM inspection lets "good times roll" in QC department at small engine plant



Background

Scanning probes speed form-data collection and feedback to machining cells, reduce CMM fixturing and cut probe calibration time from hours to minutes at Kawasaki's Maryville, MO plant. Increased measurement throughput and flexibility allow faster feedback to manufacturing and R&D department, while scanning CMMs may ultimately eliminate inspection systems for gears and cam lift.

Maryville, MO – Kawasaki encourages motorcycle enthusiasts to "let the good times roll," but good times of another sort are rolling at the company's Maryville, MO small engine plant, where two 5-axis scanning probe systems are slashing CMM inspection and probe calibration times, and speeding up QC feedback for machining of small engine components. The 5-axis Renishaw REVO systems, installed on Mitutoyo Crysta-Apex 121210 CMMs, replaced two PH10 articulating heads using SP25 scanning probes on traditional 3-axis CMMs. The REVO-equipped CMMs have cut inspection times by half or more on scanning intensive applications, eliminated the need for custom probe configurations, cut probe calibration times from six to seven hours to about 45 minutes, and added new capability to collect large amounts of form measurement data, improving part quality. Of primary importance, the REVO systems have greatly increased inspection throughput, data quality and flexibility of the QC department, enhancing its value as a strategic support asset to both manufacturing and R&D

The Kawasaki Production System

Kawasaki's 800,000 square-foot Maryville plant, opened in 1989, produces single and twin-cylinder air-cooled or watercooled engines, 1000 cc or smaller, for commercial and consumer lawnmower OEMs, as well as for a sister plant that manufactures ATVs and Mule[™] utility vehicles. Operations at Maryville include aluminium die-casting, plastic injection moulding, extensive amounts of machining, painting and assembly. All engines – approximately 500,000 per year – are run-off before shipping as well.

"We use the Kawasaki Production System (KPS)," said JC Watts, Quality Control Technical Group Supervisor at the Maryville plant. "Our quality and engineering requirements are comparable to the best in the automotive industry, though our manufacturing is focused on lower volumes of many kinds of products." The plant has 50 machining lines, typically arranged in a U-cell pattern with start and end machines across from each other. The REVO scanning capability allows us to catch form errors much more quickly, without a time penalty on our inspections. It has definitely made us more proactive in catching quality problems early in the game.

Kawasaki (USA)

"Primarily, it's one piece production with machining lines running a part through multiple processes at a high rate," Watts explained. Kawasaki utilizes automation in many die cast and some machining operations, accomplished through the integration of Kawasaki robots. On one of the crankcase lines, robots load raw materials and unload finished parts that are placed into inventory for assembly to draw upon. Machined parts include aluminium, cast iron and steel.

"We're running similar tolerances that automotive powertrain uses for high-end products, and there are probably four or five critical processes for our aluminium parts and 15 for the steel parts," Watts added. It is not uncommon to find tolerances "in single digits in microns" for form, and 0.05 mm true position.

The QC lab is responsible for inspecting 125 different massproduced parts, as well as vendor parts and those produced for engineering development. The environmentally controlled lab is located adjacent to the machining lines, and parts intended for routine inspection are delivered on carts or via train (an electric vehicle towing several trolley carts). Critical components may be hand delivered for priority inspection during a line changeover or if an operator suspects a problem.



REVO head inspecting a FX series small engine flywheel

5-axis scanning advantage

"When I started here, we had a couple of 3-axis CMMs with PH10 articulating heads and SP25 probes, and another CMM with a fixed probe head," Watts explained. "We were frustrated with having to make probe configurations and being limited to what we could do even with the articulated heads. We had so many different probe configurations that calibration times of six to seven hours took a bite out of our inspection throughput, too. We wanted to do better than what the industry considered the norm, so we looked at several options and the 5-axis REVO system appeared to be the fastest and most flexible available. It was the best fit for our requirements." Kawasaki bought a new Mitutoyo Crysta-Apex 121210 in 2009 with the REVO system installed from the factory, and retrofitted an identical machine in 2010, after the first machine was up and running with all the part programs.

The REVO 5-axis scanning probe head can collect up to 6000 data points/sec. It is engineered for high-speed precision measurement of contoured surfaces and complex geometries requiring high-volume data collection to validate fit and form with high accuracy. It uses two rotary axes, one in the vertical plane and one in the horizontal, for infinite rotation and positioning. Five-axis software drives the measuring head and synchronizes its motion with the linear axes of the CMM. Look-ahead algorithms drive the probe path and CMM in coordinated continuous motion. The head adapts position while measuring on the move, maintaining stylus tip contact with changing contours at scanning speeds of up to 500 mm/ sec.

"Though our SP25s were scanning probes, we were doing 95 percent touch probing because scanning was too slow with a 3-axis CMM," Watts explained. "Our cylinder and crank bores are probably the best examples of where we believed touch probing was inadequate.

To accurately collect enough data points to measure the geometry of a bore 80 to 100 mm in diameter and 150 mm in length, the SP25 probe took so long we limited those inspections to machine set up or special requests from our design department. Now on every crank case we measure, the REVO does a spiral scan of bores and the system outputs the values to software. We also send a graph of the data points to our network that can be used by anyone in QC, engineering or production, and it helps troubleshoot problems. You can VISUALIZE the problem. What would take 3-4 minutes with an SP25, we're measuring in 10 seconds with the REVO." The REVO scanning heads have all but eliminated the need for touch probing. Now 95 percent of inspections utilize scanning, with no "time penalty" as before, allowing Kawasaki to collect so much data that it challenges the speed of computers doing the analysis. The REVO probe can also do "head touch" probing or be used for traditional machine-touch probing when the situation calls for touches.



REVO-equipped CMMs at Kawasaki's, Maryville



"With scanning inspections, our production and engineering people have a lot more confidence that the data is valid," Watts added. "With touch probing it is easy to get one speck of dirt that causes an out-of-round condition if you're only sampling seven or eight points. It can throw the location of that circle off. We have specific documented examples of where there were flatness errors we would not have caught with touch probing, and cylinder bore geometries that would not have been caught with touch probing because of the amount of data sampled with the touch probe. We still caught these problems before they left the plant, but the parts were scrap. The REVO scanning capability allows us to catch form errors much more quickly, without a time penalty on our inspections. It has definitely made us more proactive in catching quality problems early in the game."

Fewer probe configurations, more flexibility

With REVO, the Maryville operation now has two probe configurations that measure all of its mass production parts, reserving custom probes in a changing rack for a few special applications. Special configurations for vendor parts have also been eliminated because the infinite positioning angles of REVO allow measuring of a part without special fixturing or consideration of which probe to use. With so few probes, calibration time has dropped to around 46 minutes. Now QC technicians monitor the calibration instead of calibrating every shift.

"We are now able to measure all our mass production parts with just two probe configurations," said Watts. "We were able to eliminate the large ball stylus configurations because of the large approach angle the REVO creates between the stylus and the work piece. During scanning the REVO maintains the approach angle which allows a large cylindrical feature such as a cylinder bore to be measured with the same stylus used for measuring a 5mm bore, with no chance of shanking the stylus."

Flexibility of the REVO system has also proven to be a timesaver for Kawasaki. "We can measure any part on either machine with a limited amount of fixturing and no special calibrations," said Watts. "We measure all our parts on three types of fixturing. The REVO probe orients itself to the part after it's initially aligned. The utilization of special fixtures has almost been eliminated, without concerns of measurement error due to part alignment."

Kawasaki programs all its inspection routines in-house using Mitutoyo's Mcosmos 3.1 software. The upgrade to REVO instigated a shift to parametric and modular programming of inspection routines through in-house development of coding. This allows a program to be used for a part family. "We might have 30 different crankshafts, for example, but because everyone has the same features, only in a different size or location, we can use the same inspection program to measure all the parts," Watts stated. "That's one of the big advantages we gained." Infinite angles of the REVO system make it simple to create parametric programs because there is no concern about the stylus interfering with a part feature, due to size or orientation of the feature. The probe automatically aligns normal to the feature being measured, simplifying programming.



REVO in action

Faster inspection, better data from QC to R&D

Watts says the transition from 3-axis to 5-axis programming is not difficult, and a programmer with limited ability can still program REVO inspections as 3-axis. However, when it comes to optimizing speed of inspection, it is critical to use head motion as much as possible. "This allows you to scan parts the quickest, without inducing measurement error," he added. "REVO opens up a lot of possibilities, with few limitations, so speed gains are obtainable for both the higher and lower skilled programmers."

Inspection results may be relayed to the machining lines manually or they can be accessed locally by line operators over a computer network. "Some of our inspection reports supply offsets directly back to the machining centers coordinate system; this allows the CNC operator to read the offset adjustment right off the report, allowing no misinterpretation of what offsets the operator needs to input," Watts explained. "We take advantage of some of the 'best fit' algorithms and work with our production engineers, especially on parts that require more complex algorithms to get the adjustment right, and to utilize multiple process adjustments simultaneously. We had limited ability to do this before the REVO; the REVO allowed us to utilize parametric programming, which in turn allowed us to expand our capability across the board more easily.

The REVO scanning capability allows us to utilize parametric programming, which in turn allowed us to expand our capability across the board more easily.



For more information visit, www.renishaw.com/kawasaki

Renishaw plc

New Mills, Wotton-under-Edge Gloucestershire, GL12 8JR United Kingdom

T +44 (0) 1453 524524 F +44 (0) 1453 524901 E uk@renishaw.com

www.renishaw.com

For worldwide contact details, visit www.renishaw.com/contact

RENISHAW HAS MADE CONSIDERABLE EFFORTS TO ENSURE THE CONTENT OF THIS DOCUMENT IS CORRECT AT THE DATE OF PUBLICATION BUT MAKES NO WARRANTIES OR REPRESENTATIONS REGARDING THE CONTENT. RENISHAW EXCLUDES LIABILITY, HOWSOEVER ARISING, FOR ANY INACCURACIES IN THIS DOCUMENT.

© 2017 Renishaw plc. All rights reserved. Renishaw reserves the right to change specifications without notice. RENISHAW and the probe symbol used in the RENISHAW logo are registered trade marks of Renishaw plc in the United Kingdom and other countries. apply innovation and names and designations of other Renishaw products and technologies are trade marks of Renishaw plc or its subsidiaries. All other brand names and product names used in this document are trade names, trade marks or registered trade marks of their respective owners.



Part no.: H-5650-3148-01-A Issued: 04.2012