


Defence & aerospace supplier would not operate a machine without probes


Customer:

Mekall

Industry:

Precision manufacturing

Challenge:

Minimise process development time, and maintain stable automated processes in the manufacture of high-accuracy components.

Solution:

HAAS machine tools equipped with Renishaw touch-trigger probing solutions.

Mekall, a Scottish manufacturing services group uses HAAS machine tools, each one fitted with Renishaw touch probes, to service clients in the defence, aerospace, medical and telecommunications markets. Tom Forsyth, managing director of Mekall's Machining Division (previously named Fortec), cannot understand why anyone would buy a CNC machine tool without Renishaw probes. He has 12 HAAS machines, all fitted with spindle mounted probes for part setting, and feels well equipped to expand Mekall's subcontract work.

When touch probes were first introduced total machining cycle times were reduced, with setting times cut dramatically and the whole process made highly repeatable. Simultaneously process development times were significantly reduced. As Tom Forsyth comments, "We've brought in time-served skilled engineers who've never seen probing before and left them goggle-eyed!"

Now a key supplier to a growing number of clients in the defence, aerospace, medical and telecommunications markets, Mekall is also the manufacturing partner and supplier to sister company Teknek, a world leader in contact sheet cleaning and web cleaning machinery, with over 15,000 installations worldwide, including many of the world's

leading manufacturing facilities. Teknek systems improve yields substantially in manufacturing applications such as surface-mount technology (SMT), printed circuit board (PCB), automotive glass, solar energy and converting/printing. A recent installation is at one of Sony's European plants where it manufactures surface-mount technology (SMT) boards for various Sony flat screen televisions.

Renishaw probes are critical when machining castings. We've done jobs that if set manually would have added a day's work. Knowing you have the probe shortens the development time considerably, removing the need to design and develop fixtures, since you don't need to position the part accurately.

Mekall (UK)
The main benefit is the certainty

Mekall use Renishaw touch probes on its HAAS machines to control the process. As Mr Forsyth says, "It gives us consistency and takes out the chance of human error. Scrap reduction is not even an issue we have to consider." When parts are loaded for machining the probe is used to measure the position of datum features in a matter of seconds. Machining can start immediately with no manual setting.

Mekall know how important the repeatability of the probing process can be. Before fitting the first touch probe systems to



Sister company Teknek supplies Sony with SMT cleaning machines for flat screen TV production

machine tools, they had big problems on a very accurate job for Thales. The position of machined features could vary by up to 0.1mm over the course of a shift, which was all down to operator error.

Time savings and automation of manual tasks

“Probes are critical when machining castings”, says Mr Forsyth. “We’ve done jobs that if set manually would have added a day’s work. The casting for a BAE Systems Challenger tank needed us to use a skewing function to rotate the whole coordinate system, using the positioning data gathered with the probe. The thin walls on the casting meant that you had to pick up on the feature itself, and with 50 datum features to check it would have been a huge manual task.”

Intelligent decision making

The data the touch probe provides can also be used to provide feedback so that the machine makes ‘intelligent decisions’. Mekall use routines that check for mis-load by finding the position of certain features. The program will not run if it detects a surface in the wrong place or cannot find a feature.

Rapid process development

Mr Forsyth continues, “Knowing you have the probe shortens the development time considerably, removing the need to design and develop fixtures, since you don’t need to



Mekall machined parts can be clearly seen on Teknek SMT cleaning machines

position the part accurately. Simple clamping is used and an approximate location is all that is needed for the probe to find and set the part. We’ve been able to standardise the work-holding system across all the machines.

He adds, “The probe moves are very quick and easy to program. We add single lines of NC macro commands into the programs produced by our CAM system.” Mekall use a Solidworks CAD/CAM system, importing drawings and CAD models in the various formats their customers supply ready to plan the machining routines, then quickly adding the probe moves afterwards.

HAAS machines - “capable and easy to use”

Mekall use HAAS machine tools exclusively, with 10 VMCs and 2 turning centres. There are several reasons for this, firstly that Tom Forsyth wanted to standardise on the HAAS control, which he finds very capable and easy to use. Another critical requirement was maintenance, which Mekall does in-house. Explains Mr Forsyth, “Support can all be done over the phone. Our engineers fit replacement parts, make adjustments and downtime is kept to an absolute minimum. In 15 years we’ve not had a single issue.”



Mekall has standardised on HAAS machine tools with 10 VMCs and 2 turning centres

Mekall - a 'one-stop-shop' company with multiple processes

With manufacturing facilities throughout the UK, Mekall is a diverse company, capable of prototyping and design, right through to volume manufacture. It can manufacture a broad range of components with a particular focus on sheet metal fabrication, membrane keypad manufacture and CNC milling, as well as a specialist finishing division for metals and plastics.

With years of relevant experience, Mekall now aims to double or triple the company turnover, particularly with the machining of aerospace parts. Batch sizes can vary from one-offs to 200 or more, in a variety of materials. The company has the capability for jobs from Ø1.5 mm up to Ø250 mm and prismatic parts up to 1.25 m long, with 5 machines capable of doing the larger jobs. With rapid process development, stable and predictable processes and automated machines, Mekall is well placed to compete for high-accuracy work.



Tom Forsyth holds a part for a Teknek SMT cleaning machine

For more information, visit www.renishaw.com/mekall

Renishaw plc
New Mills, Wotton-under-Edge
Gloucestershire, GL12 8JR
United Kingdom

T +44 (0) 1453 524524
F +44 (0) 1453 524901
E uk@renishaw.com
www.renishaw.com

For worldwide contact details, visit www.renishaw.com/contact

RENISHAW HAS MADE CONSIDERABLE EFFORTS TO ENSURE THE CONTENT OF THIS DOCUMENT IS CORRECT AT THE DATE OF PUBLICATION BUT MAKES NO WARRANTIES OR REPRESENTATIONS REGARDING THE CONTENT. RENISHAW EXCLUDES LIABILITY, HOWSOEVER ARISING, FOR ANY INACCURACIES IN THIS DOCUMENT.

© 2017 Renishaw plc. All rights reserved.

Renishaw reserves the right to change specifications without notice.

RENISHAW and the probe symbol used in the RENISHAW logo are registered trade marks of Renishaw plc in the United Kingdom and other countries. **apply innovation** and names and designations of other Renishaw products and technologies are trade marks of Renishaw plc or its subsidiaries. All other brand names and product names used in this document are trade names, trade marks or registered trade marks of their respective owners.



H - 5650 - 3044 - 01

Part no.: H-5650-3044-01-B
Issued: 02.2017