

Metal 3D printing pushes the boundaries in Moto2[™] through defiant innovation



Customer: TransFIORmers

Industry: Automotive

Challenge:

Reduce unsprung mass and achieve an overall weight reduction in Moto2 bike design.

Solution:

An optimised design using Renishaw's AM250 manufacturing system.

In the high-octane world of MotoGP[™] motorcycle racing, technical enhancements can have a big impact. Race winning Moto2 team TransFIORmers is using cutting edge additive manufacturing (metal 3D printing) technology in an unconventional front suspension system to gain a significant competitive advantage.

suspension system was inspired by the seminal work of the legendary French motorbike designer Claude Fior.

Boudinot's former friend and mentor, Fior, recognised the gains to be made from isolating the front suspension from steering forces. Resolving issues of 'brake dive', the design enables later braking into a corner and faster acceleration out.

Background

Motorcycles ridden in the MotoGP World Championships are special; the general public can't buy them and they can't be used on a public road. As prototype racing bikes they are custom-built to outdo their rivals and maximise performance on the track. The weight reduction that metal 3D printing has achieved for us in our wishbone component has enabled us to bypass traditional weight transfer phenomenon and the problems associated with 'brake dive'. More than that, it's allowed us to design a part that is not only lighter, but far more rigid at the same time.

TransFIORmers (France)

Moto2, the second of the three MotoGP classes, was created in 2010. Its official engine is a 600cc four-stroke production engine, currently supplied by Honda. The French Moto2 team TransFIORmers, based in Perigueux, South West France, is revolutionising front suspension design in order to stay ahead of the pack.

TransFIORmers is led by former 250cc World Championship rider Christian Boudinot, and the team's unconventional

Instead of the more traditional telescopic front fork suspension, the TransFIORmers motorcycle employs a rigid front fork suspension system separated from the chassis using two wishbones.

To further advance the development of its innovative design, TransFIORmers approached I3D Concept, a world-class expert in metal additive design and manufacturing techniques.



Original twelve part steel component

Using Renishaw's AM250 additive manufacturing system, I3D Concept worked in partnership with the TransFIORmers team to optimise the design of its upper wishbone component, one of two attaching the front fork to the chassis and critical to the bike's steering.

Challenge

In the development of new components in Moto2 bike design, achieving a weight reduction is a priority. In particular, reducing the 'unsprung mass' of the bike is a key consideration. The lower the unsprung mass, the better the suspension is in terms of vibration management and responsiveness to both braking and acceleration.

Of equal importance is the speed with which the design of a new component can be modified, and how long it takes to remanufacture. Achieving perfection in a highly competitive environment demands fast, accurate component iteration.

In a high reliability environment, mechanical strength is a further prime consideration. The TransFIORmers' wishbone component needs to assure best possible rigidity, while handling significant levels of dynamic steering force.

"To improve overall motorcycle performance, reducing the weight of all components located behind the shock absorbers is absolutely vital. Failure to optimise component weights can have an adverse effect on vibration, braking and acceleration, so weight reduction is a really high priority", says Jérôme Aldeguer, TransFIORmers.



Metal 3D printed one part titanium component

Solution

TransFIORmers' original wishbone component was handfabricated in steel, with the assembly comprising twelve separately machined and welded parts. I3D Concept consolidated the design into a single piece component, greatly reducing assembly time.

The company produced the metal 3D printed wishbone using a Renishaw AM250 additive manufacturing system; initially prototyping in stainless steel (inox) and finally manufacturing a lighter weight part in titanium.

Key to the new 3D component design was an iterative process of topological optimisation, whereby the wishbone layout was successively rationalised in software within tight space constraints to withstand a set of predefined front fork loading conditions.

Once the final component design was validated using digital CAD software, the build preparation file was prepared offline prior to export to the additive manufacturing system.

Within the CAD software, I3D Concept was able to assess whether the parameters were effectively predetermined or whether they required tweaking to match the specific metal powder characteristics and the complex target geometries of the TransFIORmers wishbone.

Importantly, using the AM250's dedicated Optical Control System (OCS) software, I3D Concept was able to very accurately control laser steering which helped to enhance precision, definition of features and surface finish.



CAD development of additively manufactured titanium component

Results

By taking an additive manufacturing approach to Moto2 bike design, TransFIORmers succeeded in dramatically reducing the weight of its critical wishbone front suspension component by a factor of 40%. Comparing the one-piece titanium component with the original welded steel component, a weight saving of 600g was achieved.

Metal 3D printing has also provided TransFIORmers with much finer control over component tolerances and the flexibility to very quickly iterate wishbone geometries to match specific chassis and kinematic requirements.

"The weight reduction that metal 3D printing has achieved for us in our wishbone component has enabled us to bypass traditional weight transfer phenomenon and the problems associated with 'brake dive'. More than that, it's allowed us to design a part that is not only lighter, but far more rigid at the same time", explains Jérôme Aldeguer, TransFIORmers.

With an ultimate tensile strength in excess of 1100 MPa when processed using additive manufacturing, and near perfect 99.7% densities, the titanium Ti6AI4V alloy used has delivered a radical new wishbone offering far greater rigidity than the original multi-part, hand-assembled steel component.

Thanks to additive manufacturing, TransFIORmers' prototype wishbone development has become a highly efficient and cost effective process. Extensive part machining and assembly time overheads have been removed and design iterations and manufacturing have been made many times faster.

In June 2016, the team won its first ever Moto2 GP race at the CEV event in Barcelona.



Metal 3D printed one part titanium component on the TransFIORmers bike



TransFIORmers race bike



The team analysing the bike's characteristics



Christian Boudinot working on the race bike





TransFIORmers competing at CEV Moto2 GP in the European championship

For more information and to watch the video visit, www.renishaw.com/transfiormers

Renishaw plc

New Mills, Wotton-under-Edge Gloucestershire, GL12 8JR United Kingdom

T +44 (0) 1453 524524 F +44 (0) 1453 524901 E uk@renishaw.com

www.renishaw.com

RENISHAW HAS MADE CONSIDERABLE EFFORTS TO ENSURE THE CONTENT OF THIS DOCUMENT IS CORRECT AT THE DATE OF PUBLICATION BUT MAKES NO WARRANTIES OR REPRESENTATIONS REGARDING THE CONTENT. RENISHAW EXCLUDES LIABILITY, HOWSOEVER ARISING, FOR ANY INACCURACIES IN THIS DOCUMENT.

© 20xx Renishaw plc. All rights reserved. Renishaw reserves the right to change specifications without notice. **RENISHAW** and the probe symbol used in the RENISHAW logo are registered trade marks of Renishaw plc in the United Kingdom and other countries. **apply innovation** and names and designations of other Renishaw products and technologies are trade marks of Renishaw plc or its subsidiaries. All other brand names and product names used in this document are trade names, trade marks or registered trade marks of their respective owners.



Part no.: H-5650-3341-01-A Issued: 07.2016