Pocket guide:

An explanation of CMM sensor technologies



CMM technology guide

A guide to CMM sensor technology – the heart of any CMM

CMM technology guide an explanation of CMM technologies

Pocket guide contents

This pocket guide provides an overview of the different sensing technologies available from Renishaw for in co-ordinate measuring machines (CMMs). It will help you select the right equipment for your CMM to get the very best out of your investment. It will be particularly useful when specifying new CMMs or considering upgrades or retrofits.

"...boost inspection throughput by as much as 50 times."



See section 6 5-axis measurement – Renscan 5™



Contents

	Page
Section 1 The range of automated probing systems at a glance	4
Section 2 Touch trigger probing – an introduction	5
Section 3 Touch trigger probing – entry level auto-indexing and stylus changing	6
Section 4 Touch trigger probing – advanced	7
Section 5 3-axis contact scanning	8-9
Section 6 5-axis measurement – Renscan5™	10-13
Section 7 Stylus and probe change racks – 'changers' promotion	14-15
Section 8 Styli selection – good practice	16-17
Section 9 Monitoring CMM accuracy – Machine checking gauge (MCG)	18-19
Section 10 Renishaw retrofits – A one stop shop service	20
Section 11 Modus™ software	21
System flexibility – I++DME	22
Section 13 Service and support	23
Section 14 Notes	24-25
Section 15 Worldwide contact information	26

The range of automated probing at a glance



* see section 7

CMM throughput

Automated probing

1



Touch trigger probing – an introduction

Renishaw invented the first touch trigger probe back in the early 1970s and since then, has constantly developed the technology to offer ever-increasing levels of accuracy and flexibility.

The job of a touch trigger probe is a simple one: to act as a highly repeatable, sub micron, switch giving a trigger signal when a surface to be measured is contacted.

This type of probe is best suited to applications where a few touch points are sufficient to define each feature of a component. Examples include prismatic parts with easily defined features such as flat faces, pockets, bores and bosses.



Touch trigger probing – with entry level auto-indexing and stylus changing

RTP20 - 'round the pole' head

The RTP20 head is a novel hybrid between a manual and a motorised indexing head and uses the CMM motion (not in-built motors) to automatically index to a range of positions at 15° increments (see picture sequence to right). The industry standard TP20 probe body is integral to the head and it can carry the full range of TP20 modules, giving an overall reach of up to 155 mm when a 60 mm stylus is used. The TP20 modules can be automatically changed using the MCR20 change rack included in the low cost kits. This is a popular choice with those taking their first step into automated inspection with a CMM.

For more advanced applications requiring longer extensions, more precise indexing or ultra precise probes, the PH10 head is the natural choice – see section 4.



Stylus module changing



Unlock



Re-orientate



Lock



Measure



Touch trigger probing - advanced

PH10T indexing head and TP20/TP200 probe (with free change racks*)



Always choose touch trigger probes with detachable magnetic stylus modules; they are no more expensive than older fixed types, and have significant time saving benefits and extra crash protection (e.g. TP20 and TP200).



*End users buying a PH10 head (or PH9 – PH10 upgrade) through participating OEMs receive a free MCR20 or SCR200 change rack - see section 7, 'changers' promotion for full details The PH10 range of motorised heads represent an auto-indexing solution which can carry up to 300 mm extensions and orientate probes to a wide range of angles at 7.5 ° increments (we know from over 20 years of experience that smaller increments compromise durability). It is a proven and robust system with full repair back up if accidents occur – see section 11, service and support.

PH10T with the industry standard TP20 probe is the most common head/probe combination used on CMMs worldwide. The flexibility of PH10's auto-indexing combined with TP20's automatic stylus changing with the FREE* MCR20 change rack is what makes it so popular.

By combining PH10T with the TP200 strain gauge probe, users still get automatic stylus changing, using the FREE* SCR200, and even higher repeatability with the capacity to carry longer (up to 100 mm) or heavier stylus configurations.

3-axis contact scanning

G 3-axis scanning - SP25M

Renishaw's high accuracy award winning SP25M is the most compact 3-axis scanning probe available, allowing it to be fitted to the PH10M/MQ indexing head.

SP25 is two probes in one - a high accuracy scanning probe and a touch trigger probe, giving added flexibility.

3-axis contact scanning offers significant speed advantages over touch trigger data capture.

3-axis scanning operates in a different way from touch trigger probing, by constantly streaming data as the stylus 'scans' in contact with the measurement surface (2000 – 6000 points a second is typical). The X, Y and Z axes of the machine provide all the movement during 3-axis scanning.



SP25M high accuracy indexing scanning probe



SP80 ultra-high accuracy fixed scanning probe



This type of system is suitable where features need large amounts of data to define their form, but maximum throughput is not top priority. Good examples include taking batch samples of propeller blades, aerofoil sections or automotive cylinder bores.

In these cases a few touch points don't give enough information to accurately measure the form.

The SP25M is the most recent 3-axis scanning probe of this type and is mounted using the autojoint connection on PH10M or PH10MQ heads.

The PH10M is a shank mounted head, whilst the PH10MQ is directly mounted within the quill of a CMM.

The SP80 is an ultra-high accuracy 3-axis scanning probe with some unique features - it can carry up to 800 mm long styli, and operates without the need for counter-balanced styli configurations. The addition of in-built crash protection means this high performance is protected from accidental damage.

Gear inspection is 30 times faster

It now takes Meltham Mills Engineering (MME) only eight minutes to inspect every critical feature on a typical gear component; 30 times faster than previously. Simultaneously, data is gathered on the form of features, the first time MME has had this automated capability. This has been made possible using Renishaw's SP25M scanning probe fitted to a new CMM, allowing continuous measurement data to be captured along 3D profiles.



5-axis measurement – with Renscan5[™]

Renscan5[™] is a revolutionary new CMM technology giving unrivalled speed and accuracy to boost inspection throughput by as much as 50 times.

The 5-axis technology can run identical routines to those commonly used with conventional touch trigger or 3-axis scanning probes, but also has additional time saving features for users to exploit.

Even before measurement begins, the technology reduces set-up time because Renscan5[™] probe heads (eg REVO[™]) only require a single 20 minute calibration routine to be accurate at all angles of their infinite rotation. This replaces the conventional multiple calibration procedure that can take many hours.

Where simple touch points are all that is required, they can be gathered 'on the fly' at very high speed using an infinitely positional 2-axis servo head. For a series of points around a bore, the head's axes revolve to the required position then 'flicks' the stylus out, taking the touch points.











This novel technique can also be used to take very rapid points on flat and freeform surfaces. The machine's axes guide the head parallel to the surface and the 'tip sensing' probe flicks down to take points without the machine slowing down (although scanning could be even guicker in many applications).

Most modern components are designed in CAD where designers have much more freedom to produce complex forms. When the finished components are inspected, it takes far too long using touch trigger probes or even 3-axis scanning. It is here where 5-axis scanning is invaluable with its ability to gather the huge quantity of accurate inspection data that is required.

When attempting to use traditional 3-axis scanning at high speed, large dynamic errors result from the machine frame flexing under the loads of movement.

5-axis measurement – with Renscan5[™] continued

Renscan5[™] uses novel techniques to eliminate dynamic errors from scanning results:

By fixing the machine's X, Y and Z-axes, whilst the 2-axis servo head scans the surface with a 'tip sensing' probe, no machine accelerations or decelerations are present to create dynamic errors.

In certain applications it isn't possible to measure components with the machine axes fixed. Instead the axes are moved in a vector (at constant speed) resulting in a smooth motion with minimal acceleration or deceleration, enabling the servo head and 'tip sensing' probe to scan accurately.

REVO[™], the first head to use Renscan5[™] technology manages to avoid the biggest limitation of 3-axis scanning (low speed) by breaking through the traditional speed/accuracy barrier. Although 3-axis scanning can run at speeds of up to 80 mm/sec, accuracy is severely compromised. Typically 15 – 20 mm/sec is required for accurate results.

REVO[™] can achieve speeds of up to 500 mm/sec **and** maintain accuracy.



It is difficult to identify one typical application for the Renscan5[™] technology as the range of benefits are so varied. Some customers justify the investment on calibration set up time alone, whilst others make best use of the ultra high scanning speeds. In either case the result is the same; large increases in inspection throughput.



Renscan5[™] uses 'tip sensing' a novel method of taking measurements very close to a component's surface with ultra high speed and accuracy.



Renscan5[™] systems are offered by CMM suppliers on new machines or as retrofit packages.

'Tip sensing' - how it works:

The 'tip sensor' is attached to a 2-axis servo positioning head which can orientate to infinite angles, and to the untrained eye looks like an ordinary carbon fibre extension rod with a stylus at the end. However, there are some important differences:

The carbon fibre stylus holder is hollow, allowing a laser beam to be fired down its centre to a reflector positioned immediately behind the stylus tip. The reflected beam returns back up the stylus holder and is focussed onto a position sensitive detector (PSD) in the servo head.

When the stylus tip comes into contact with a surface the stylus holder bends slightly, causing the laser beam to move on the PSD. The system then adjusts all 5 axes (3 machine axes and 2 rotary head axes) to maintain a constant deflection of 110 μ m.

Stylus and probe change racks – 'changers' promotion

The wide range of features and components measured in a typical factory means that manufacturers need a flexible measuring solution. A single sensor and stylus configuration will not be sufficient in most cases.

Stylus and module changing

Unless you are constantly measuring one simple component, you will need to change your stylus configuration to suit different measurement tasks. This can be done manually by swapping styli using the threaded connection, but takes time and requires a recalibration after every change.

Probe systems like TP20 are available with repeatable, automated means to change styli without the need to recalibrate each time. This greatly increases flexibility by allowing you to access features that demand long or complex styli, as well as using different styli types (sphere, disc, cylinder). It reduces operator intervention and increases measurement throughput.

The MCR20 module changing rack is completely passive and has the capability of storing up to 6 TP20 probe modules for automatic changing under measurement program control.



Changers promotion Under the 'changers' promotion auto-change racks are offered free of charge* to customers purchasing new PH10s (including PH9 – PH10 upgrades) from participating OEMs.

Rack	Probe	Cost
MCR20	TP20	FREE
SCR200	TP200	FREE
FCR25	SP25M	FREE
ACR3	various	(50% DISCOUNT)*





The MCR20 (free under the 'changers' scheme) is designed to securely hold the stored probe modules for automatic changing and to protect them from airborne contaminants which may be present in the working environment.



When using the TP200 high precision strain gauge probe, the SCR200 change rack provides automatic, high speed changing of up to six TP200 stylus modules. The SCR200 is powered by a separate interface and provides features to facilitate safe stylus changing.

Most Renishaw probes, including Renscan5[™] heads, have the ability to automatically interchange styli configurations, giving a more flexible solution.

Probe change racks

There are situations where the whole probe needs to be changed automatically, for example when using both contact and non-contact probes together on the same machine. In these cases a probe changing system like ACR3 is essential – these are discounted by 50% under the 'changers' scheme. The ACR3 probe changer safely stores the probes and because these each use a repeatable 'autojoint' there is no need for calibration after each change.







Styli selection - good practice



All Renishaw styli use high accuracy grade 5 balls as standard - look for the Renishaw logo on every stylus.



What type of styli should I choose?

General notes on stylus selection:

- Keep styli short; the shorter and stiffer a stylus the better the accuracy
- Choose the largest ball possible as this maximises stem clearance and minimises the effect of component surface finish
- Use as few joints as possible as they introduce potential points of bending and deflection which adversely affect accuracy
- Star styli allow up to 5 styli to be used in a cluster, and are useful when measuring internal features such as circlip grooves in bores.

In addition to the general features above, the following three areas should be considered:

1. Stylus ball grade

To achieve good accuracy most CMMs are supplied with grade 5 stylus balls. When purchasing replacements it is essential that lower grade (grade 10) styli are not chosen, as it is common for them to cause the loss of up to 15% of overall machine accuracy.



ry standard material,

This is the industry standard material, is very hard and wear resistant, and is used in the vast majority of applications.

Saving money on a stylus is false

accuracy of your quality assurance

system. For exceptional accuracy

Benishaw can offer ultra-accurate

grade 3 styli on special order. For

more information ask for Renishaw's

'Ball grading' document, part number

economy when it can compromise the

Silicon nitride

2. Stylus ball materials

H-1000-3001

Ruby

This is preferred to Ruby where aluminium is being scanned in a heavyduty cycle, as it resists a phenomenon known as 'adhesive wear'

Zirconia



When scanning cast iron in a heavyduty cycle, this material is more resistant to 'abrasive wear'.

3. Stylus stem materials

Steel

Most styli with a ball diameter greater than 2 mm and a length of up to 30 mm use non-magnetic stainless steel stems. A one-piece construction gives the optimum weight-to-stiffness ratio. This is the most common choice of stem material.

Tungsten carbide

Where the ball diameter is less than 1 mm or the stylus is up to 50 mm long, this material offers the best stiffness.

Ceramic

Where the ball diameter is greater than 3 mm or the stylus length is over 30 mm, this material offers the stiffness of stainless steel but is a lighter option than Tungsten carbide.

Carbon fibre (Renishaw GF)

This specially developed grade of carbon fibre is not only light, but also offers excellent stiffness when very long lengths are required (up to 800 mm with the SP80 scanning probe).

For more information on stylus selection, ball and stem materials, plus the full range of styli ask for Renishaw's 'Styli and accessories' guide (part number H-1000-3200).

Monitoring CMM accuracy – Machine checking gauge (MCG)





The machine checking gauge (MCG)

When a service engineer carries out the annual calibration check on your CMM, corrections are often made to the electronic error map to restore accuracy specifications. This well recognised procedure is essential, but many end users want a method of monitoring accuracy at regular intervals between these checks, or after a collision.

Using the Renishaw MCG, users are able to carry out a 10 minute interim verification of volumetric accuracy to ISO 10360-2. The results give assurance that measurements taken on the CMM are accurate, or give conclusive proof that re-calibration work is needed.

A range of pillar heights and arm lengths mean that volumetric accuracy can be checked on both large and small machines.



Do you trust your co-ordinate measuring machines? Take Messier-Dowty's lead and actively monitor CMM performance.

Messier Dowty (MD) takes the matter of CMM accuracy very seriously, establishing a regular and thorough program of MCG checks for the company's seven measuring machines.

Before MD invested in an MCG it had no way to monitor the accuracy of the CMM machines – it was unable to understand the impact on performance related to the specific working conditions. The MCG is now used to perform verification as part of the ISO 10360 standard, which defines the process of CMM verification.

By graphing the results, MD can monitor the machine accuracy every month. If it deviates too much too soon, the CMM is stopped and the calibration company brought in to re-qualify the machine.



Renishaw retrofits – A one stop shop service

Recent advances in CMM sensor and motion control technology allow users to get far more out of CMMs than was possible just a few years ago. This is especially true when using a modern software package like MODUS[™] with the benefits of intuitive CAD-based offline programming and graphical reporting.

Because these benefits are not derived from any significant changes to the CMM frame, it is possible to transform the performance and capability of an older frame with an upgrade, giving 'as new' benefits at a fraction of the cost of a new machine.

The new MODUS[™] software enables programs to be created offline allowing the CMM to continue measuring. By using programming wizards the task of creating or editing a program is much simpler and all programs are automatically DMIS compliant. Presentation of results in a graphical format allows all necessary information to be assessed at a glance. MODUS[™] software is guaranteed to keep pace with new sensor developments giving a future proof platform to meet future measurement needs.

An unparalleled choice of sensors are



available for retrofits, from a basic touch trigger probe (TP20) to fast scanning probes (SP25M or SP80), including the state-of-the-art REVO™ 5-axis scanning technology. New sensors and motion controllers have the ability to capture measurement data far more quickly (up to 50 times faster), shortening lead times and eliminating bottle necks. The overall result of these efficiency improvements is a reduction in operating costs.

Renishaw's UCC range of controllers are all I++DME compatible and allow open access to the error map giving end users the choice of which service company to use in the future. Some larger companies have chosen to bring CMM calibration in house.

All retrofits are backed up with telephone and on line support direct from Renishaw.



MODUS[™] software

Software is perhaps the biggest single reason why many CMM users choose to upgrade, as it is the aspect of the CMM that they interact with most often. Fast programming, swift program execution, friendly reporting and an up-to-date operating system all lead to increases in productivity.

Renishaw's MODUS™ metrology software is a modern package designed to make full use of the power of CAD, enabling rapid offline programming with nominal and tolerance data coming straight from the model. Reporting can be graphical rather than tabular, making it far easier to interpret measurement data and, more importantly, take appropriate action as a result.

MODUS[™] is built on industry standards such as the DMIS programming language, and I++ DME communication protocol with the CMM controller.

Highlights:

 Powerful offline editor, generating measurement programs directly from CAD with on-screen probe path verification



- Intuitive user interface that features full graphical display of measurement routines.
- Wizards provide a quick and easy way to create programs without the need for specialist programming skills.
- · Full compatibility with REVO
- Support for CAD formats IGES, STEP, Parasolid and VDAFS
- Full simulation and collision detection of 5-axis moves
- Full DMIS compliance allowing quick conversion of existing programs with minimal re-writing
- Future-proof investment, with guaranteed access to the latest sensor and controller technology advancements from Renishaw

System flexibility - I++DME

When deciding which overall CMM system is best for you, factors such as cost, functionality, CAD compatibility and personal preference will all be taken in to account. One area that should not be overlooked is 'flexibility':

CMM flexibility

The new I++DME (Dimensional Metrology Equipment) specification has been created by a number of large end users demanding a more flexible approach to the way their CMMs can be used (these include VW-Audi, BMW, Boeing, Volvo and Daimler Chrysler).

The specification was driven by a frustration that different brands of CMM were unable to share measurement jobs due to a lack of compatibility at the software/controller level.



The solution is an elegant one: specify all future controllers and software packages to share a common interface language (I++DME). All major controller and software suppliers now offer this option, so end users have the ability to swap software from machine to machine to suit production demands (every hour if necessary)!

The range of UCC CMM controllers from Renishaw are all I++DME compatible. Starting with UCC/*ite* for touch trigger applications, up to UCC2 with it's 5-axis scanning capability, for increased throughout.



Service and support

Renishaw recognises the value of good support and offers many different options direct to end-users.

Upgrades

One alternative with worn out or damaged product is to upgrade to a more modern equivalent. Where this is possible, the option will always be offered to you when contacting us.

Repairs

There are several levels of repair, so if your equipment only has a minor fault, you only pay a minor charge. However, all repaired items have to pass the same final tests as new equipment. In the case of PH10T/M motorised heads, that's 7 hours of cycle testing alone, where all 720 indexing positions are visited ten times, just one failure at one position, and the head is reworked at no extra charge to you.

RBE (Repair by exchange)

If damage is beyond economical repair, or immediate despatch is required, we have stocks of service exchange items (RBEs). These items have also passed the stringent 'as new' final tests, and have been subject to a complete refurbishment with the replacement of all parts subject to wear regardless of their condition. A fully refurbished PH10M RBE typically costs less than 30% of the new price, reflecting our commitment to existing users.



Notes







Worldwide contact information

Australia

- T +61 3 9521 0922
- E australia@renishaw.com

Austria

- T +43 2236 379790
- E austria@renishaw.com

Brazil

T +55 11 4195 2866 E brazil@renishaw.com

Canada

T +1 905 828 0104 E canada@renishaw.com

The People's Republic of China

- T +86 21 6180 6416
- E shanghai@renishaw.com

Czech Republic

- T +420 5 4821 6553
- E czech@renishaw.com

France

- T +33 1 64 61 84 84 E france@renishaw.com
- E france@renishaw.cor

Germany

T +49 7127 9810 F verkauf@renishaw.com

Hong Kong

- T +852 2753 0638
- E hongkong@renishaw.com

Hungary

- T +36 23 502 183
- E hungary@renishaw.com

India

- T +91 80 6623 6000
- E india@renishaw.com

Israel

- T +972 4 953 6595
- E israel@renishaw.com

Italy

- T +39 011 966 10 52
- E italy@renishaw.com

Japan

- T +81 3 5366 5317
- E japan@renishaw.com

Malaysia

- T +60 3 5631 4420
- E malaysia@renishaw.com

The Netherlands

T +31 76 543 11 00 E benelux@renishaw.com

Poland

- T +48 22 577 11 80
- E poland@renishaw.com

Russia

- T +7 495 231 1677
- E russia@renishaw.com

Singapore

T +65 6897 5466 E singapore@renishaw.com

Slovenia

- T +386 1 52 72 100
- E mail@rls.si

South Korea

- T +82 2 2108 2830
- E korea@renishaw.com

Spain

- T +34 93 663 34 20
- E spain@renishaw.com

Sweden

- T +46 8 584 90 880
- E sweden@renishaw.com

Switzerland

- T +41 55 415 50 60
- E switzerland@renishaw.com

Taiwan

- T +886 2473 3177
- E taiwan@renishaw.com

Thailand

- T +66 27 469 811
- E thailand@renishaw.com

Turkey

- T +90 216 380 92 40
- E turkiye@renishaw.com

UK (Head Office)

- T +44 1453 524524
- E uk@renishaw.com

USA

- T +1 847 286 9953
- E usa@renishaw.com

For all other countries

- T +44 1453 524524
- E international@renishaw.com





Renishaw plc

New Mills, Wotton-under-Edge, Gloucestershire GL12 8JR United Kingdom T +44 (0) 1453 524524

F +44 (0) 1453 524901

E uk@renishaw.com

www.renishaw.com

For worldwide Renishaw contact information please refer to page 26, or visit www.renishaw.com/contact

©2002-2009 Renishaw plc. All rights reserved.

RENISHAW® and the probe emblem used in the RENISHAW logo are registered trademarks of Renishaw plc in the UK and other countries. **apply innovation** is a trademark of Renishaw plc.