

RKLC incremental linear scale

RKLC is a robust, 6 mm wide stainless steel encoder tape scale with a thickness of 0.15 mm. This allows the scale, when rigidly fixed to a machine axis, to become 'mastered' to the machine substrate, matching its thermal expansion coefficient and behaviour. Differential movement between the scale and the machine is thus minimised, improving the metrological performance that can be achieved with simple thermal system compensation.

Index positions are provided by *IN-TRAC*[™] optical reference marks which are directly embedded into the incremental scale markings to enable auto-phasing. The combination of these compact reference marks with the narrow 6 mm wide scale facilitates encoder installation in space-constrained applications.

RKLC tape scale also combines $\pm 5 \ \mu$ m/m accuracy with the mechanical and chemical ruggedness of stainless steel, easy coiling and cut-to-length convenience.

RKLC is installed onto the axis substrate by a self-adhesive backing tape and a simple application tool makes this a quick, straightforward and inexpensive process. The scale ends are rigidly fixed to the axis substrate by means of epoxy fastened end clamps, eliminating the need to drill holes.

- Mastered scale matches the coefficient of thermal expansion of the substrate
- Narrow 6 mm wide scale suitable for confined spaces
- Suitable for partial arc applications
- IN-TRAC optical reference marks
- 20 µm and 40 µm pitch versions available
- 'Cut-to-length' convenience
- Up to 20 m lengths (> 20 m available on request)
- Compatible with VIONiC[™], TONiC[™] and QUANTiC[™] high-performance readheads
- High solvent immunity
- Scale accuracy up to ±5 µm/m. Further improvement possible with error correction



Compatible readheads

| | VIONiC | TONiC | QUANTIC |
|------------------|--|--|---|
| | MADEIN UK CC | - Title Transort | a contraction |
| Scale type | RKLC20-S | RKLC20-S | RKLC40-S/RKLC40H-S |
| Pitch | 20 µm | 20 µm | 40 µm |
| Outputs | Digital resolutions from 5 μ m to 2.5 nm direct from the readhead. | Analogue 1 Vpp. Digital resolutions from 5 μm to 1 nm from an interface. | Analogue 1 Vpp. Digital resolutions from 10 μm to 50 nm direct from the readhead. |
| SDE (typical) | < ±15 nm | ±30 nm | < ±80 nm [†] |
| Jitter (RMS) | down to 1.6 nm | down to 0.5 nm | down to 2.73 nm |
| Maximum speed | 12 m/s | 10 m/s | 24 m/s† |
| UHV variant | No | Yes* | No |

* Scale mastering is not guaranteed after system bakeout.

[†] Digital variants.

Readhead features

- > Filtering optics and Auto Gain Control for high reliability and solid Lissajous signals.
- Dynamic signal processing ensures ultra-low sub-divisional error (SDE). Result: smoother scanning performance.
- > High signal-to-noise ratio provides ultra-low jitter for optimum positional stability.
- Auto-phasing of *IN-TRAC* reference mark.
- Clocked outputs ensure optimised speed performance for all resolutions, for a wide variety of industry-standard controllers.
- > Diagnostic tool compatibility for detailed information on encoder performance.
- DOP Dual output interfaces available to provide simultaneous analogue and digital outputs (TONiC systems only).



RKLC scale specifications*

| Form (H × W) | | 0.15 mm × 6 mm including adhesive |
|-----------------------------|------------------------|--|
| Pitch | RKLC20-S | 20 µm |
| | RKLC40-S/RKLC40H-S | 40 µm |
| Accuracy (at 20 °C) | RKLC20-S/RKLC40H-S | ±5 μm/m |
| | RKLC40-S | ±15 μm/m |
| Linearity (at 20 °C) | RKLC20-S/RKLC40H-S | $\pm 2.5 \ \mu\text{m/m}$ achievable with two point error correction |
| | RKLC40-S | $\pm 3 \ \mu$ m/m achievable with two point error correction |
| Supplied length | | 20 mm to 20 m (> 20 m available on request) |
| Material | | Hardened and tempered stainless steel |
| Mass | | 4.6 g/m |
| Coefficient of thermal expa | ansion (at 20 °C) | Matches that of substrate material when scale ends fixed by epoxy mounted end clamps |
| Temperature | Storage | –20 °C to +80 °C |
| | Operating [†] | 0 °C to +70 °C |
| | Installation | +10 °C to +35 °C |
| Humidity | | 95% relative humidity (non-condensing) to IEC 60068-2-78 |
| Shock | Operating | 500 m/s², 11 ms, ½ sine, 3 axes |
| Vibration | Operating | 300 m/s ² max @ 55 to 2000 Hz, 3 axes |
| End fixing | | Epoxy mounted end clamps (A-9523-4015) |
| | | Approved epoxy adhesive (A-9531-0342) |
| | | Scale end movement typically < 1 μ m [‡] |

Reference mark

| Туре | <i>IN-TRAC</i> reference mark $^{\diamond}$, directly embedded into incremental track, 50 mm (nominal) spacing |
|--|---|
| Selection Single reference mark selection by magnetic actuator (A-9653-0143) customer positioned | |
| Repeatability | Unit of resolution repeatability (bi-directional) across full system rated speed and temperature ranges |

Limit switches

| Туре | Magnetic actuators; with dimple triggers Q limit, without dimple triggers P limit (see RKLC scale installation drawings) | |
|---|--|--|
| Trigger point The limit output is nominally asserted when the readhead limit switch sensor passes leading edge, but can trigger up to 3 mm before that edge | | |
| Mounting Customer placed at desired locations | | |
| Repeatability | < 0.1 mm | |

* For more information on partial arc applications refer to RKL scale for partial arc applications data sheet (Renishaw part no. L-9517-9897).

[†] To limit maximum tension in the scale ($CTE_{substrate} - CTE_{scale}$) × ($T_{use extreme} - T_{install}$) ≤ 550 µm/m where $CTE_{scale} = ~ 10.1 µm/m/°C$. [‡] Ensure that scale and end clamps have been installed following the installation process described in the relevant RKLC installation guide.

*Scale available with no *IN-TRAC* reference mark; see scale part numbers for details.



Dimensions and tolerances in mm

RKLC scale installation drawing







Scale part numbers

RKLC-S

Stainless steel tape scale with self-adhesive backing tape.

| | | | Distance from scale end to first reference mark | Part number (where xxxx is the length in cm) [†] | | |
|-------------------------------|-------------------------------|--|--|--|---|--|
| Available lengths | Available in increments of | Reference mark spacing [*] | | RKLC20-S (Compatible with VIONiC and TONiC) | RKLC40-S (Compatible with QUANTiC) | RKLC40H-S (Compatible with QUANTIC) |
| 20 mm to 100 mm | 10 mm | Middle of scale length | Middle of scale length | A-6663-xxxx | A-6665-xxxx A-6685-xxxx | A 6695 YYYY |
| > 100 mm to 20 m [‡] | 10 mm | 50 mm | 50 mm | A-0003-XXX | | A-0003-XXXX |

RKLR-S (no reference mark)

Stainless steel tape scale with self-adhesive backing tape.

| | Available | Available in | Part number (where xxxx is the length in cm) [†] | | |
|---------|----------------------------|---------------|--|---------------------------------------|--|
| lengths | | increments of | RKLR20-S (Compatible with VIONIC and TONIC) | RKLR40-S (Compatible with QUANTIC) | |
| | 20 mm to 20 m [‡] | 10 mm | A-6753-xxxx | A-6744-xxxx | |

* Only calibrated reference mark is bi-directionally repeatable.

[†] Ordering A-6663-0070 for example, will result in a 70 cm length of RKLC20-S.
[‡] Lengths greater than 20 m available on request.



Accessory part numbers

Reference mark and limit magnets*

| Part description | Part number | Product image |
|---|-------------|---------------|
| Reference mark selector magnet – Adhesive mounted | A-9653-0143 | |
| Bolted reference mark selector magnet | A-9653-0290 | |
| Q limit switch actuator magnet – Adhesive mounted | A-9653-0139 | |
| Bolted Q limit switch actuator magnet | A-9653-0291 | |
| P limit switch actuator magnet – Adhesive mounted | A-9653-0138 | |
| Bolted P limit switch actuator magnet | A-9653-0292 | |
| Magnet applicator device (Aids positioning) | A-9653-0201 | |

* Longer limit magnets are available. Contact your local Renishaw representative for more information.

RKLC scale accessories

| Guillotine (For cutting RKLC scale) | A-9589-0071 | |
|--|-------------|------------------|
| Shears (For cutting RKLC scale) | A-9589-0133 | |
| RKLC-S side mount scale applicator (Compatible with all VIONiC, TONiC and QUANTiC side mount systems) | A-6547-1912 | |
| RKLC-S top mount scale applicator (Required for TONiC top mounted systems only) | A-6547-1915 | NUMBER OF STREET |



End clamp accessories

| Part description | Part number | Product image |
|---|-------------|--|
| RGC-F End clamp kit – epoxy mounted. The RGC-F end clamps master the RKLC scale to the substrate material to match its thermal expansion. | A-9523-4015 | Recently and the second s |
| End clamp kit, epoxy mounted, narrow The end clamps master the RKLC scale to the substrate material to match its thermal expansion. | A-9523-4027 | |
| RGG-2 (2 part epoxy) The RGG-2 epoxy is recommended for the mounting of end clamps. | A-9531-0342 | |

Renishaw plc New Mills, Wotton-under-Edge Gloucestershire, GL12 8JR United Kingdom

T +44 (0)1453 524524 F +44 (0)1453 524901 E uk@renishaw.com www.renishaw.com



Compatible products



For worldwide contact details, visit www.renishaw.com/contact

RENISHAW HAS MADE CONSIDERABLE EFFORTS TO ENSURE THE CONTENT OF THIS DOCUMENT IS CORRECT AT THE DATE OF PUBLICATION BUT MAKES NO WARRANTIES OR REPRESENTATIONS REGARDING THE CONTENT. RENISHAW EXCLUDES LIABILITY, HOWSOEVER ARISING, FOR ANY INACCURACIES IN THIS DOCUMENT.

© 2019-2020 Renishaw plc. All rights reserved. Renishaw reserves the right to change specifications without notice. **RENISHAW** and the probe symbol used in the RENISHAW logo are registered trade marks of Renishaw plc in the United Kingdom and other countries. **apply innovation** and names and designations of other Renishaw products and technologies are trade marks of Renishaw plc or its subsidiaries. All other brand names and product names used in this document are trade names, trade marks or registered trade marks of their respective owners.



Part no.: L-9517-9862-01-D Issued: 12.2020