

RMB14 angular magnetic encoder module







The image does not represent all variants.

The RMB14 is a compact, absolute high-speed encoder module. With a PCB diameter of only 14 mm, the module fits motor control and instrumentation. into miniature designs.

The encoder module consists of a magnetic actuator and a separate sensor board. The rotation of the magnetic actuator is read and processed by a custom encoder chip mounted on the sensor board to obtain the required output format. The output signals are provided in industry standard absolute and incremental formats.

The RMB14 can be used in a variety of applications including robotic grippers, marine, medical, printing, converting, industrial automation,

Product range

RMB14IC

Incremental with 128 to 1,024 pulses per revolution (32 to 4,096 counts per revolution with x4 evaluation).


RMB14SC

Synchro serial interface (SSI) with 32 to 4,096 positions per revolution.

- 14 mm diameter circular module
- 3.3 V and 5 V power supply
- High speed operation up to 30,000 rpm
- Absolute up to 12 bit resolution (4,096 counts per revolution)
- Industry standard absolute and incremental output formats
- Accuracy up to ±0.5°
- RoHS compliant (lead free) see **Declaration of conformity**

Data sheet RMB14D01_03

Installation drawingDimensions and tolerances in mm.






RMB14IC - Incremental output, RS422

Power supply	$V_{dd} = 3.3 \text{ V or } 5 \text{ V } \pm 5\%$
Current consumption	Max. 35 mA
Output signals	A+, B+, Z+, A-, B- Z- (RS422)
Accuracy*	±0.5° *
Hysteresis	0.18°
Resolutions	32, 64, 128, 256, 512, 1024, 2048, 4096 cpr
Maximum speed	30,000 rpm
Temperature Operating and storage	-40 °C to +85 °C (limited by FFC connector)

^{*} Valid for Ø4 × 4 mm magnets only.


Recommended signal termination

For data output lines only



Connections

RMB14IC with FFC connector



Connector type JST_08FKZ-SM1-1-TB

Zero position setting

Encoder zero position can be easily set by shortening the zeroing pads on the board. After locking the motor at the mechanical zero position short together the two zeroing pads.

The output angle position data can be zeroed at any angle with resolution of 0.0879° .

RMB14D01_03


RMB14SC - Absolute binary synchro-serial (SSI), RS422

Power supply	$V_{dd} = 3.3 \text{ V or } 5 \text{ V } \pm 5 \%$
Current consumption	Max. 35 mA
Data output	Serial data (RS422)
Data input	Clock (RS422)
Accuracy	Typ. ±0.5° *
Hysteresis	0.18°
Resolutions	32, 64, 128, 256, 512, 1,024, 2,048, 4,096 cpr
Maximum speed	30,000 rpm
Temperature Operating and storage	-25 °C to +85 °C (limited by SMD connector)-40 °C to +85 °C (limited by FFC connector)

^{*} Valid for Ø4 × 4 mm magnets only.


Connections

RMB14SC with FFC connector



Connector type JST_08FKZ-SM1-1-TB

RMB14SC with SMD connector



Connector type
JST SM06B-SURS-TF


Mating connector
JST 06SUR-32S (not provided)

Zero position setting

Encoder zero position can be easily set by shortening the zeroing pads on the board. After locking the motor at the mechanical zero position short together the two zeroing pads.

The output angle position data can be zeroed at any angle with resolution of 0.0879°.


Timing diagram



Clock \leq 1 MHz 20 μ s \leq t_m \leq 40 μ s


Recommended signal termination

For data output lines only





Part numbering



NOTE: Not all combinations are valid.

Valid combinations:

RMB14ICxxxE10 – Incremental, RS422, circular, FFC connector, 5 V RMB14ICxxxE33 – Incremental, RS422, circular, FFC connector, 3.3 V RMB14SCxxxE10 – Absolute SSI, circular, FFC connector, 5 V RMB14SCxxxE33 – Absolute SSI, circular, FFC connector, 3.3 V RMB14SCxxxF10 – Absolute SSI, circular, SMD connector, 5 V RMB14SCxxxF33 – Absolute SSI, circular, SMD connector, 3.3 V

Magnet ordering information

Magnet for direct recessing in non-ferrous shafts

Fixing: Glue (recommended - LOCTITE 648 or LOCTITE 2701)







Part numbers:

For resolutions up to 9 bit absolute (512 cpr incremental)

RMM44A2A00 (individually packed) – for sample quantities only

RMM44A2C00 (packed in tubes)

For resolutions from 10 bit absolute (800 cpr incremental) and above RMM44A3A00 (individually packed) – for sample quantities only RMM44A3C00 (packed in tubes)



NOTE: RMM3010 magnets are only tested (not graded). Specified accuracy cannot be achieved by using magnet RMM3010.

^{*} For sample quantities of RMB14 supplied with a magnet please add "KIT" to the end of the required RMB14 part number, eg. RMB14IC09BE10KIT.

Data sheet

RMB14D01_03


Accessories

Cables

ACC031, ACC032 (compatible with RMB14SC with SMD connector)



Part number	Cable length (L)
ACC031	1 m
ACC032	0.5 m



Dimensions and tolerances in mm.

Cable specifications	M-9693-2350-01-C
Configuration	10 × 0.0320 mm ²
Sheath color	Black
Rated voltage	30 V
Temperature range	From -40 °C to +90 °C

Pin	Wire color
1	Red
2	Blue
3	Green
4	Yellow
5	Brown
6	White

ACC037 (compatible with RMB14SC with FFC connector)

Molex Premo-Flex™ FFC Jumper, 6 Circuits, 203 mm



ACC038 (compatible with RMB14IC with FFC connector)

Molex Premo-Flex™ FFC Jumper, 8 Circuits, 203 mm





Head office

RLS merilna tehnika d.o.o.

Poslovna cona Žeje pri Komendi Pod vrbami 2 SI-1218 Komenda Slovenia

T +386 1 5272100 F +386 1 5272129 E mail@rls.si www.rls.si

Document issues

Issue	Date	Page	Amendments done
1	18. 10. 2019	-	New document
2	3. 2. 2020	6	Cable ordering informations added
3	24. 2. 2020	6	ACC037 and ACC038 cable options added

This product is not designed or intended for use outside the environmental limitations and operating parameters expressly stated on the product's datasheet. Products are not designed or intended for use in medical, military, aerospace, automotive or oil & gas applications or any safety-critical applications where a failure of the product could cause severe environmental or property damage, personal injury or death. Any use in such applications must be specifically agreed to by seller in writing, and is subject to such additional terms as the seller may impose in its sole discretion. Use of products in such applications is at buyer's own risk, and buyer will indemnify and hold harmless seller and its affiliates against any liability, loss, damage or expense arising from such use. Information contained in this datasheet was derived from product testing under controlled laboratory conditions and data reported thereon is subject to the stated tolerances and variations, or if none are stated, then to tolerances and variations consistent with usual trade practices and testing methods. The product's performance outside of laboratory conditions, including when one or more operating parameters is at its maximum range, may not conform to the product's datasheet. Further, information in the product's datasheet does not reflect the performance of the product in any application, end-use or operating environment buyer or its customer may put the product to. Seller and its affiliates make no recommendation, warranty or representation as to the suitability of the product for buyer's application, use, end-product, process or combination with any other product or as to any results buyer or its customer might obtain in their use of the product. Buyer should use its own knowledge, judgment, expertise and testing in selecting the product for buyer's application, end-use and/or operating environment, and should not rely on any oral or written statement, representation, or samples made by seller or its affiliates for any purpose. EXC

RLS merilna tehnika d.o.o. has made considerable effort to ensure the content of this document is correct at the date of publication but makes no warranties or representations regarding the content. RLS merilna tehnika d.o.o. excludes liability, howsoever arising, for any inaccuracies in this document.